

## CDBD1040-G Thru. CDBD10200-G

Reverse Voltage: 40 to 200 Volts

Forward Current: 10.0 Amp

RoHS Device




### Features


- Batch process design, excellent power dissipation offers better reverse leakage current and thermal resistance.
- Low power loss, high efficiency.
- High current capability, low forward voltage drop.
- High surge capability.
- Guard ring for overvoltage protection.
- Ultra high-speed switching.
- Silicon epitaxial planar chip, metal silicon junction.
- Lead-free part meets environmental standards of MIL-STD-19500 /228

### Mechanical data

- Case: TO-263/D2PAK, molded plastic.
- Terminals: Solder plated, Solderable per MIL-STD-750, method 2026.
- Polarity: Indicated by cathode band.
- Mounting Position: Any
- Weight: 1.46 grams (approx.).



### Circuit Diagram



### Maximum Ratings (At Ta=25°C, unless otherwise noted)

| Parameter                                                                                               |                                                        | Symbol           | CDBD<br>1040-G | CDBD<br>1060-G | CDBD<br>10100-G | CDBD<br>10150-G | CDBD<br>10200-G | Unit |
|---------------------------------------------------------------------------------------------------------|--------------------------------------------------------|------------------|----------------|----------------|-----------------|-----------------|-----------------|------|
| Repetitive peak reverse voltage                                                                         |                                                        | V <sub>RRM</sub> | 40             | 60             | 100             | 150             | 200             | V    |
| Continuous reverse voltage                                                                              |                                                        | V <sub>R</sub>   | 40             | 60             | 100             | 150             | 200             | V    |
| RMS voltage                                                                                             |                                                        | V <sub>RMS</sub> | 28             | 42             | 70              | 105             | 140             | V    |
| Maximum forward rectified current<br>(See fig. 1)                                                       |                                                        | I <sub>O</sub>   | 10.0           |                |                 |                 |                 | A    |
| Maximum forward voltage<br>I <sub>F</sub> =5.0A                                                         |                                                        | V <sub>F</sub>   | 0.55           | 0.75           | 0.85            | 1.00            |                 | V    |
| Maxium forward surge current, 8.3ms<br>singlehalf sine-wave superimposed on<br>rate load (JEDEC method) |                                                        | I <sub>FSM</sub> | 150            |                |                 |                 |                 | A    |
| Maximum reverse<br>current                                                                              | V <sub>R</sub> =V <sub>RRM</sub> T <sub>A</sub> =25°C  | I <sub>R</sub>   | 0.5            |                |                 |                 |                 | mA   |
|                                                                                                         | V <sub>R</sub> =V <sub>RRM</sub> T <sub>A</sub> =100°C | I <sub>R</sub>   | 50             |                |                 |                 |                 | mA   |
| Typical thermal<br>resistance                                                                           | Junction to Case                                       | R <sub>θJc</sub> | 3.0            |                |                 |                 |                 | °C/W |
| Operating temperature                                                                                   |                                                        | T <sub>J</sub>   | -55 to +125    | -55 to +150    |                 |                 |                 | °C   |
| Storage temperature                                                                                     |                                                        | T <sub>STG</sub> | -65 to +175    |                |                 |                 |                 | °C   |

## RATING AND CHARACTERISTIC CURVES (CDBD1040-G Thru. CDBD10200-G)

FIG.1- Typical Forward Current Derating Curve




FIG.2- Typical Forward Characteristics




FIG.3- Maximum Non-Repetitive Forward Surge Current






FIG.4 - Typical Reverse Characteristics



## Reel Taping Specification




| TO-263/D2PAK | SYMBOL | A                 | B                 | C                 | d                 | D                 | D1         | D2                |
|--------------|--------|-------------------|-------------------|-------------------|-------------------|-------------------|------------|-------------------|
|              | (mm)   | $10.70 \pm 0.10$  | $16.30 \pm 0.10$  | $5.10 \pm 0.10$   | $1.50 \pm 0.10$   | $330.00 \pm 2.00$ | 50.0 MIN.  | $13.0 \pm 0.50$   |
|              | (inch) | $0.421 \pm 0.004$ | $0.642 \pm 0.004$ | $0.201 \pm 0.004$ | $0.059 \pm 0.004$ | $13.00 \pm 0.079$ | 1.969 MIN. | $0.512 \pm 0.020$ |

| TO-263/D2PAK | SYMBOL | E                 | F                 | P                 | P0                | P1                | T                 | W                 | W1                |
|--------------|--------|-------------------|-------------------|-------------------|-------------------|-------------------|-------------------|-------------------|-------------------|
|              | (mm)   | $1.75 \pm 0.10$   | $11.50 \pm 0.10$  | $16.00 \pm 0.10$  | $4.00 \pm 0.10$   | $2.00 \pm 0.10$   | $0.23 \pm 0.10$   | $24.00 \pm 0.30$  | $30.00 \pm 1.0$   |
|              | (inch) | $0.069 \pm 0.004$ | $0.453 \pm 0.004$ | $0.630 \pm 0.004$ | $0.157 \pm 0.004$ | $0.079 \pm 0.004$ | $0.009 \pm 0.004$ | $0.945 \pm 0.012$ | $1.181 \pm 0.039$ |

## Marking Code


| Part Number | Marking Code |
|-------------|--------------|
| CDBD1040-G  | SK1040       |
| CDBD1060-G  | SK1060       |
| CDBD10100-G | SK10100      |
| CDBD10150-G | SK10150      |
| CDBD10200-G | SK10200      |



XXXXXXX / XXXXXXXX = Product type marking code

## Suggested PAD Layout

| SIZE | TO-263 / D2PAK |        |
|------|----------------|--------|
|      | (mm)           | (inch) |
| A    | 9.50           | 0.374  |
| B    | 2.50           | 0.098  |
| C    | 16.90          | 0.665  |
| X1   | 10.80          | 0.425  |
| X2   | 1.80           | 0.071  |
| Y1   | 11.40          | 0.449  |
| Y2   | 3.50           | 0.138  |



## Standard Packaging

| Case Type    | REEL PACK       |                     |
|--------------|-----------------|---------------------|
|              | REEL<br>( pcs ) | Reel Size<br>(inch) |
| TO-263/D2PAK | 800             | 13                  |