




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	54		U2	REVISED PER ECR-17-018200	09JAN2018	BDA	SC



- 1

MATERIAL: CONNECTOR – NYLON UL94V-2 (YELLOW).
CONTACTS – 0.30[.012] THICK COPPER ALLOY (BRIGHT TIN-LEAD 0.00203[.000080] MIN. THICK FOR CONTACTS 640600-2 THRU 2-640600-4)
(MATTE WHISKER MITIGATED TIN 0.00203[.000080] MIN THICKNESS OVER NICKEL UNDERPLATE FOR 3-640600-2 THRU 5-640600-4).
- 2

CONTACTS ACCEPT 20 AWG WIRE WITH 2.41[.095] MAX INSULATION DIAMETER.
- 3

CONTACTS MUST ACCEPT 1.14±0.03[.045±.001] SQUARE POST AND REMAIN LOCKED IN POSITION.
- 4

IDENTIFICATION NUMBER FOR LAST CIRCUIT MAY NOT APPEAR ON ALL ASSEMBLIES.
- 5

DIMENSIONS IN BRACKETS ARE IN INCHES.
- 6

HOUSING FEATURES ARE: FEED-THRU WITH LOCKING RAMP.
- 7

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 8

OBSOLETE PARTS

95.10	[3.744]	24	5-640600-4
91.14	[3.588]	23	5-640600-3
87.17	[3.432]	22	5-640600-2
83.21	[3.276]	21	5-640600-1
79.25	[3.120]	20	5-640600-0
75.29	[2.964]	19	4-640600-9
71.32	[2.808]	18	4-640600-8
67.36	[2.652]	17	4-640600-7
63.40	[2.496]	16	4-640600-6
59.44	[2.340]	15	4-640600-5
55.47	[2.184]	14	4-640600-4
51.51	[2.028]	13	4-640600-3
47.55	[1.872]	12	4-640600-2
43.59	[1.716]	11	4-640600-1
39.62	[1.560]	10	4-640600-0
35.66	[1.404]	9	3-640600-9
31.70	[1.248]	8	3-640600-8
27.74	[1.092]	7	3-640600-7
23.77	[.936]	6	3-640600-6
19.81	[.780]	5	3-640600-5
15.85	[.624]	4	3-640600-4
11.89	[.468]	3	3-640600-3
7.92	[.312]	2	3-640600-2
95.10	[3.744]	24	2-640600-4
91.14	[3.588]	23	2-640600-3
87.17	[3.432]	22	2-640600-2
83.21	[3.276]	21	2-640600-1
79.25	[3.120]	20	2-640600-0
75.29	[2.964]	19	1-640600-9
71.32	[2.808]	18	1-640600-8
67.36	[2.652]	17	1-640600-7
63.40	[2.496]	16	1-640600-6
59.44	[2.340]	15	1-640600-5
55.47	[2.184]	14	1-640600-4
51.51	[2.028]	13	1-640600-3
47.55	[1.872]	12	1-640600-2
43.59	[1.716]	11	1-640600-1
39.62	[1.560]	10	1-640600-0
35.66	[1.404]	9	640600-9
31.70	[1.248]	8	640600-8
27.74	[1.092]	7	640600-7
23.77	[.936]	6	640600-6
19.81	[.780]	5	640600-5
15.85	[.624]	4	640600-4
11.89	[.468]	3	640600-3
7.92	[.312]	2	640600-2

SUPERSEDED
7

8
SUPERSEDED
7

8
SUPERSEDED

7
SUPERSEDED

8
SUPERSEDED

DIM A	NO OF CIRCUITS	PART NO
-------	----------------	---------

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. LEWIS	12FEB91	 TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK R. SWING	12FEB91			
	0 PLC ± -	APVD D. CLARK	19FEB91	NAME MTA-156 CONNECTOR ASSEMBLY, 20 AWG, STANDARD		
	1 PLC ± -	PRODUCT SPEC 108-1051				
	2 PLC ± -	APPLICATION SPEC 114-1020				
	3 PLC ± 0.13 [.005]					
	4 PLC ± -	WEIGHT	SIZE A2	CAGE CODE 00779	DRAWING NO C-640600	RESTRICTED TO -
	ANGLES ± -	CUSTOMER DRAWING	SCALE 4:1		SHEET 1 of 1	REV U2