

# GX-F/H SERIES


**Related Information**

■ General terms and conditions..... F-17

■ Sensor selection guide ..... P.757~

■ Glossary of terms..... P.1386~

■ General precautions ..... P.1405

Conforming to  
EMC Directive[panasonic-electric-works.net/sunx](http://panasonic-electric-works.net/sunx)PNP output  
type available

Oil resistant


Different freq.  
type available

## Industry No. 1\* in stable sensing

\* Based on research conducted by Panasonic Electric Works SUNX as of August 2010 among equivalent rectangular inductive sensors.

### Can be installed with ample space

This sensor has the longest stable sensing range among the same level of rectangular inductive proximity sensors in the industry. It is easy to install the sensor.



| Type               | Maximum operation distance | Stable sensing range        |                             |
|--------------------|----------------------------|-----------------------------|-----------------------------|
|                    |                            | GX-F/H series               | Previous model              |
| <b>GX-□6</b>       | 1.6 mm <b>0.063 in</b>     | 0 to 1.3 mm <b>0.051 in</b> | 0 to 1.2 mm <b>0.047 in</b> |
| <b>GX-□8</b>       | 2.5 mm <b>0.098 in</b>     | 0 to 2.1 mm <b>0.083 in</b> | 0 to 1.8 mm <b>0.709 in</b> |
| <b>GX-□12</b>      | 4.0 mm <b>0.157 in</b>     | 0 to 3.3 mm <b>0.130 in</b> | 0 to 3.0 mm <b>0.118 in</b> |
| <b>GX-□15</b>      | 5.0 mm <b>0.197 in</b>     | 0 to 4.2 mm <b>0.165 in</b> | 0 to 4.0 mm <b>0.157 in</b> |
| Long sensing range | 8.0 mm <b>0.315 in</b>     | 0 to 6.7 mm <b>0.264 in</b> | 0 to 6.4 mm <b>0.252 in</b> |


\* With standard sensing object

### Variation at the maximum operation distance is within ±8 %

Thorough adjustment and control of sensing sensitivity greatly reduces individual sensor differences and variations.

The work of adjusting sensor positions when using multiple sensors and when sensors have been replaced is much easier.


Example: GX-□8






### Temperature characteristics vary within ±8 %

Components such as the sensor coil and core and product design have been totally revised to provide excellent temperature characteristics.

Stable sensing can be obtained regardless of the time of day or the yearly season.




\* Typical

**APPLICATIONS****Muting control of light curtains****Positioning processing equipment****Positioning metal pallets****ENVIRONMENTAL RESISTANCE****10 times the durability! (Compared to previous models)**


The new integrated construction method used provides shock resistance of 10,000 m/s<sup>2</sup> (approx. 1,000 G in X, Y and Z directions for three times each), and vibration resistance clears durability tests of between 10 and 500 Hz (3 mm 0.118 in amplitude in X, Y and Z directions for 2 hours each). In addition, resistance to impulse noise is approx. three times greater than for previous models.

Checking up / down  
operation of  
compact molding  
equipment



Shock resistance:  
1,000 G

Sensing presence of metallic  
objects on a part feeder



Vibration resistance: 500 Hz

**Highly resistant to water or oil!  
IP68g\* protective construction**


The new integrated construction method used improves environmental resistance performance. The IP68g prevents damage to the sensor by stopping water and oil getting inside.

\* For details, refer to the "SPECIFICATIONS".

**FUNCTIONS****Indicators are easy to see over a wide field of view**

A prism with a wide field of view has been developed. This has greatly improved the visibility of the operation indicators.

GX-H□



GX-F□

**MOUNTING****Tightening strength increased with no damage! (excluding GX-□6)**

A metal sleeve has been inserted. It prevents the sensor from being damaged by tightening too much.

GX-□8, GX-□12



Approx. 1.4 times  
greater than before

M3 screw  
Tightening torque: 0.7 N · m or less

GX-□15



M3 screw  
Tightening torque: 1 N · m or less


**Conductor thickness doubled to make wiring much easier! (GX-□6/□8 only)**

The conductor's thickness was doubled for the GX-□6/□8. This makes it easier to handle and perform crimping work on the cables. In addition, the tensile strength of the crimping area has become higher.

0.08 mm<sup>2</sup>  
Previous model



0.15 mm<sup>2</sup>  
GX-□8



Conductor thickness approx.  
2 times greater

FIBER  
SENSORS

LASER  
SENSORS

PHOTOELECTRIC  
SENSORS

MICRO  
PHOTOELECTRIC  
SENSORS

AREA  
SENSORS

LIGHT  
CURTAINS

PRESSURE /  
FLOW  
SENSORS

INDUCTIVE  
PROXIMITY  
SENSORS

PARTICULAR  
USE SENSORS

SENSOR  
OPTIONS

SIMPLE  
WIRE-SAVING  
UNITS

WIRE-SAVING  
SYSTEMS

MEASUREMENT  
SENSORS

STATIC CONTROL  
DEVICES

ENDSCOPE

LASER  
MARKERS

PLC /  
TERMINALS

HUMAN MACHINE  
INTERFACES

ENERGY CONSUMPTION  
VISUALIZATION  
COMPONENTS

FA COMPONENTS

MACHINE VISION  
SYSTEMS

UV CURING  
SYSTEMS

Selection  
Guide

Amplifier  
Built-in  
Amplifier-  
separated

**GX-F/H**







**GXL**

**GL**

**GX-U/GX-FU/  
GX-N**

**GX**

**ORDER GUIDE****GX-6 type**






| Type       |               | Appearance (mm in)                                                                | Sensing range (Note 1)                                                            | Model No.<br>(Note 2) | Output                        | Output operation |
|------------|---------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------|-------------------------------|------------------|
| NPN output | Front sensing |  |  | GX-F6A                | NPN open-collector transistor | Normally open    |
|            | Top sensing   |  |                                                                                   | GX-F6AI               |                               | Normally closed  |
|            |               |                                                                                   |                                                                                   | GX-F6B                |                               | Normally open    |
|            |               |                                                                                   |                                                                                   | GX-F6BI               |                               | Normally closed  |
|            |               |                                                                                   |                                                                                   | GX-H6A                |                               | Normally open    |
|            |               |                                                                                   |                                                                                   | GX-H6AI               |                               | Normally closed  |
|            |               |                                                                                   |                                                                                   | GX-H6B                |                               | Normally open    |
|            |               |                                                                                   |                                                                                   | GX-H6BI               |                               | Normally closed  |
| PNP output | Front sensing |  |  | GX-F6A-P              | PNP open-collector transistor | Normally open    |
|            | Top sensing   |  |                                                                                   | GX-F6AI-P             |                               | Normally closed  |
|            |               |                                                                                   |                                                                                   | GX-F6B-P              |                               | Normally open    |
|            |               |                                                                                   |                                                                                   | GX-F6BI-P             |                               | Normally closed  |
|            |               |                                                                                   |                                                                                   | GX-H6A-P              |                               | Normally open    |
|            |               |                                                                                   |                                                                                   | GX-H6AI-P             |                               | Normally closed  |
|            |               |                                                                                   |                                                                                   | GX-H6B-P              |                               | Normally open    |
|            |               |                                                                                   |                                                                                   | GX-H6BI-P             |                               | Normally closed  |

Notes: 1) The maximum operation distance stands for the maximum distance for which the sensor can detect the standard sensing object.

The stable sensing range stands for the sensing range for which the sensor can stably detect the standard sensing object even if there is an ambient temperature drift and/or supply voltage fluctuation.

2) "I" in the model No. indicates a different frequency type.

**GX-8 type**






| Type       |               | Appearance (mm in)                                                                  | Sensing range (Note 1)                                                              | Model No.<br>(Note 2) | Output                        | Output operation |
|------------|---------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-----------------------|-------------------------------|------------------|
| NPN output | Front sensing |  |  | GX-F8A                | NPN open-collector transistor | Normally open    |
|            | Top sensing   |  |                                                                                     | GX-F8AI               |                               | Normally closed  |
|            |               |                                                                                     |                                                                                     | GX-F8B                |                               | Normally open    |
|            |               |                                                                                     |                                                                                     | GX-F8BI               |                               | Normally closed  |
|            |               |                                                                                     |                                                                                     | GX-H8A                |                               | Normally open    |
|            |               |                                                                                     |                                                                                     | GX-H8AI               |                               | Normally closed  |
| PNP output | Front sensing |  |                                                                                     | GX-F8A-P              | PNP open-collector transistor | Normally open    |
|            | Top sensing   |  |                                                                                     | GX-F8AI-P             |                               | Normally closed  |
|            |               |                                                                                     |                                                                                     | GX-F8B-P              |                               | Normally open    |
|            |               |                                                                                     |                                                                                     | GX-F8BI-P             |                               | Normally closed  |
|            |               |                                                                                     |                                                                                     | GX-H8A-P              |                               | Normally open    |
|            |               |                                                                                     |                                                                                     | GX-H8AI-P             |                               | Normally closed  |

Notes: 1) The maximum operation distance stands for the maximum distance for which the sensor can detect the standard sensing object.

The stable sensing range stands for the sensing range for which the sensor can stably detect the standard sensing object even if there is an ambient temperature drift and/or supply voltage fluctuation.




2) "I" in the model No. indicates a different frequency type.

**ORDER GUIDE****GX-12 type**

| Type       |               | Appearance (mm in)                                                                | Sensing range (Note 1)                                                            | Model No.<br>(Note 2) | Output                        | Output operation |                 |
|------------|---------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------|-------------------------------|------------------|-----------------|
| NPN output | Front sensing |  |  | GX-F12A               | NPN open-collector transistor | Normally open    |                 |
|            | Top sensing   |  |                                                                                   | GX-F12AI              |                               | Normally closed  |                 |
|            |               |                                                                                   |                                                                                   | GX-F12B               |                               | Normally open    |                 |
|            |               |                                                                                   |                                                                                   | GX-F12BI              |                               |                  | Normally closed |
|            |               |                                                                                   |                                                                                   | GX-H12A               |                               |                  | Normally open   |
|            |               |                                                                                   |                                                                                   | GX-H12AI              |                               | Normally closed  |                 |
| PNP output | Front sensing |  |                                                                                   | GX-H12BI              | PNP open-collector transistor | Normally open    |                 |
|            | Top sensing   |  |                                                                                   | GX-F12A-P             |                               | Normally closed  |                 |
|            |               |                                                                                   |                                                                                   | GX-F12AI-P            |                               | Normally open    |                 |
|            |               |                                                                                   |                                                                                   | GX-F12B-P             |                               |                  | Normally closed |
|            |               |                                                                                   |                                                                                   | GX-F12BI-P            |                               |                  | Normally open   |
|            |               |                                                                                   |                                                                                   | GX-H12A-P             |                               | Normally closed  |                 |
|            |               |                                                                                   | GX-H12AI-P                                                                        | Normally open         |                               |                  |                 |
|            |               |                                                                                   | GX-H12B-P                                                                         | Normally closed       |                               |                  |                 |
|            |               |                                                                                   | GX-H12BI-P                                                                        | Normally closed       |                               |                  |                 |

Notes: 1) The maximum operation distance stands for the maximum distance for which the sensor can detect the standard sensing object.  
The stable sensing range stands for the sensing range for which the sensor can stably detect the standard sensing object even if there is an ambient temperature drift and/or supply voltage fluctuation.  
2) "I" in the model No. indicates a different frequency type.

**GX-15 type**

| Type       |               | Appearance (mm in)                                                                  | Sensing range (Note 1)                                                              | Model No.<br>(Note 2)         | Output                        | Output operation |
|------------|---------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------|-------------------------------|------------------|
| NPN output | Front sensing |  |  | GX-F15A                       | NPN open-collector transistor | Normally open    |
|            | Top sensing   |  |                                                                                     | GX-F15AI                      |                               | Normally closed  |
|            |               |                                                                                     |                                                                                     | GX-F15B                       |                               |                  |
|            |               |                                                                                     |                                                                                     | GX-F15BI                      |                               |                  |
|            |               |                                                                                     |                                                                                     | GX-H15A                       |                               |                  |
|            |               |                                                                                     |                                                                                     | GX-H15AI                      |                               |                  |
| GX-H15B    | Normally open |                                                                                     |                                                                                     |                               |                               |                  |
| GX-H15BI   |               | Normally closed                                                                     |                                                                                     |                               |                               |                  |
| GX-F15A-P  |               |                                                                                     |                                                                                     | PNP open-collector transistor | Normally open                 |                  |
| GX-F15AI-P |               |                                                                                     |                                                                                     |                               | Normally closed               |                  |
| GX-F15B-P  |               |                                                                                     |                                                                                     |                               |                               |                  |
| GX-F15BI-P |               |                                                                                     |                                                                                     |                               |                               |                  |
| GX-H15A-P  |               |                                                                                     |                                                                                     |                               |                               |                  |
| GX-H15AI-P |               |                                                                                     |                                                                                     |                               |                               |                  |
| GX-H15B-P  | Normally open |                                                                                     |                                                                                     |                               |                               |                  |
| GX-H15BI-P |               | Normally closed                                                                     |                                                                                     |                               |                               |                  |






Notes: 1) The maximum operation distance stands for the maximum distance for which the sensor can detect the standard sensing object.  
The stable sensing range stands for the sensing range for which the sensor can stably detect the standard sensing object even if there is an ambient temperature drift and/or supply voltage fluctuation.  
2) "I" in the model No. indicates a different frequency type.

FIBER  
SENSORSLASER  
SENSORSPHOTO-  
ELECTRIC  
SENSORSMICRO  
PHOTO-  
ELECTRIC  
SENSORSAREA  
SENSORSLIGHT  
CURTAINSPRESSURE /  
FLOW  
SENSORSINDUCTIVE  
PROXIMITY  
SENSORSPARTICULAR  
USE  
SENSORSSENSOR  
OPTIONSSIMPLE  
WIRE-  
SAVING  
UNITSWIRE-  
SAVING  
SYSTEMSMEASURE-  
MENT  
SENSORSSTATIC  
CONTROL  
DEVICES

ENDSCOPE

LASER  
MARKERSPLC /  
TERMINALSHUMAN  
MACHINE  
INTERFACESENERGY  
CONSUMPTION  
VISUALIZATION  
COMPONENTSFA  
COMPONENTSMACHINE  
VISION  
SYSTEMSUV  
CURING  
SYSTEMSSelection  
GuideAmplifier  
Built-inAmplifier-  
separated**GX-F/H****GXL****GL**GX-U/GX-FU/  
GX-N**GX**

**ORDER GUIDE****GX-15 (Long sensing range) type**

| Type       |               | Appearance (mm in)                                                                | Sensing range (Note 1)                                                                                                                                                                                        | Model No.<br>(Note 2) | Output                           | Output operation |
|------------|---------------|-----------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|----------------------------------|------------------|
| NPN output | Front sensing |  |  <p>Maximum<br/>operation distance</p> <p>8.0 mm 0.315 in</p> <p>(0 to 6.7 mm 0 to 0.264 in)</p> <p>Stable sensing range</p> | GX-FL15A              | NPN open-collector<br>transistor | Normally open    |
|            | Top sensing   |  |                                                                                                                                                                                                               | GX-FL15AI             |                                  | Normally closed  |
|            |               |                                                                                   |                                                                                                                                                                                                               | GX-FL15B              |                                  | Normally open    |
|            |               |                                                                                   |                                                                                                                                                                                                               | GX-FL15BI             |                                  | Normally closed  |
|            |               |                                                                                   |                                                                                                                                                                                                               | GX-HL15A              |                                  | Normally open    |
|            |               |                                                                                   |                                                                                                                                                                                                               | GX-HL15AI             |                                  | Normally closed  |
| PNP output | Front sensing |  |                                                                                                                                                                                                               | GX-FL15B              | PNP open-collector<br>transistor | Normally closed  |
|            | Top sensing   |  |                                                                                                                                                                                                               | GX-FL15A-P            |                                  | Normally open    |
|            |               |                                                                                   |                                                                                                                                                                                                               | GX-FL15AI-P           |                                  | Normally closed  |
|            |               |                                                                                   |                                                                                                                                                                                                               | GX-FL15B-P            |                                  | Normally open    |
|            |               |                                                                                   |                                                                                                                                                                                                               | GX-FL15BI-P           |                                  | Normally closed  |
|            |               |                                                                                   |                                                                                                                                                                                                               | GX-HL15A-P            |                                  | Normally open    |
|            |               |                                                                                   | GX-HL15AI-P                                                                                                                                                                                                   | Normally closed       |                                  |                  |
|            |               |                                                                                   | GX-HL15B-P                                                                                                                                                                                                    | Normally open         |                                  |                  |
|            |               |                                                                                   | GX-HL15BI-P                                                                                                                                                                                                   | Normally closed       |                                  |                  |

Notes: 1) The maximum operation distance stands for the maximum distance for which the sensor can detect the standard sensing object. The stable sensing range stands for the sensing range for which the sensor can stably detect the standard sensing object even if there is an ambient temperature drift and/or supply voltage fluctuation.  
2) "I" in the model No. indicates a different frequency type.

**5 m 16.404 ft cable length type, flexible cable type**


5 m 16.404 ft cable length type (standard: 1 m 3.281 ft) and flexible cable (excluding 5 m 16.404 ft cable length type) are available. However, long sensing range type is not available. When ordering 5 m 16.404 ft cable length type, suffix "-C5" to the model No. When ordering flexible cable type, suffix "-R" to the model No.  
(e.g.) 5 m 16.404 ft cable length type of GX-F15AI-P is "GX-F15AI-P-C5". Flexible cable type of GX-F15AI-P is "GX-F15AI-P-R".

**OPTIONS**

| Designation             | Model No.        | Description                                                                                                    |
|-------------------------|------------------|----------------------------------------------------------------------------------------------------------------|
| Sensor mounting bracket | <b>MS-GX6-1</b>  | Mounting bracket for <b>GX-6</b> type (recommended). Sensors can be mounted closely together for space-saving. |
|                         | <b>MS-GL6-1</b>  | Mounting brackets for <b>GX-6</b> type                                                                         |
|                         | <b>MS-GL6-2</b>  | Sensor mounting brackets for <b>GL-6</b> can be used. Interchange is possible.                                 |
|                         | <b>MS-GXL8-4</b> | Mounting bracket for <b>GX-8</b> type                                                                          |
|                         | <b>MS-GXL15</b>  | Mounting bracket for <b>GX-15</b> type                                                                         |
| Aluminum sheet          | <b>MS-A15F</b>   | For <b>GX-FL15□(-P)</b>                                                                                        |
|                         | <b>MS-A15H</b>   | For <b>GX-HL15□(-P)</b>                                                                                        |


**Sensor mounting bracket**

• MS-GX6-1




Nut is not attached.

• MS-GL6-1




Nut is not attached.

• MS-GL6-2




Nut is not attached.

• MS-GXL8-4



1pc. each of M3 (length: 12 mm 0.472 in) truss head screw, nut, spring washer and plain washer is attached.


• MS-GXL15



Nut is not attached.

**Aluminum sheet**

• MS-A15F  
• MS-A15H



**SPECIFICATIONS****GX-6 type**

| Item                             | Model No.<br>(Note 2)       | Type          | NPN output                                                                                                                                                                                                                                  |                 | PNP output                                                                                                                                                                                                                                     |                 |
|----------------------------------|-----------------------------|---------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------|
|                                  |                             | Front sensing | GX-F6A(I)                                                                                                                                                                                                                                   | GX-F6B(I)       | GX-F6A(I)-P                                                                                                                                                                                                                                    | GX-F6B(I)-P     |
|                                  |                             | Top sensing   | GX-H6A(I)                                                                                                                                                                                                                                   | GX-H6B(I)       | GX-H6A(I)-P                                                                                                                                                                                                                                    | GX-H6B(I)-P     |
| Max. operation distance (Note 3) |                             |               | 1.6 mm <b>0.063 in</b> ± 8 %                                                                                                                                                                                                                |                 |                                                                                                                                                                                                                                                |                 |
| Stable sensing range (Note 3)    |                             |               | 0 to 1.3 mm <b>0 to 0.051 in</b>                                                                                                                                                                                                            |                 |                                                                                                                                                                                                                                                |                 |
| Standard sensing object          |                             |               | Iron sheet 12 × 12 × t 1 mm <b>0.472 × 0.472 × t 0.039 in</b>                                                                                                                                                                               |                 |                                                                                                                                                                                                                                                |                 |
| Hysteresis                       |                             |               | 20 % or less of operation distance (with standard sensing object)                                                                                                                                                                           |                 |                                                                                                                                                                                                                                                |                 |
| Repeatability                    |                             |               | Along sensing axis, perpendicular to sensing axis: 0.04 mm <b>0.0016 in</b> or less                                                                                                                                                         |                 |                                                                                                                                                                                                                                                |                 |
| Supply voltage                   |                             |               | 12 to 24 V DC $\begin{smallmatrix} +10 \\ -15 \end{smallmatrix}$ % Ripple P-P 10 % or less                                                                                                                                                  |                 |                                                                                                                                                                                                                                                |                 |
| Current consumption              |                             |               | 15 mA or less                                                                                                                                                                                                                               |                 |                                                                                                                                                                                                                                                |                 |
| Output                           |                             |               | NPN open-collector transistor <ul style="list-style-type: none"><li>Maximum sink current: 100 mA</li><li>Applied voltage: 30 V DC or less (between output and 0 V)</li><li>Residual voltage: 2 V or less (at 100 mA sink current)</li></ul> |                 | PNP open-collector transistor <ul style="list-style-type: none"><li>Maximum source current: 100 mA</li><li>Applied voltage: 30 V DC or less (between output and +V)</li><li>Residual voltage: 2 V or less (at 100 mA source current)</li></ul> |                 |
|                                  |                             |               | Utilization category                                                                                                                                                                                                                        |                 |                                                                                                                                                                                                                                                |                 |
|                                  |                             |               | Output operation                                                                                                                                                                                                                            |                 |                                                                                                                                                                                                                                                |                 |
|                                  |                             |               | Normally closed                                                                                                                                                                                                                             | Normally closed | Normally closed                                                                                                                                                                                                                                | Normally closed |
| Max. response frequency          |                             |               | 400 Hz                                                                                                                                                                                                                                      |                 |                                                                                                                                                                                                                                                |                 |
| Operation indicator              |                             |               | Orange LED (lights up when the output is ON)                                                                                                                                                                                                |                 |                                                                                                                                                                                                                                                |                 |
| Environmental resistance         | Pollution degree            |               | 3 (Industrial environment)                                                                                                                                                                                                                  |                 |                                                                                                                                                                                                                                                |                 |
|                                  | Protection                  |               | IP68 (IEC), IP68g (JEM) (Note 4, 5)                                                                                                                                                                                                         |                 |                                                                                                                                                                                                                                                |                 |
|                                  | Ambient temperature         |               | −25 to +70 °C <b>−13 to +158 °F</b> , Storage: −40 to +85 °C <b>−40 to +185 °F</b>                                                                                                                                                          |                 |                                                                                                                                                                                                                                                |                 |
|                                  | Ambient humidity            |               | 35 to 85 % RH, Storage: 35 to 95 % RH                                                                                                                                                                                                       |                 |                                                                                                                                                                                                                                                |                 |
|                                  | EMC                         |               | EN 60947-5-2                                                                                                                                                                                                                                |                 |                                                                                                                                                                                                                                                |                 |
|                                  | Voltage withstandability    |               | 1,000 V AC for one min. between all supply terminals connected together and enclosure                                                                                                                                                       |                 |                                                                                                                                                                                                                                                |                 |
|                                  | Insulation resistance       |               | 50 MΩ, or more, with 500 V DC megger between all supply terminals connected together and enclosure                                                                                                                                          |                 |                                                                                                                                                                                                                                                |                 |
|                                  | Vibration resistance        |               | 10 to 500 Hz frequency, 3 mm <b>0.118 in</b> amplitude (Max. 20 G) in X, Y and Z directions for two hours each                                                                                                                              |                 |                                                                                                                                                                                                                                                |                 |
|                                  | Shock resistance            |               | 10,000 m/s <sup>2</sup> acceleration (1,000 G approx.) in X, Y and Z directions for three times each                                                                                                                                        |                 |                                                                                                                                                                                                                                                |                 |
| Sensing range variation          | Temperature characteristics |               | Over ambient temperature range −25 to +70 °C <b>−13 to +158 °F</b> : Within ± 8 % of sensing range at +23 °C <b>+73 °F</b>                                                                                                                  |                 |                                                                                                                                                                                                                                                |                 |
|                                  | Voltage characteristics     |               | Within ±2 % for $\begin{smallmatrix} +10 \\ -15 \end{smallmatrix}$ % fluctuation of the supply voltage                                                                                                                                      |                 |                                                                                                                                                                                                                                                |                 |
| Material                         |                             |               | Enclosure: PBT, Indicator part: Polyester                                                                                                                                                                                                   |                 |                                                                                                                                                                                                                                                |                 |
| Cable                            |                             |               | 0.15 mm <sup>2</sup> 3-core oil, heat and cold resistant cabtyre cable, 1 m <b>3.281 ft</b> long                                                                                                                                            |                 |                                                                                                                                                                                                                                                |                 |
| Cable extension                  |                             |               | Extension up to total 100 m <b>328.084 ft</b> is possible with 0.3 mm <sup>2</sup> , or more, cable.                                                                                                                                        |                 |                                                                                                                                                                                                                                                |                 |
| Net weight                       |                             |               | 15 g approx.                                                                                                                                                                                                                                |                 |                                                                                                                                                                                                                                                |                 |

Notes: 1) Where measurement conditions have not been specified precisely, the conditions used were an ambient temperature of +23 °C **+73 °F**.

2) "I" in the model No. indicates a different frequency type.

3) The maximum operation distance stands for the maximum distance for which the sensor can detect the standard sensing object.

The stable sensing range stands for the sensing range for which the sensor can stably detect the standard sensing object even if there is an ambient temperature drift and/or supply voltage fluctuation.

4) Panasonic Electric Works SUNX's IP68 test method

① Immerse at 0 m below 0 °C **+32 °F** water surface and leave for 30 min. Then, immerse at 0 m below +70 °C **+158 °F** water surface and leave for 30 min.

② Regard the heat shock test in ① as one cycle and perform 20 cycles.

③ Leave in water at a depth of 1 m **3.281 ft** in water for 500 hours.

④ After tests ① to ③, insulation resistance, voltage withstandability, current consumption, and sensing range must meet the standard values.

5) If using the sensor in an environment where cutting oil droplets splatter, the sensor may be deteriorated due to added substances in the oil.

FIBER  
SENSORSLASER  
SENSORSPHOTO-  
ELECTRIC  
SENSORSMICRO  
PHOTO-  
ELECTRIC  
SENSORSAREA  
SENSORSLIGHT  
CURTAINSPRESSURE /  
FLOW  
SENSORSINDUCTIVE  
PROXIMITY  
SENSORSPARTICULAR  
USE  
SENSORSSENSOR  
OPTIONSSIMPLE  
WIRE-SAVING  
UNITSWIRE-SAVING  
SYSTEMSMEASURE-  
MENT  
SENSORSSTATIC  
CONTROL  
DEVICES

ENDSCOPE

LASER  
MARKERSPLC /  
TERMINALSHUMAN  
MACHINE  
INTERFACESENERGY  
CONSUMPTION  
VISUALIZATION  
COMPONENTSFA  
COMPONENTSMACHINE  
VISION  
SYSTEMSUV  
CURING  
SYSTEMSSelection  
GuideAmplifier  
Built-inAmplifier-  
separated**GX-F/H****GXL****GL**GX-UGX-FU/  
GX-N**GX**

## SPECIFICATIONS

### GX-8 type

| Item                             | Model No.<br>(Note 2)       | Type                                                                                                                       | NPN output                                                                                           |               | PNP output                                                 |             |
|----------------------------------|-----------------------------|----------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------|---------------|------------------------------------------------------------|-------------|
|                                  |                             | Front sensing                                                                                                              | GX-F8A(I)                                                                                            | GX-F8B(I)     | GX-F8A(I)-P                                                | GX-F8B(I)-P |
|                                  |                             | Top sensing                                                                                                                | GX-H8A(I)                                                                                            | GX-H8B(I)     | GX-H8A(I)-P                                                | GX-H8B(I)-P |
| Max. operation distance (Note 3) |                             |                                                                                                                            | 2.5 mm <b>0.098 in</b> ± 8 %                                                                         |               |                                                            |             |
| Stable sensing range (Note 3)    |                             |                                                                                                                            | 0 to 2.1 mm <b>0 to 0.083 in</b>                                                                     |               |                                                            |             |
| Standard sensing object          |                             |                                                                                                                            | Iron sheet 15 × 15 × t 1 mm <b>0.591 × 0.591 × t 0.039 in</b>                                        |               |                                                            |             |
| Hysteresis                       |                             |                                                                                                                            | 20 % or less of operation distance (with standard sensing object)                                    |               |                                                            |             |
| Repeatability                    |                             |                                                                                                                            | Along sensing axis, perpendicular to sensing axis: 0.04 mm <b>0.0016 in</b> or less                  |               |                                                            |             |
| Supply voltage                   |                             |                                                                                                                            | 12 to 24 V DC <sup>+10</sup> <sub>-15</sub> %    Ripple P-P 10 % or less                             |               |                                                            |             |
| Current consumption              |                             |                                                                                                                            | 15 mA or less                                                                                        |               |                                                            |             |
| Output                           |                             |                                                                                                                            | NPN open-collector transistor                                                                        |               | PNP open-collector transistor                              |             |
|                                  |                             |                                                                                                                            | • Maximum sink current: 100 mA                                                                       |               | • Maximum source current: 100 mA                           |             |
|                                  |                             |                                                                                                                            | • Applied voltage: 30 V DC or less (between output and 0 V)                                          |               | • Applied voltage: 30 V DC or less (between output and +V) |             |
|                                  |                             |                                                                                                                            | • Residual voltage: 2 V or less (at 100 mA sink current)                                             |               | • Residual voltage: 2 V or less (at 100 mA source current) |             |
|                                  | Utilization category        | DC-12 or DC-13                                                                                                             |                                                                                                      |               |                                                            |             |
|                                  | Output operation            | Normally open                                                                                                              | Normally closed                                                                                      | Normally open | Normally closed                                            |             |
| Max. response frequency          |                             |                                                                                                                            | 500 Hz                                                                                               |               |                                                            |             |
| Operation indicator              |                             |                                                                                                                            | Orange LED (lights up when the output is ON)                                                         |               |                                                            |             |
| Environmental resistance         | Pollution degree            | 3 (Industrial environment)                                                                                                 |                                                                                                      |               |                                                            |             |
|                                  | Protection                  | IP68 (IEC), IP68g (JEM) (Note 4, 5)                                                                                        |                                                                                                      |               |                                                            |             |
|                                  | Ambient temperature         | −25 to +70 °C <b>−13 to +158 °F</b> , Storage: −40 to +85 °C <b>−40 to +185 °F</b>                                         |                                                                                                      |               |                                                            |             |
|                                  | Ambient humidity            | 35 to 85 % RH, Storage: 35 to 95 % RH                                                                                      |                                                                                                      |               |                                                            |             |
|                                  | EMC                         | EN 60947-5-2                                                                                                               |                                                                                                      |               |                                                            |             |
|                                  | Voltage withstandability    | 1,000 V AC for one min. between all supply terminals connected together and enclosure                                      |                                                                                                      |               |                                                            |             |
|                                  | Insulation resistance       | 50 MΩ, or more, with 500 V DC megger between all supply terminals connected together and enclosure                         |                                                                                                      |               |                                                            |             |
|                                  | Vibration resistance        | 10 to 500 Hz frequency, 3 mm <b>0.118 in</b> amplitude (Max. 20 G) in X, Y and Z directions for two hours each             |                                                                                                      |               |                                                            |             |
|                                  | Shock resistance            | 10,000 m/s <sup>2</sup> acceleration (1,000 G approx.) in X, Y and Z directions for three times each                       |                                                                                                      |               |                                                            |             |
| Sensing range variation          | Temperature characteristics | Over ambient temperature range −25 to +70 °C <b>−13 to +158 °F</b> : Within ± 8 % of sensing range at +23 °C <b>+73 °F</b> |                                                                                                      |               |                                                            |             |
|                                  | Voltage characteristics     | Within ±2 % for <sup>+10</sup> <sub>-15</sub> % fluctuation of the supply voltage                                          |                                                                                                      |               |                                                            |             |
| Material                         |                             |                                                                                                                            | Enclosure: PBT, Indicator part: Polyester                                                            |               |                                                            |             |
| Cable                            |                             |                                                                                                                            | 0.15 mm <sup>2</sup> 3-core oil, heat and cold resistant cabtyre cable, 1 m <b>3.281 ft</b> long     |               |                                                            |             |
| Cable extension                  |                             |                                                                                                                            | Extension up to total 100 m <b>328.084 ft</b> is possible with 0.3 mm <sup>2</sup> , or more, cable. |               |                                                            |             |
| Net weight                       |                             |                                                                                                                            | Front sensing type: 15 g approx., Top sensing type: 20 g approx..                                    |               |                                                            |             |

Notes: 1) Where measurement conditions have not been specified precisely, the conditions used were an ambient temperature of +23 °C **+73 °F**.

2) "I" in the model No. indicates a different frequency type.

3) The maximum operation distance stands for the maximum distance for which the sensor can detect the standard sensing object.

The stable sensing range stands for the sensing range for which the sensor can stably detect the standard sensing object even if there is an ambient temperature drift and/or supply voltage fluctuation.

4) Panasonic Electric Works SUNX's IP68 test method

① Immerse at 0 m below 0 °C **+32 °F** water surface and leave for 30 min. Then, immerse at 0 m below +70 °C **+158 °F** water surface and leave for 30 min.

② Regard the heat shock test in ① as one cycle and perform 20 cycles.

③ Leave in water at a depth of 1 m **3.281 ft** in water for 500 hours.

④ After tests ① to ③, insulation resistance, voltage withstandability, current consumption, and sensing ranges must meet the standard values.

5) If using the sensor in an environment where cutting oil droplets splatter, the sensor may deteriorate due to added substances in the oil.

GX-F/H

GXL

GL

GX-4/GX-FU/

GX-N

GX

**SPECIFICATIONS****GX-12 type**

| Item                             | Model No.<br>(Note 2)       | Type                                                                                                                                                                                                                                        | NPN output                                                                                              |                 | PNP output                                                                                                                                                                                                                                     |                 |
|----------------------------------|-----------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------|-----------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------|
|                                  |                             | Front sensing                                                                                                                                                                                                                               | GX-F12A(I)                                                                                              | GX-F12B(I)      | GX-F12A(I)-P                                                                                                                                                                                                                                   | GX-F12B(I)-P    |
|                                  |                             | Top sensing                                                                                                                                                                                                                                 | GX-H12A(I)                                                                                              | GX-H12B(I)      | GX-H12A(I)-P                                                                                                                                                                                                                                   | GX-H12B(I)-P    |
| Max. operation distance (Note 3) |                             |                                                                                                                                                                                                                                             | 4.0 mm 0.157 in ± 8 %                                                                                   |                 |                                                                                                                                                                                                                                                |                 |
| Stable sensing range (Note 3)    |                             |                                                                                                                                                                                                                                             | 0 to 3.3 mm 0 to 0.130 in                                                                               |                 |                                                                                                                                                                                                                                                |                 |
| Standard sensing object          |                             |                                                                                                                                                                                                                                             | Iron sheet 20 × 20 × t 1 mm 0.787 × 0.787 × t 0.039 in                                                  |                 |                                                                                                                                                                                                                                                |                 |
| Hysteresis                       |                             |                                                                                                                                                                                                                                             | 20 % or less of operation distance (with standard sensing object)                                       |                 |                                                                                                                                                                                                                                                |                 |
| Repeatability                    |                             |                                                                                                                                                                                                                                             | Along sensing axis, perpendicular to sensing axis: 0.04 mm 0.0016 in or less                            |                 |                                                                                                                                                                                                                                                |                 |
| Supply voltage                   |                             |                                                                                                                                                                                                                                             | 12 to 24 V DC <sup>+10</sup> <sub>-15</sub> % Ripple P-P 10 % or less                                   |                 |                                                                                                                                                                                                                                                |                 |
| Current consumption              |                             |                                                                                                                                                                                                                                             | 15 mA or less                                                                                           |                 |                                                                                                                                                                                                                                                |                 |
| Output                           |                             | NPN open-collector transistor <ul style="list-style-type: none"><li>Maximum sink current: 100 mA</li><li>Applied voltage: 30 V DC or less (between output and 0 V)</li><li>Residual voltage: 2 V or less (at 100 mA sink current)</li></ul> |                                                                                                         |                 | PNP open-collector transistor <ul style="list-style-type: none"><li>Maximum source current: 100 mA</li><li>Applied voltage: 30 V DC or less (between output and +V)</li><li>Residual voltage: 2 V or less (at 100 mA source current)</li></ul> |                 |
|                                  |                             | Utilization category                                                                                                                                                                                                                        | DC-12 or DC-13                                                                                          |                 |                                                                                                                                                                                                                                                |                 |
|                                  |                             | Output operation                                                                                                                                                                                                                            | Normally open                                                                                           | Normally closed | Normally open                                                                                                                                                                                                                                  | Normally closed |
| Max. response frequency          |                             |                                                                                                                                                                                                                                             | 500 Hz                                                                                                  |                 |                                                                                                                                                                                                                                                |                 |
| Operation indicator              |                             |                                                                                                                                                                                                                                             | Orange LED (lights up when the output is ON)                                                            |                 |                                                                                                                                                                                                                                                |                 |
| Environmental resistance         | Pollution degree            |                                                                                                                                                                                                                                             | 3 (Industrial environment)                                                                              |                 |                                                                                                                                                                                                                                                |                 |
|                                  | Protection                  |                                                                                                                                                                                                                                             | IP68 (IEC), IP68g (JEM) (Note 4, 5)                                                                     |                 |                                                                                                                                                                                                                                                |                 |
|                                  | Ambient temperature         |                                                                                                                                                                                                                                             | −25 to +70 °C −13 to +158 °F, Storage: −40 to +85 °C −40 to +185 °F                                     |                 |                                                                                                                                                                                                                                                |                 |
|                                  | Ambient humidity            |                                                                                                                                                                                                                                             | 35 to 85 % RH, Storage: 35 to 95 % RH                                                                   |                 |                                                                                                                                                                                                                                                |                 |
|                                  | EMC                         |                                                                                                                                                                                                                                             | EN 60947-5-2                                                                                            |                 |                                                                                                                                                                                                                                                |                 |
|                                  | Voltage withstandability    |                                                                                                                                                                                                                                             | 1,000 V AC for one min. between all supply terminals connected together and enclosure                   |                 |                                                                                                                                                                                                                                                |                 |
|                                  | Insulation resistance       |                                                                                                                                                                                                                                             | 50 MΩ, or more, with 500 V DC megger between all supply terminals connected together and enclosure      |                 |                                                                                                                                                                                                                                                |                 |
|                                  | Vibration resistance        |                                                                                                                                                                                                                                             | 10 to 500 Hz frequency, 3 mm 0.118 in amplitude (Max. 20 G) in X, Y and Z directions for two hours each |                 |                                                                                                                                                                                                                                                |                 |
|                                  | Shock resistance            |                                                                                                                                                                                                                                             | 10,000 m/s <sup>2</sup> acceleration (1,000 G approx.) in X, Y and Z directions for three times each    |                 |                                                                                                                                                                                                                                                |                 |
| Sensing range variation          | Temperature characteristics | Over ambient temperature range −25 to +70 °C −13 to +158 °F: Within ±8 % of sensing range at +23 °C +73 °F                                                                                                                                  |                                                                                                         |                 |                                                                                                                                                                                                                                                |                 |
|                                  | Voltage characteristics     | Within ±2 % for <sup>+10</sup> <sub>-15</sub> % fluctuation of the supply voltage                                                                                                                                                           |                                                                                                         |                 |                                                                                                                                                                                                                                                |                 |
| Material                         |                             |                                                                                                                                                                                                                                             | Enclosure: PBT, Indicator part: Polyester                                                               |                 |                                                                                                                                                                                                                                                |                 |
| Cable                            |                             |                                                                                                                                                                                                                                             | 0.15 mm <sup>2</sup> 3-core oil, heat and cold resistant cabtyre cable, 1 m 3.281 ft long               |                 |                                                                                                                                                                                                                                                |                 |
| Cable extension                  |                             |                                                                                                                                                                                                                                             | Extension up to total 100 m 328.084 ft is possible with 0.3 mm <sup>2</sup> , or more, cable.           |                 |                                                                                                                                                                                                                                                |                 |
| Net weight                       |                             |                                                                                                                                                                                                                                             | Front sensing type: 20 g approx., Top sensing type: 20 g approx..                                       |                 |                                                                                                                                                                                                                                                |                 |

Notes: 1) Where measurement conditions have not been specified precisely, the conditions used were an ambient temperature of +23 °C **+73 °F**.

2) " I " in the model No. indicates a different frequency type.

3) The maximum operation distance stands for the maximum distance for which the sensor can detect the standard sensing object.

The stable sensing range stands for the sensing range for which the sensor can stably detect the standard sensing object even if there is an ambient temperature drift and/or supply voltage fluctuation.

4) Panasonic Electric Works SUNX's IP68 test method

① Immerse at 0 m below 0 °C **+32 °F** water surface and leave for 30 min. Then, immerse at 0 m below +70 °C **+158 °F** water surface and leave for 30 min.

② Regard the heat shock test in ① as one cycle and perform 20 cycles.

③ Leave in water at a depth of 1 m **3.281 ft** in water for 500 hours.

④ After tests ① to ③, insulation resistance, voltage withstandability, current consumption, and sensing ranges must meet the standard values.

5) If using the sensor in an environment where cutting oil droplets splatter, the sensor may deteriorate due to added substances in the oil.

FIBER  
SENSORSLASER  
SENSORSPHOTO-  
ELECTRIC  
SENSORSMICRO  
PHOTO-  
ELECTRIC  
SENSORSAREA  
SENSORSLIGHT  
CURTAINSPRESSURE /  
FLOW  
SENSORSINDUCTIVE  
PROXIMITY  
SENSORSPARTICULAR  
USE  
SENSORSSENSOR  
OPTIONSSIMPLE  
WIRE-SAVING  
UNITSWIRE-SAVING  
SYSTEMSMEASURE-  
MENT  
SENSORSSTATIC  
CONTROL  
DEVICES

ENDSCOPE

LASER  
MARKERSPLC /  
TERMINALSHUMAN  
MACHINE  
INTERFACESENERGY  
CONSUMPTION  
VISUALIZATION  
COMPONENTSFA  
COMPONENTSMACHINE  
VISION  
SYSTEMSUV  
CURING  
SYSTEMSSelection  
GuideAmplifier  
Built-inAmplifier-  
separated**GX-F/H****GXL****GL**GX-UI/GX-FU/  
GX-N**GX**

## SPECIFICATIONS

## GX-15 type

| Model No.<br>(Note 2)            |                             | Type                                                                                                                                                                                       | NPN output                                                                                                  |                                                           |                 |                                                                                                                                                                                               | PNP output         |                                                           |                 |               |
|----------------------------------|-----------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------|-----------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|-----------------------------------------------------------|-----------------|---------------|
|                                  |                             |                                                                                                                                                                                            | Long sensing range                                                                                          |                                                           |                 |                                                                                                                                                                                               | Long sensing range |                                                           |                 |               |
|                                  |                             | Front sensing                                                                                                                                                                              | GX-F15A(I)                                                                                                  | GX-F15B(I)                                                | GX-FL15A(I)     | GX-FL15B(I)                                                                                                                                                                                   | GX-F15A(I)-P       | GX-F15B(I)-P                                              | GX-FL15A(I)-P   | GX-FL15B(I)-P |
| Item                             | Top sensing                 | GX-H15A(I)                                                                                                                                                                                 | GX-H15B(I)                                                                                                  | GX-HL15A(I)                                               | GX-HL15B(I)     | GX-H15A(I)-P                                                                                                                                                                                  | GX-H15B(I)-P       | GX-HL15A(I)-P                                             | GX-HL15B(I)-P   |               |
| Max. operation distance (Note 3) |                             | 5.0 mm 0.197 in ± 8 %                                                                                                                                                                      |                                                                                                             | 8.0 mm 0.315 in ± 8 % (Note 4)                            |                 | 5.0 mm 0.197 in ± 8 %                                                                                                                                                                         |                    | 8.0 mm 0.315 in ± 8 % (Note 4)                            |                 |               |
| Stable sensing range (Note 3)    |                             | 0 to 4.2 mm 0 to 0.165 in                                                                                                                                                                  |                                                                                                             | 0 to 6.7 mm 0 to 0.264 in (Note 4)                        |                 | 0 to 4.2 mm 0 to 0.165 in                                                                                                                                                                     |                    | 0 to 6.7 mm 0 to 0.264 in (Note 4)                        |                 |               |
| Standard sensing object          |                             | Iron sheet 20 × 20 × t 1 mm<br>0.7874 × 0.7874 × t 0.039 in                                                                                                                                |                                                                                                             | Iron sheet 30 × 30 × t 1 mm<br>1.181 × 1.181 × t 0.039 in |                 | Iron sheet 20 × 20 × t 1 mm<br>0.7874 × 0.7874 × t 0.039 in                                                                                                                                   |                    | Iron sheet 30 × 30 × t 1 mm<br>1.181 × 1.181 × t 0.039 in |                 |               |
| Hysteresis                       |                             | 20 % or less of operation distance (with standard sensing object)                                                                                                                          |                                                                                                             |                                                           |                 |                                                                                                                                                                                               |                    |                                                           |                 |               |
| Repeatability                    |                             | Along sensing axis, perpendicular to sensing axis: 0.04 mm 0.0016 in or less                                                                                                               |                                                                                                             |                                                           |                 |                                                                                                                                                                                               |                    |                                                           |                 |               |
| Supply voltage                   |                             | 12 to 24 V DC <sup>+10</sup> <sub>−15</sub> % Ripple P-P 10 % or less                                                                                                                      |                                                                                                             |                                                           |                 |                                                                                                                                                                                               |                    |                                                           |                 |               |
| Current consumption              |                             | 15 mA or less                                                                                                                                                                              |                                                                                                             |                                                           |                 |                                                                                                                                                                                               |                    |                                                           |                 |               |
| Output                           |                             | NPN open-collector transistor<br>• Maximum sink current: 100 mA<br>• Applied voltage: 30 V DC or less (between output and 0 V)<br>• Residual voltage: 2 V or less (at 100 mA sink current) |                                                                                                             |                                                           |                 | PNP open-collector transistor<br>• Maximum source current: 100 mA<br>• Applied voltage: 30 V DC or less (between output and +V)<br>• Residual voltage: 2 V or less (at 100 mA source current) |                    |                                                           |                 |               |
|                                  |                             | Utilization category                                                                                                                                                                       |                                                                                                             | DC-12 or DC-13                                            |                 |                                                                                                                                                                                               |                    |                                                           |                 |               |
| Output operation                 |                             | Normally open                                                                                                                                                                              | Normally closed                                                                                             | Normally open                                             | Normally closed | Normally open                                                                                                                                                                                 | Normally closed    | Normally open                                             | Normally closed |               |
| Max. response frequency          |                             | 250 Hz                                                                                                                                                                                     |                                                                                                             | 150 Hz (Note 5)                                           |                 | 250 Hz                                                                                                                                                                                        |                    | 150 Hz (Note 5)                                           |                 |               |
| Operation indicator              |                             | Orange LED (lights up when the output is ON)                                                                                                                                               |                                                                                                             |                                                           |                 |                                                                                                                                                                                               |                    |                                                           |                 |               |
| Environmental resistance         | Pollution degree            |                                                                                                                                                                                            | 3 (Industrial environment)                                                                                  |                                                           |                 |                                                                                                                                                                                               |                    |                                                           |                 |               |
|                                  | Protection                  |                                                                                                                                                                                            | IP68 (IEC), IP68g (JEM) (Note 6, 7)                                                                         |                                                           |                 |                                                                                                                                                                                               |                    |                                                           |                 |               |
|                                  | Ambient temperature         |                                                                                                                                                                                            | −25 to +70 °C −13 to +158 °F, Storage: −40 to +85 °C −40 to +185 °F                                         |                                                           |                 |                                                                                                                                                                                               |                    |                                                           |                 |               |
|                                  | Ambient humidity            |                                                                                                                                                                                            | 35 to 85 % RH, Storage: 35 to 95 % RH                                                                       |                                                           |                 |                                                                                                                                                                                               |                    |                                                           |                 |               |
|                                  | EMC                         |                                                                                                                                                                                            | EN 60947-5-2                                                                                                |                                                           |                 |                                                                                                                                                                                               |                    |                                                           |                 |               |
|                                  | Voltage withstandability    |                                                                                                                                                                                            | 1,000 V AC for one min. between all supply terminals connected together and enclosure                       |                                                           |                 |                                                                                                                                                                                               |                    |                                                           |                 |               |
|                                  | Insulation resistance       |                                                                                                                                                                                            | 50 MΩ, or more, with 500 V DC megger between all supply terminals connected together and enclosure          |                                                           |                 |                                                                                                                                                                                               |                    |                                                           |                 |               |
|                                  | Vibration resistance        |                                                                                                                                                                                            | 10 to 500 Hz frequency, 3 mm 0.118 in amplitude (Max. 20 G) in X, Y and Z directions for two hours each     |                                                           |                 |                                                                                                                                                                                               |                    |                                                           |                 |               |
|                                  | Shock resistance            |                                                                                                                                                                                            | 10,000 m/s <sup>2</sup> acceleration (1,000 G approx.) in X, Y and Z directions for three times each        |                                                           |                 |                                                                                                                                                                                               |                    |                                                           |                 |               |
| Sensing range variation          | Temperature characteristics |                                                                                                                                                                                            | Over ambient temperature range −25 to +70 °C −13 to +158 °F: Within ± 8 % of sensing range at +23 °C +73 °F |                                                           |                 |                                                                                                                                                                                               |                    |                                                           |                 |               |
|                                  | Voltage characteristics     |                                                                                                                                                                                            | Within ±2 % for <sup>+10</sup> <sub>−15</sub> % fluctuation of the supply voltage                           |                                                           |                 |                                                                                                                                                                                               |                    |                                                           |                 |               |
| Material                         |                             | Enclosure: PBT, Indicator part: Polyester                                                                                                                                                  |                                                                                                             |                                                           |                 |                                                                                                                                                                                               |                    |                                                           |                 |               |
| Cable                            |                             | 0.15 mm <sup>2</sup> 3-core oil, heat and cold resistant cabtyre cable, 1 m 3.281 ft long                                                                                                  |                                                                                                             |                                                           |                 |                                                                                                                                                                                               |                    |                                                           |                 |               |
| Cable extension                  |                             | Extension up to total 100 m 328.084 ft is possible with 0.3 mm <sup>2</sup> , or more, cable.                                                                                              |                                                                                                             |                                                           |                 |                                                                                                                                                                                               |                    |                                                           |                 |               |
| Net weight                       |                             | 20 g approx.                                                                                                                                                                               |                                                                                                             |                                                           |                 |                                                                                                                                                                                               |                    |                                                           |                 |               |

Notes: 1) Where measurement conditions have not been specified precisely, the conditions used were an ambient temperature of +23 °C **+73 °F**.

2) "I" in the model No. indicates a different frequency type.

3) The maximum operation distance stands for the maximum distance for which the sensor can detect the standard sensing object.

The stable sensing range stands for the sensing range for which the sensor can stably detect the standard sensing object even if there is an ambient temperature drift and/or supply voltage fluctuation.

4) This is the numerical value which the sensor mount onto an insulant plate. When mounted onto a steel or stainless steel plate, insert the optional aluminum sheet between the sensor and the plate.

5) This is the numerical value which the sensor mount onto an insulant plate. When mounted onto a metallic plate, max. response frequency will decrease.

6) Panasonic Electric Works SUNX's IP68 test method

① Immerse at 0 m below 0 °C **+32 °F** water surface and leave for 30 min. Then, immerse at 0 m below +70 °C **+158 °F** water surface and leave for 30 min.

② Regard the heat shock test in ① as one cycle and perform 20 cycles.

③ Leave in water at a depth of 1 m **3.281 ft** in water for 500 hours.

④ After tests ① to ③, insulation resistance, voltage withstandability, current consumption, and sensing range must meet the standard values.

7) If using the sensor in an environment where cutting oil droplets splatter, the sensor may be deteriorated due to added substances in the oil.

GX-F/H

GXL



GL

GX-4/GX-FU/



GX-N

GX





**SENSING CHARACTERISTICS (TYPICAL)****GX-6 type****Sensing field****Correlation between sensing object size and sensing range**



As the sensing object size becomes smaller than the standard size (iron sheet  $12 \times 12 \times t 1 \text{ mm}$   $0.472 \times 0.472 \times t 0.039 \text{ in}$ ), the sensing range shortens as shown in the left figure.

**GX-8 type****Sensing field****Correlation between sensing object size and sensing range**

As the sensing object size becomes smaller than the standard size (iron sheet  $15 \times 15 \times t 1 \text{ mm}$   $0.591 \times 0.591 \times t 0.039 \text{ in}$ ), the sensing range shortens as shown in the left figure.

**GX-12 type****Sensing field****Correlation between sensing object size and sensing range**

As the sensing object size becomes smaller than the standard size (iron sheet  $20 \times 20 \times t 1 \text{ mm}$   $0.787 \times 0.787 \times t 0.039 \text{ in}$ ), the sensing range shortens as shown in the left figure.

**GX-15 type****Sensing field****Correlation between sensing object size and sensing range**

As the sensing object size becomes smaller than the standard size (iron sheet  $20 \times 20 \times t 1 \text{ mm}$   $0.787 \times 0.787 \times t 0.039 \text{ in}$ ), the sensing range shortens as shown in the left figure.

FIBER  
SENSORSLASER  
SENSORSPHOTO-  
ELECTRIC  
SENSORSMICRO  
PHOTO-  
ELECTRIC  
SENSORSAREA  
SENSORSLIGHT  
CURTAINSPRESSURE /  
FLOW  
SENSORSINDUCTIVE  
PROXIMITY  
SENSORSPARTICULAR  
USE  
SENSORSSENSOR  
OPTIONSSIMPLE  
WIRE-SAVING  
UNITSWIRE-SAVING  
SYSTEMSMEASURE-  
MENT  
SENSORSSTATIC  
CONTROL  
DEVICES

ENDOSCOPE

LASER  
MARKERSPLC /  
TERMINALSHUMAN  
MACHINE  
INTERFACESENERGY  
CONSUMPTION  
VISUALIZATION  
COMPONENTSFA  
COMPONENTSMACHINE  
VISION  
SYSTEMSUV  
CURING  
SYSTEMSSelection  
GuideAmplifier  
Built-inAmplifier-  
separated



GX-F/H

GXL

GL

GX-4/GX-FU/  
GX-N

GX

**SENSING CHARACTERISTICS (TYPICAL)****GX-15 (Long sensing range) type****Sensing field****Correlation between sensing object size and sensing range**

As the sensing object size becomes smaller than the standard size (iron sheet 30 × 30 × t 1 mm 1.181 × 1.181 × t 0.039 in), the sensing range shortens as shown in the left figure.

**PRECAUTIONS FOR PROPER USE**

Refer to General precautions.




- Never use this product as a sensing device for personnel protection.
- In case of using sensing devices for personnel protection, use products which meet laws and standards, such as OSHA, ANSI or IEC etc., for personnel protection applicable in each region or country.

**Mounting****GX-6 type**


- Use the optional sensor mounting bracket when installing.

**<When using MS-GX6-1 (recommended)>**


- To mount the sensor with a nut, the mounting hole diameter should be  $\phi 3.4$  mm  $\phi 0.134$  in.
- ① Insert the sensor into the bracket as shown on the right.
  - ② Push the sensor until the bracket hook is lodged in the groove on the upper portion of the sensor.
  - ③ Fix the bracket in place with M3 pan head screw.

**<When using MS-GL6-1 / MS-GL6-2>**


- To mount the sensor with a nut, the mounting hole diameter should be  $\phi 3.4$  mm  $\phi 0.134$  in.

**GX-8 type**


- Make sure to use a M3 (length: 12 mm 0.472 in or more) truss head screw. The tightening torque should be 0.7 N·m or less. (Do not use a flat head screw or a pan head screw.)

**GX-12 type**


- The tightening torque should be 0.7 N·m or less.
- To mount the sensor with a nut, the mounting hole diameter should be  $\phi 3.4$  mm  $\phi 0.134$  in. Further, the hole in which the boss is inserted should be  $\phi 2.5$  mm  $\phi 0.098$  in and 3 mm 0.118 in, or more, deep.

**GX-15 type**

- The tightening torque should be 1 N·m or less.
- To mount the sensor with a nut, the mounting hole diameter should be  $\phi 3.4$  mm  $\phi 0.134$  in.



- When installing the long sensing range type on iron or stainless steel plate, put the optional aluminum sheet in between the sensor and the plate.



FIBER SENSORS

LASER SENSORS

PHOTO-ELECTRIC SENSORS

MICRO PHOTO-ELECTRIC SENSORS

AREA SENSORS

LIGHT CURTAINS

PRESSURE / FLOW SENSORS

INDUCTIVE PROXIMITY SENSORS

PARTICULAR USE SENSORS

SENSOR OPTIONS

SIMPLE WIRE-SAVING UNITS

WIRE-SAVING SYSTEMS

MEASURE-MENT SENSORS

STATIC CONTROL DEVICES

ENDOSCOPE

LASER MARKERS

PLC / TERMINALS

HUMAN MACHINE INTERFACES

ENERGY CONSUMPTION VISUALIZATION COMPONENTS

FA COMPONENTS

MACHINE VISION SYSTEMS

UV CURING SYSTEMS

SELECTION GUIDE

AMPLIFIER BUILT-IN

AMPLIFIER-SEPARATED

GX-F/H

GXL

GL

GX-UG/GX-FU/GX-N


GX

**PRECAUTIONS FOR PROPER USE**

Refer to General precautions.


**Influence of surrounding metal**

- When there is a metal near the sensor, keep the minimum separation distance specified below.

**Front sensing type**

|   | GX-F6 type                       | GX-F8 type             | GX-F12 type            | GX-F15 type           | GX-FL15 type                     |
|---|----------------------------------|------------------------|------------------------|-----------------------|----------------------------------|
| A | 6 mm <b>0.236 in</b><br>(Note 1) | 7.4 mm <b>0.291 in</b> | 7.1 mm <b>0.280 in</b> | 8 mm <b>0.315 in</b>  | 8 mm <b>0.315 in</b><br>(Note 2) |
| B | 8 mm <b>0.315 in</b>             | 8 mm <b>0.315 in</b>   | 20 mm <b>0.787 in</b>  | 20 mm <b>0.787 in</b> | 30 mm <b>1.181 in</b>            |
| C | 3 mm <b>0.118 in</b>             | 3 mm <b>0.118 in</b>   | 7 mm <b>0.276 in</b>   | 7 mm <b>0.276 in</b>  | 10 mm <b>0.394 in</b>            |

Notes: 1) When using **MS-GX6-1** (recommended mounting bracket), the distance "A" including the thickness of mounting bracket will be 6.4 mm **0.252 in**.  
 2) The **GXL-FL15** type should be mounted on an insulator. To mount it on an iron or stainless steel, use the enclosed aluminum sheet.

**Top sensing type**

|   | GX-H6 type            | GX-H8 type            | GX-H12 type           | GX-H15 type           | GX-HL15 type                    |
|---|-----------------------|-----------------------|-----------------------|-----------------------|---------------------------------|
| D | 3 mm <b>0.118 in</b>  | 4 mm <b>0.157 in</b>  | 7 mm <b>0.276 in</b>  | 6 mm <b>0.236 in</b>  | 12 mm <b>0.472 in</b>           |
| E | 10 mm <b>0.394 in</b> | 10 mm <b>0.394 in</b> | 20 mm <b>0.787 in</b> | 20 mm <b>0.787 in</b> | 30 mm <b>1.181 in</b>           |
| F | 2 mm <b>0.079 in</b>  | 3 mm <b>0.118 in</b>  | 3 mm <b>0.118 in</b>  | 0 mm <b>0 in</b>      | 10 mm <b>0.394 in</b><br>(Note) |
| G | 2 mm <b>0.079 in</b>  | 3 mm <b>0.118 in</b>  | 3 mm <b>0.118 in</b>  | 3 mm <b>0.118 in</b>  | 10 mm <b>0.394 in</b>           |



Note: When **GX-HL15** type is mounted on an insulator or seated on the enclosed aluminum sheet, the distance "F" can be zero.

**Mutual interference prevention**

- When two or more sensors are installed in parallel or face to face, keep the minimum separation distance specified below to avoid mutual interference.

|                                          | H                                             | J                      |
|------------------------------------------|-----------------------------------------------|------------------------|
| <b>GX-F6</b><br><b>GX-H6</b><br>type     | Between "I" type and non "I" type<br>(Note 2) | 0 mm <b>0.591 in</b>   |
|                                          | Between two "I" types or two non "I" types    | 13 mm <b>0.512 in</b>  |
| <b>GX-F8</b><br><b>GX-H8</b><br>type     | Between "I" type and non "I" type<br>(Note 2) | 0 mm <b>0.591 in</b>   |
|                                          | Between two "I" types or two non "I" types    | 20 mm <b>0.787 in</b>  |
| <b>GX-F12</b><br><b>GX-H12</b><br>type   | Between "I" type and non "I" type<br>(Note 2) | 0 mm <b>0.984 in</b>   |
|                                          | Between two "I" types or two non "I" types    | 25 mm <b>0.984 in</b>  |
| <b>GX-F15</b><br><b>GX-H15</b><br>type   | Between "I" type and non "I" type<br>(Note 2) | 0 mm <b>0.984 in</b>   |
|                                          | Between two "I" types or two non "I" types    | 45 mm <b>1.772 in</b>  |
| <b>GX-FL15</b><br><b>GX-HL15</b><br>type | Between "I" type and non "I" type<br>(Note 2) | 0 mm <b>0.984 in</b>   |
|                                          | Between two "I" types or two non "I" types    | 110 mm <b>3.059 in</b> |

Notes: 1) "I" in the model No. specifies the different frequency type.  
 2) Close mounting is possible for up to two sensors. When mounting three sensors or more at an equal spacing, align the model with "I" and the model without "I" alternately. The minimum value of dimension "H" should be as given below.  
**GX-F6 / H6 type:** 3.5mm **0.138 in**  
**GX-F8 / H8 type:** 6mm **0.236 in**  
**GX-F12 / H12 type:** 6.5mm **0.256 in**  
**GX-F15 / H15 type:** 15mm **0.591 in**  
**GX-FL15 / HL15 type:** 47.5mm **1.870 in**

**Front sensing****Top sensing****Sensing range**

- The sensing range is specified for the standard sensing object. With a non-ferrous metal, the sensing range is obtained by multiplying with the correction coefficient specified below. Further, the sensing range also changes if the sensing object is smaller than the standard sensing object or if the sensing object is plated.

**Correction coefficient**

| Model No.                | GX-F6<br>GX-H6<br>type | GX-F8<br>GX-H8<br>type | GX-F12<br>GX-H12<br>type | GX-F15<br>GX-H15<br>type | GX-FL15<br>type | GX-HL15<br>type |
|--------------------------|------------------------|------------------------|--------------------------|--------------------------|-----------------|-----------------|
| Metal                    |                        |                        |                          |                          |                 |                 |
| Iron                     | 1                      | 1                      | 1                        | 1                        | 1               | 1               |
| Stainless steel (SUS304) | 0.76 approx.           | 0.76 approx.           | 0.79 approx.             | 0.68 approx.             | 0.70 approx.    | 0.76 approx.    |
| Brass                    | 0.50 approx.           | 0.50 approx.           | 0.56 approx.             | 0.47 approx.             | 0.45 approx.    | 0.50 approx.    |
| Aluminum                 | 0.48 approx.           | 0.48 approx.           | 0.53 approx.             | 0.45 approx.             | 0.43 approx.    | 0.48 approx.    |

**Wiring**

- The output does not incorporate a short-circuit protection circuit. Do not connect it directly to a power supply or a capacitive load.

**Others**


- Do not use during the initial transient time (50 ms) after the power supply is switched on.

**DIMENSIONS (Unit: mm in)**


The CAD data in the dimensions can be downloaded from our website.

**GX-F6**□


Sensor

**GX-H6**□


Sensor

**GX-F8**□


Sensor

**GX-H8**□


Sensor

**GX-F12**□


Sensor

**GX-H12**□


Sensor

**GX-F(L)15**□

Sensor

**GX-H(L)15**□

Sensor





FIBER  
SENSORSLASER  
SENSORSPHOTO-  
ELECTRIC  
SENSORSMICRO  
PHOTO-  
ELECTRIC  
SENSORSAREA  
SENSORSLIGHT  
CURTAINSPRESSURE /  
FLOW  
SENSORSINDUCTIVE  
PROXIMITY  
SENSORSPARTICULAR  
USE  
SENSORSSENSOR  
OPTIONSSIMPLE  
WIRE-SAVING  
UNITSWIRE-SAVING  
SYSTEMSMEASURE-  
MENT  
SENSORSSTATIC  
CONTROL  
DEVICES

ENDOSCOPE

LASER  
MARKERSPLC/  
TERMINALSHUMAN  
MACHINE  
INTERFACESENERGY  
CONSUMPTION  
VISUALIZATION  
COMPONENTSFA  
COMPONENTSMACHINE  
VISION  
SYSTEMSUV  
CURING  
SYSTEMSSelection  
GuideAmplifier  
Built-inAmplifier-  
separated**GX-F/H****GXL****GL****GX-UGX-FU/  
GX-N****GX**


**DIMENSIONS (Unit: mm in)**

The CAD data in the dimensions can be downloaded from our website.


**MS-GX6-1** Sensor mounting bracket for GX-6 type (Optional)**MS-GL6-1** Sensor mounting bracket for GX-6 type (Optional)**MS-GL6-2** Sensor mounting bracket for GX-6 type (Optional)**MS-GXL8-4** Sensor mounting bracket for GX-8 type (Optional)

Material: Stainless steel (SUS304)

1 pc. each of M3 (length 12 mm 0.472 in) truss head screw, nut, spring washer and plain washer is attached.

**MS-GXL15** Sensor mounting bracket for GX-15 type (Optional)

Material: SPCC

**MS-A15F MS-A15H** Aluminum sheet (Optional)

FIBER SENSORS

LASER SENSORS

PHOTO-ELECTRIC SENSORS  
MICRO PHOTO-ELECTRIC SENSORS

AREA SENSORS

LIGHT CURTAINS

PRESSURE / FLOW SENSORS

INDUCTIVE PROXIMITY SENSORS

PARTICULAR USE SENSORS

SENSOR OPTIONS

SIMPLE WIRE-SAVING UNITS

WIRE-SAVING SYSTEMS

MEASUREMENT SENSORS

STATIC CONTROL DEVICES

ENDSCOPE

LASER MARKERS

PLC / TERMINALS

HUMAN MACHINE INTERFACES

ENERGY CONSUMPTION VISUALIZATION COMPONENTS

FA COMPONENTS

MACHINE VISION SYSTEMS

UV CURING SYSTEMS

Selection Guide

Amplifier Built-in

Amplifier-separated

GX-F/H

GXL

GL

GX-4/GX-FU/GX-N

GX

# MEMO