







LAY-OUT
P.C.B.- HOLE



PERFORMANCE CHARACTERISTICS

CURRENT RATING 1.5A AT 20°C (FULLY LOADED)
1 A AT 70°C (FULLY LOADED)

RATED VOLTAGE : 500 V AC (CONT /CONT)

OPERATING TEMPERATURE : -55°C TO 125°C

CONTACT RESISTANCE 20 MΩ MAX

INSERTION FORCE : 0.75N MAX/CONT

EXTRACTION FORCE : 0.15N MIN/CONT

INSULATION RESISTANCE : 10⁴ MΩ MIN

NOTES

1. LEAD FREE INDICATOR :LF=LEAD FREE
PERFORMANCE LEVEL INDICATOR
(REF DWG NO.BSC 201844.003)

2. THIS PRODUCT IS CSA APPROVED.
THIS PRODUCT IS UL RECOGNIZED.

3. FOR RECOMMENDED PTH DIMENSIONS REFER DRAWING :
BSA.201572.001

4. THIS PRODUCT (LF) MEETS EUROPEAN UNION DIRECTIVES AND
OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008

rev	ecn no	dr	date
A	CONVERSION REVISION 06	KN	14-09-01
B	DG05-0278	Kason	02-08-05
C	DG07-0362	Kason	05-09-07
D	DG08-0159	NZ	06-12-08
E	DG10-0110	NZ	05-30-10

Material			Spec ref				
Mat code			✓	tolerance 1DEC ± 0.2 1DEC 2DEC ± 0.1 2DEC ANGLES ± 1° HOEKEN	projection 	MM 	
Heat treat							
Plating/Finish							
Dr	W.Panis	10-01-95	size A4			Scale 2.000	
Eng			Product family MILLIPACS				
Chr			Model Name			ECN	
Appr			Model Revision			REL Level	
		title MPACS 5+2R RA RCP CONN TYPE CR			dwg no BSC201418023		Rev. E
Pro/E file		catalog no	HM2R20PA5100----		CUSTOMER DRAWING		sheet 1 of 1



title

MPACS 5+2R RA RCP
CONN TYPE CR

dwg no

BSC201418023

Rev.
E

Pro/E file

catalog no

HM2R20PA5100----

CUSTOMER DRAWING

sheet 1 of 1