


REV.	ECN NO.	REVISIONS	DRN.	CKD.	APP.	DATE
A	—	NEW RELEASE	TC			




RED/GREEN BI-COLOR LEDS
OPERATING CHARACTERISTICS AT T_A = 25 °C

SYMBOL	PARAMETER	COLOR	MIN	TYP	MAX	UNITS	TEST COND.
V _F	FORWARD VOLTAGE	RED GREEN		2.0 2.1	2.8 2.8	V	I _F = 20 mA
λ _{PEAK}	PEAK WAVELENGTH	RED GREEN		635 565		nm	
I _V	LUMINOUS INTENSITY	RED GREEN	2.5 3.7	4.7 10.0		mcd	I _F = 10 mA

ABSOLUTE MAXIMUM RATING AT 25 °C AMBIENT		UNITS
POWER DISSIPATION		100 mW
CONTINUOUS FORWARD CURRENT		30 mA
DERATE LINEARLY FROM 25°C		40 mA/°C
PEAK PULSE CURRENT, 10μs PULSE		120 mA
PEAK REVERSE VOLTAGE		5 V
LEAD SOLDERING TEMPERATURE, 6 SEC., 1/16" FROM BASE		260 °C
OPERATING TEMPERATURE		-55 TO +100 °C
STORAGE TEMPERATURE		-55 TO +100 °C

- NOTES:
- LEADS TO FIT INTO HOLES SPACED AS PER HOLE PATTERN.
 - PIN NUMBERS FOR REFERENCE ONLY, DESIGNATION NON-EXISTENT ON PART.
 - LED LEAD DIMENSIONS SHOWN ARE MEASURED AT HOUSING EXIT.
 - DIALIGHT PART NO. 553-0711-010



THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT. REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE FORBIDDEN WITHOUT THE WRITTEN CONSENT OF DIALIGHT.		
SCALE 5:1	DRAWING NUMBER	REV
ALL DIM'S IN: INCHES	C-16660	A
TOLERANCES: UNLESS OTHERWISE SPECIFIED	TITLE 3mm BI-LEVEL CBI, CATHODE LEFT	
FRACTIONS: ±1/64	MATERIAL	
DECIMALS (.XX): ±.01	Dialight	
DECIMALS (.XXX): ±.015	1913 ATLANTIC AVE. MANASQUAN, N.J. 08736	
ANGLES: ±3°	SHEET 1 OF 1	
FINISH:	FAMILY TABLE:	
FSCM 83330		