








11. NOTE DELETED.



	44 MM	13.97	11	16.36	24	5-147378-9
	88 MM	62.23	49	64.62	100	5-147378-8
	88 MM	49.53	39	51.92	80	5-147378-7
	72 MM	36.83	29	39.22	60	5-147378-6
	56 MM	30.48	24	32.87	50	5-147378-5
	56 MM	24.13	19	26.52	40	5-147378-4
	44 MM	17.78	14	20.17	30	5-147378-3
	32 MM	11.43	9	13.82	20	5-147378-2
	32 MM	5.08	4	7.47	10	5-147378-1
	44 MM	13.97	11	16.36	24	147378-9
	88 MM	62.23	49	64.62	100	147378-8
	88 MM	49.53	39	51.92	80	147378-7
	72 MM	36.83	29	39.22	60	147378-6
	56 MM	30.48	24	32.87	50	147378-5
	56 MM	24.13	19	26.52	40	147378-4
	44 MM	17.78	14	20.17	30	147378-3
FINISH	32 MM	11.43	9	13.82	20	147378-2
	32 MM	5.08	4	7.47	10	147378-1
	TAPE WIDTH	DIM_F	E SPACES	DIM_A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG NO. 05DEC2017		DATE		PERSON		NUMBER	
DRAWING NO. 05DEC2017		CHK K. SHRISHAI		DATE 05DEC2017				TE Connectivity	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		RECEPTACLE ASSEMBLY, VERTICAL, DOUBLE ROW			
mm				APPROVED J. OLSON 05DEC2017		SURFACE MOUNT, AMPMODU System 50			
				PRODUCT SPEC 108-1093					
				APPLICATION SPEC 114-25035					
MATERIAL FINISH		WEIGHT		SIZE		CAGE CODE		DRAWING NO	
SEE TABLE		-		A1		00779		C=147378	
		CUSTOMER DRAWING		SCALE 6:1		SHEET 1 OF 1		REV D	