

DeoxIT® L260Cp Mechanical & Electrical Grease

Part No.: L260Cp



Formulation: 92.5% DeoxIT® L260Np Lithium Grease
 7.0% Copper particles, -150 mesh (-105 µm)
 0.5% Deoxidizing agent

Container Size:

L260-C2C	100%	cartridge	50 g
L260-C1	100%	jar	28 g
L260-C8	100%	jar	226 g
L260-C35	100%	pail	16 Kg



Product Description:

Manufactured in semi-solid form for use as a combination cleaning, deoxidizing, protecting and lubricating preparation. Greases protect against oxidation (galvanic corrosion) and are free of mineral acids, sulphurs, alkalis and other noxious components aggressive to metals. DeoxIT® Greases improve performance of electrical contacts and mechanical components that require precise lubrication.

Particles: Copper. Use when you require particles (conductive) to assist in oxide and corrosion breakup and need good lubrication. Copper is conductive. Use in areas that two contacts will not touch and possibly short. Example: disconnect switches or large connectors and relays. Temperature range: -40 to +260°C.

Features/Benefits:

Safe on Plastics.

Lithium-based preparation.

Good lubrication, good abrasion, excellent wear resistance, excellent pressure resistance, excellent oxidation (galvanic corrosion) protection, high dripping-point characteristics.

USES:

Electrical:

Antenna connections, battery terminals, Buss bars, commutators, conductor rails, conductors, contactors, disconnects, drying & processing equipment, high amperage/high voltage applications, industrial electrical equipment (lifts, cranes, robotics, etc.), power tools, relays & switches (heavy duty, knife, step, rotary), etc.

Mechanical:

Bearings (all types), doors (closures), drives (chain/sprockets), hatch closures, O-rings and seals, linear motion systems, plugs (threaded holes), rack & pinion assemblies, screw devices (jacks, rails), slide bushings, sliding parts, tracks/guides/rails, threaded closures, worm gears, etc.

SPECS: (Base material)

	TYPE: M260	L260	TYPE: M260	L260
Flow Point, min.	-30°C	-30°C	Oil Type	Mineral Synthetic Blend
Viscosity @ 100°F, SUS763	785	Soap Type	None Lithium-12 Hydroxy
ASTM Dropping Point260°C	285°C	Soap %,	9.52
Specific Gravity @ 20°C	1.85	1.87	ASTM - Penetration280 295
Flash Point300°C	300°C	NLGI	2 2
¹ Lowest/Best Operating Temp. (general)	-30°C	-30°C	Deoxidizer	Yes Yes
¹ Highest Operating Temp. (continuous duty) ...	200°C	200°C	Oxidation Inhibitor	Yes Yes
Acid & Neutralization No. (mg KOH/g)	1.15	1.17	Corrosion Inhibitor	Yes Yes
Saponification No. (mg KOH/g)	2.79	2.81	TextureButtery Short Fiber
Electrical Conductivity (27°C) (10 ⁻¹² ohm ⁻¹ cm ⁻¹) ..	0.17	0.17	Color	Amber Amber
² Dielectric Constant E _r	2.751	3.236	¹ Temperatures are conservative values for reference only.	
(Tan δ (10 ⁻⁴)			² NOTE: All values are relative to an ambient temperature of 26 to 28°C (approx. 80°F). Dielectric strength value is a statistical average taken from 10 measurings. Voltage measurement taken with 0.5% accuracy. Tests conducted on base material only. Greases with particles may have different measurements.	
² Dielectric Strength E _d	(kV/cm) 54.6	45.9		
² Specific Insulation Resistance D (10 ¹² ohm-cm) 5.7	5.9			
	+ .50/- .03	+ .50/- .03		

Other Formulations:

L260Np	Lithuim formulation with no particles
L260Ap	Lithuim formulation with aluminum particles
L260Gp	Lithuim formulation with graphite particles
L260Qp	Lithuim formulation with quartz particles
L260GQp	Lithuim formulation with graphite and quartz particles
M260Np	Mineral based with no particles
M260Cp	Mineral based with copper particles

Shipping Information:

Hazardous: No

Other Information:

RoHS Compliant: YES
L260Cp MSDS Link:
Product Sheet: <http://store.caig.com/>

MANUFACTURER DISCLAIMER:

To the best of our knowledge, the information contained herein is accurate. However, neither CAIG Laboratories, Inc., or any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. All materials may present unknown hazards and should be used with caution. In particular, improper use of our products and their inappropriate combination with other products and substances may produce harmful results which cannot be anticipated. Final determination of the suitability of any material is the sole responsibility of the user. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that may exist. All service performed on internal parts and equipment should be provided by qualified technicians.

Contact Information:



North America

CAIG Laboratories, Inc.
12200 Thatcher Court
Poway, CA 92064 USA
Tel: (858) 486-8388
Fax: (858) 486-8398

Website www.caig.com
www.deoxit.com

General email info@caig.com

Technical email tech@caig.com