



W2E200 Series

Tubeaxial

225x225x80mm

- AC fans with external rotor shaded-pole motor. Impedance protected against overloading.
- Die-cast aluminum housing. Impeller of sheet-steel, directly welded onto rotor.
- Air exhaust over struts. Rotational direction CCW looking at rotor.
- Mounting from either face using four 4.5 mm holes.
- Electrical connection via 2 flat pin terminals 2.8 x 0.5 mm.
- Mounting from either face using 2 4.3 mm (.169") holes.
- UL, CSA, VDE approvals on some models, please contact application engineering.

| Part Number | CFM @ 0 | Curve | Volts | Hertz | Power (W) | Max Ambient Temp C | Wgt. (lbs) | Type Of Bearing | Features | |
|----------------|---------|-------|-------|-------|-----------|--------------------|------------|-----------------|----------|----------------|
| W2E200-HH82-01 | 500 | 1 | 115 | 50/60 | 60 | 56 | 75 | 4.38 | Ball | Terminal Block |
| W2E200-HH86-01 | 607 | 2 | 115 | 50/60 | 80 | 61 | 75 | 4.38 | Ball | Terminal Block |
| W2E200-HH64-05 | 500 | 1 | 230 | 50/60 | 60 | 56 | 75 | 4.38 | Ball | Terminal Block |
| W2E200-HH38-01 | 607 | 2 | 230 | 50/60 | 80 | 61 | 75 | 4.38 | Ball | Terminal Block |

Note: The W2E200-HH86-90 has the same performance and nominal data as the W2E200-HH86-01 with an additional 3 wires that exit the motor for the HES (speed monitoring feature).

