


Hose Clamp Type W2



- nach DIN 3017
- with hexagon screw SW7, incl. cross slot
- Material:
 - Case and strip = 1.4016
 - Screw = steel, zinc plated

Type	Range	s	b1	b2	h	L	Clamping-torque	Order Code
L146.2200	8 - 12 mm	0.7	9	11.5	7	22.4	2 + 0.5 Nm	429-3071
L146.2202	10 - 16 mm	0.7	9	11.5	7	22.4	2 + 0.5 Nm	429-3083
L146.2204	12 - 20 mm	0.7	9	11.5	7	22.4	3 + 0.5 Nm	429-3095
L146.2206	16 - 25 mm	0.7	9	11.5	7	22.4	3 + 0.5 Nm	429-3101
L146.2208	20 - 32 mm	0.7	9	11.5	7	22.4	3 + 0.5 Nm	429-3113
L146.2210	25 - 40 mm	0.7	9	11.5	7	22.4	3 + 0.5 Nm	429-3125
L146.2212	32 - 50 mm	0.7	9	11.5	7	22.4	3 + 0.5 Nm	429-3137
L146.2214	40 - 60 mm	0.7	9	11.5	7	22.4	3 + 0.5 Nm	429-3149

249976

Type	Order Code	Price Each
L146.2200	429-3071	
L146.2202	429-3083	
L146.2204	429-3095	
L146.2206	429-3101	
L146.2208	429-3113	
L146.2210	429-3125	
L146.2212	429-3137	
L146.2214	429-3149	

