




RoHS compliant

FEATURES

1. Now even more miniature.

The new thin type cuts 35% from the thickness of the previous short type. Device installing is now easier than ever.

2. Certain detection unaffected by the reflectance of the object

The sensor can provide stable detection that is not affected by the condition (color or material of the clothing) or parts (skin, hair, etc.) of the object being monitored. (Reflectance 18% to 90%). Excellent performance even when the detection surface is dirty.

3. Only connecting DC power supply for operating

Built-in oscillation circuit type obviates the hitherto existing need for start signal input.

4. Use in adjacent positions is possible

These sensors can be located in adjacent positions, because the timing of the external trigger signals can be adjusted so that the beam frequency of each adjacent sensor will not interfere with the other.

APPLICATIONS

1. Water-based product market

- Automatic lighting of wash basin units
- Toilets

2. Stores and financial institutions

- Automatic doors
- Automatic lighting
- Cash dispensing machines
- Automatic teller machines
- Visitor detecting sensors

3. Amusement market

- Automatic lighting for game display

4. Medical field

- Non-contact switch

ORDERING INFORMATION

AM

A: Thin short type MA Motion sensor

B: MA Motion sensor

Detection distance type (shape)

- 1: Short type
- 2: Middle type
- 3: Long type

Triggering function

- 1: External triggering type
- 4: Built-in oscillation circuit type (Internal trigger)

Classification by output method & mounting direction

- 0: NPN open collector/H type
- 5: NPN open collector/V type
- 6: PNP open collector/V type

Operating voltage

- 2: Free-ranging power type (6.5 to 27V DC)
- 9: 5V DC type (4.5 to 6.5V DC)

Rated detection distance

Part No.	02	03	04	05	06	07	08 (Middle type does not need 08)	09	10 (Short type does not need 10)	11	12	13	14	15	16	17	18	19	20 (Long type does not need 20)
Type	—	—	—	5	—	—	—	—	10	—	—	—	—	15	—	—	—	—	—
Thin short type	—	—	—	1.969	—	—	—	—	3.937	—	—	—	—	5.906	—	—	—	—	—
Short type	—	—	—	5	6	7	8	9	10	—	—	—	—	—	—	—	—	—	—
Middle type	20	30	40	50	60	70	80	—	—	—	—	—	—	—	—	—	—	—	—
	7.874	11.811	15.748	19.685	23.622	27.559	31.496	—	—	—	—	—	—	—	—	—	—	—	—
Long type	—	30	40	50	60	70	80	90	100	110	120	130	140	150	160	170	180	190	200
	—	11.811	15.748	19.685	23.622	27.559	31.496	35.433	39.37	43.307	47.244	51.181	55.118	59.055	62.992	66.929	70.866	74.803	78.74

MA Motion Sensor (AMA1, AMB1, 2, 3)

PRODUCT TYPES

1. Detection distance type (distance limited)

1) Thin short type (V type)

Operating voltage	Output method	Rated detection distance	Built-in oscillation circuit type	External triggering type
			Part No.	Part No.
4.5 to 5.5 V DC	NPN open collector output	5 cm 1.969 inch	AMA145905	AMA115905
		10 cm 3.937 inch	AMA1459	AMA1159
		15 cm 5.906 inch	AMA145915	AMA115915
	PNP open collector output	5 cm 1.969 inch	AMA146905	AMA116905
		10 cm 3.937 inch	AMA1469	AMA1169
		15 cm 5.906 inch	AMA146915	AMA116915

Standard packing: Carton: 20 pcs.; Case: 200 pcs.
Note: If you plan to use multiple sensors side-by-side, or you wish to keep the current consumption small, inquire for details about external trigger type, which is suitable for such applications.

2) Short type (H type)

Rated operating voltage	Rated detection distance	Mounting direction: H type	
		Short type	
		Built-in oscillation circuit type	External triggering type
		Part No.	Part No.
4.5 to 5.5 V DC	5 cm 1.969 inch	AMB140905	AMB110905
	6 cm 2.362 inch	AMB140906	AMB110906
	7 cm 2.756 inch	AMB140907	AMB110907
	8 cm 3.150 inch	AMB140908	AMB110908
	9 cm 3.543 inch	AMB140909	AMB110909
	10 cm 3.937 inch	AMB1409	AMB1109
5.5 to 27 V DC	5 cm 1.969 inch	AMB140205	AMB110205
	6 cm 2.362 inch	AMB140206	AMB110206
	7 cm 2.756 inch	AMB140207	AMB110207
	8 cm 3.150 inch	AMB140208	AMB110208
	9 cm 3.543 inch	AMB140209	AMB110209
	10 cm 3.937 inch	AMB1402	AMB1102

Standard packing: Carton: 20 pcs.; Case: 200 pcs.
Note: If you plan to use multiple sensors side-by-side, or you wish to keep the current consumption small, inquire for details about external trigger type, which is suitable for such applications.

3) Middle type (H type)

Rated operating voltage	Rated detection distance	Mounting direction: H type	
		Middle type	
		Built-in oscillation circuit type	External triggering type
		Part No.	Part No.
4.5 to 5.5 V DC	20 cm 7.874 inch	AMB240902	AMB210902
	30 cm 11.811 inch	AMB240903	AMB210903
	40 cm 15.748 inch	AMB240904	AMB210904
	50 cm 19.685 inch	AMB240905	AMB210905
	60 cm 23.622 inch	AMB240906	AMB210906
	70 cm 27.559 inch	AMB240907	AMB210907
	80 cm 31.496 inch	AMB2409	AMB2109
5.5 to 27 V DC	20 cm 7.874 inch	AMB240202	AMB210202
	30 cm 11.811 inch	AMB240203	AMB210203
	40 cm 15.748 inch	AMB240204	AMB210204
	50 cm 19.685 inch	AMB240205	AMB210205
	60 cm 23.622 inch	AMB240206	AMB210206
	70 cm 27.559 inch	AMB240207	AMB210207
	80 cm 31.496 inch	AMB2402	AMB2102

Standard packing: Carton: 20 pcs.; Case: 200 pcs.
Note: If you plan to use multiple sensors side-by-side, or you wish to keep the current consumption small, inquire for details about external trigger type, which is suitable for such applications.

MA Motion Sensor (AMA1, AMB1, 2, 3)

4) Long type

Rated operating voltage	Rated detection distance	Mounting direction: H type		Mounting direction: V type		
		Long type				
		Built-in oscillation circuit type	External triggering type	Built-in oscillation circuit type	External triggering type	
		Part No.	Part No.	Part No.	Part No.	
4.5 to 5.5 V DC	30 cm 11.811 inch	AMB340903	AMB310903	AMB345903	AMB315903	
	40 cm 15.748 inch	AMB340904	AMB310904	AMB345904	AMB315904	
	50 cm 19.685 inch	AMB340905	AMB310905	AMB345905	AMB315905	
	60 cm 23.622 inch	AMB340906	AMB310906	AMB345906	AMB315906	
	70 cm 27.559 inch	AMB340907	AMB310907	AMB345907	AMB315907	
	80 cm 31.496 inch	AMB340908	AMB310908	AMB345908	AMB315908	
	90 cm 35.433 inch	AMB340909	AMB310909	AMB345909	AMB315909	
	100 cm 39.370 inch	AMB340910	AMB310910	AMB345910	AMB315910	
	110 cm 43.307 inch	AMB340911	AMB310911	AMB345911	AMB315911	
	120 cm 47.244 inch	AMB340912	AMB310912	AMB345912	AMB315912	
	130 cm 51.181 inch	AMB340913	AMB310913	AMB345913	AMB315913	
	140 cm 55.118 inch	AMB340914	AMB310914	AMB345914	AMB315914	
	150 cm 59.055 inch	AMB340915	AMB310915	AMB345915	AMB315915	
	160 cm 62.992 inch	AMB340916	AMB310916	AMB345916	AMB315916	
	170 cm 66.929 inch	AMB340917	AMB310917	AMB345917	AMB315917	
	180 cm 70.866 inch	AMB340918	AMB310918	AMB345918	AMB315918	
	190 cm 74.803 inch	AMB340919	AMB310919	AMB345919	AMB315919	
	200 cm 78.740 inch	AMB3409	AMB3109	AMB3459	AMB3159	
	5.5 to 27 V DC	30 cm 11.811 inch	AMB340203	AMB310203	AMB345203	AMB315203
		40 cm 15.748 inch	AMB340204	AMB310204	AMB345204	AMB315204
50 cm 19.685 inch		AMB340205	AMB310205	AMB345205	AMB315205	
60 cm 23.622 inch		AMB340206	AMB310206	AMB345206	AMB315206	
70 cm 27.559 inch		AMB340207	AMB310207	AMB345207	AMB315207	
80 cm 31.496 inch		AMB340208	AMB310208	AMB345208	AMB315208	
90 cm 35.433 inch		AMB340209	AMB310209	AMB345209	AMB315209	
100 cm 39.370 inch		AMB340210	AMB310210	AMB345210	AMB315210	
110 cm 43.307 inch		AMB340211	AMB310211	AMB345211	AMB315211	
120 cm 47.244 inch		AMB340212	AMB310212	AMB345212	AMB315212	
130 cm 51.181 inch		AMB340213	AMB310213	AMB345213	AMB315213	
140 cm 55.118 inch		AMB340214	AMB310214	AMB345214	AMB315214	
150 cm 59.055 inch		AMB340215	AMB310215	AMB345215	AMB315215	
160 cm 62.992 inch		AMB340216	AMB310216	AMB345216	AMB315216	
170 cm 66.929 inch		AMB340217	AMB310217	AMB345217	AMB315217	
180 cm 70.866 inch		AMB340218	AMB310218	AMB345218	AMB315218	
190 cm 74.803 inch		AMB340219	AMB310219	AMB345219	AMB315219	
200 cm 78.740 inch		AMB3402	AMB3102	AMB3452	AMB3152	

Standard packing: Carton: 20 pcs.; Case: 200 pcs.

Note: If you plan to use multiple sensors side-by-side, or you wish to keep the current consumption small, inquire for details about external trigger type, which is suitable for such applications.

RATING

1. Detection performance

1) Thin short type (Measuring conditions: ambient temp.: 25°C 77°F; operating voltage: 5 V DC)

Items		Thin short type			Measured conditions	
		5 cm 1.969 inch	10 cm 3.937 inch	15 cm 3.937 inch		
Rated detection distance	Minimum	45 mm 1.772 inch	90 mm 3.543 inch	135 mm 5.315 inch	with a standard reflection board*1	
	Typical	50 mm 1.969 inch	100 mm 3.937 inch	150 mm 5.906 inch		
	Maximum	55 mm 2.165 inch	110 mm 4.331 inch	165 mm 6.496 inch		
Measuring tolerance		Typical	10%	25%	35%	Reflection rate: 90 to 18%
Usable ambient brightness (Resistance to ambient light)*2	Brightness of sensor surface	Maximum	30,000 lx			See the drawing (Fig. 1) on the next page.
	Brightness of reflection surface	Maximum	24,000 lx			

Notes: *1. Ambient brightness: 500 lx

*2. Install so that light from direct light sources does not enter the sensor (within 30° of the sensor light beam).

Indicates brightness detectible enough for sensor operation.

MA Motion Sensor (AMA1, AMB1, 2, 3)

2) Short type (Measuring conditions: ambient temp.: 25°C 77°F; operating voltage: 5 V DC type 5V, Free-ranging power type 24V DC)

Items			Short type*1						Measured conditions
			5 cm 1.969 inch	6 cm 2.362 inch	7 cm 2.756 inch	8 cm 3.150 inch	9 cm 3.543 inch	10 cm 3.937 inch	
Rated detection distance	Minimum	45 mm	54 mm	63 mm	72 mm	81 mm	90 mm	with a standard reflection board	
	Typical	1.772 inch	2.126 inch	2.480 inch	2.835 inch	3.189 inch	3.543 inch		
		50 mm	60 mm	70 mm	80 mm	90 mm	100 mm		
		1.969 inch	2.362 inch	2.756 inch	3.150 inch	3.543 inch	3.937 inch		
Maximum	55 mm	66 mm	77 mm	88 mm	99 mm	110 mm			
	2.165 inch	2.598 inch	3.031 inch	3.465 inch	3.898 inch	4.331 inch			
Measuring tolerance		Typical	10%		15%	20%		25%	Reflection rate: 90 to 18%
Usable ambient brightness (Resistance to ambient light)*2	Brightness of sensor surface	Maximum	30,000 lx						See the drawing (Fig. 1) on the next page.
	Brightness of reflection surface	Maximum	24,000 lx						

Notes: *1. After receipt of order, average rated detection distance to 15 cm 5.906 inch is possible. Please inquire.

*2. Install so that light from direct light sources does not enter the sensor (within 30° of the sensor light beam).

3) Middle type (Measuring conditions: ambient temp.: 25°C 77°F; operating voltage: 5 V DC type 5V, Free-ranging power type 24V DC)

Items			Middle type*1						Measured conditions
			20 cm 7.874 inch	30 cm 11.811 inch	40 cm 15.748 inch	50 cm 19.685 inch	60 cm 23.622 inch	70 cm 27.559 inch	
Rated detection distance	Minimum	190 mm	285 mm	380 mm	475 mm	570 mm	665 mm	760 mm	with a standard reflection board
	Typical	7.480 inch	11.220 inch	14.961 inch	18.701 inch	22.441 inch	26.181 inch	29.921 inch	
		200 mm	300 mm	400 mm	500 mm	600 mm	700 mm	800 mm	
		7.874 inch	11.811 inch	15.748 inch	19.685 inch	23.622 inch	27.559 inch	31.496 inch	
Maximum	210 mm	315 mm	420 mm	525 mm	630 mm	735 mm	840 mm		
	8.268 inch	12.402 inch	16.535 inch	20.669 inch	24.803 inch	28.937 inch	33.071 inch		
Measuring tolerance		Typical	3%			5%		10%	Reflection rate: 90 to 18%
Usable ambient brightness (Resistance to ambient light)*2	Brightness of sensor surface	Maximum	30,000 lx						See the drawing (Fig. 1) on the next page.
	Brightness of reflection surface	Maximum	24,000 lx						

Notes: *1. After receipt of order, average rated detection distance to 110 cm 43.307 inch is possible. Please inquire.

*2. Install so that light from direct light sources does not enter the sensor (within 30° of the sensor light beam).

4) Long type (Measuring conditions: ambient temp.: 25°C 77°F; operating voltage: 5 V DC type 5V, Free-ranging power type 24V DC)

Items			Long type								Measured conditions
			30 cm 11.811 inch	40 cm 15.748 inch	50 cm 19.685 inch	60 cm 23.622 inch	70 cm 27.559 inch	80 cm 31.496 inch	90 cm 35.433 inch	100 cm 39.37 inch	
Rated detection distance	Minimum	285 mm 11.220 inch	380 mm 14.961 inch	475 mm 18.701 inch	570 mm 22.441 inch	665 mm 26.181 inch	760 mm 29.921 inch	855 mm 33.661 inch	950 mm 37.402 inch	1045 mm 41.142 inch	with a standard reflection board
	Typical	300 mm	400 mm	500 mm	600 mm	700 mm	800 mm	900 mm	1000 mm	1100 mm	
	Maximum	11.811 inch 315 mm	15.748 inch 420 mm	19.685 inch 525 mm	23.622 inch 630 mm	27.559 inch 735 mm	31.496 inch 840 mm	34.433 inch 945 mm	39.37 inch 1050 mm	43.307 inch 1155 mm	
		12.402 inch	16.535 inch	20.669 inch	24.803 inch	28.937 inch	33.071 inch	37.205 inch	41.339 inch	45.472 inch	
Measuring tolerance		Typical	3%					5%			Reflection rate: 90 to 18%
Usable ambient brightness (Resistance to ambient light)*	Brightness of sensor surface	Maximum	30,000 lx								See the drawing (Fig. 1) on the next page.
	Brightness of reflection surface	Maximum	24,000 lx								

Items			Long type								Measured conditions
			120 cm 47.244 inch	130 cm 51.181 inch	140 cm 55.118 inch	150 cm 59.055 inch	160 cm 62.992 inch	170 cm 66.929 inch	180 cm 70.866 inch	190 cm 74.803 inch	
Rated detection distance	Minimum	1140 mm 44.882 inch	1235 mm 48.622 inch	1330 mm 52.362 inch	1425 mm 56.102 inch	1520 mm 59.842 inch	1615 mm 63.583 inch	1710 mm 67.323 inch	1805 mm 71.063 inch	1900 mm 74.803 inch	with a standard reflection board
	Typical	1200 mm	1300 mm	1400 mm	1500 mm	1600 mm	1700 mm	1800 mm	1900 mm	2000 mm	
	Maximum	47.244 inch 1260 mm	51.181 inch 1365 mm	55.118 inch 1470 mm	59.055 inch 1575 mm	62.992 inch 1680 mm	66.929 inch 1785 mm	70.866 inch 1890 mm	74.803 inch 1995 mm	78.74 inch 2100 mm	
		49.606 inch	53.740 inch	57.874 inch	62.008 inch	66.142 inch	70.275 inch	74.409 inch	78.543 inch	82.677 inch	
Measuring tolerance		Typical	5%	10%			15%				Reflection rate: 90 to 18%
Usable ambient brightness (Resistance to ambient light)*	Brightness of sensor surface	Maximum	30,000 lx								See the drawing (Fig. 1) on the next page.
	Brightness of reflection surface	Maximum	24,000 lx								

Note: * Install so that light from direct light sources does not enter the sensor (within 30° of the sensor light beam).

MA Motion Sensor (AMA1, AMB1, 2, 3)


- For thin short type:
Standard reflection board: 150 mm 5.906 inch square area,
90% reflection rate.
- For short type:
Standard reflection board: 100 mm 3.937 inch square area,
90% reflection rate.
- For middle type:
Standard reflection board: 200 mm 7.874 inch square area,
90% reflection rate.
- For long type:
Standard reflection board: 500 mm 19.685 inch square area,
90% reflection rate.

Notes: 1. Detecting an object within the maximum preset detection distance.

$$2. \text{Distance deviation} = \frac{a-b}{a} \times 100 (\%)$$


(a: detection distance of detection target with reflectance of 90%.
b: detection distance of standard detection target with reflectance of 18%.)

<Fig. 1>
[Brightness of sensor surface]



Note: Light from direct light sources (sunlight, strobe light, inverter illumination, reflected light from glass or mirrors etc.) that enters the sensor from within the prohibited range can cause the sensor to operate erroneously.

[Brightness of reflection surface]



2. Absolute maximum rating (Measuring condition: ambient temp.: 25°C 77°F)

Items	Type	Absolute maximum rating			
		Built-in oscillation circuit type		External triggering type	
		5 V DC type	Free-ranging power type	5 V DC type	Free-ranging power type
Power supply voltage		-0.3 to 6 V DC	-0.3 to 30 V DC	-0.3 to 6 V DC	-0.3 to 30 V DC
Output dielectric strength		30 V		30 V	
Output flow current		100 mA		10 mA*	
Usable ambient temperature		-25 to +75°C +5 to +131°F (No freezing)		-25 to +75°C +5 to +131°F (No freezing)	
Storage temperature		-30 to +85°C -4 to +176°F		-30 to +85°C -4 to +176°F	

Note: * Thin short type is only: 100 mA

3. Electrical characteristics

(Measuring conditions: ambient temp.: 25°C 77°F; operating voltage: 5 V DC type =5V DC, free-ranging power type =24V DC)

1) Built-in oscillation circuit type

Items			Symbol	Thin short type*		Short type	Middle type	Long type	Measured conditions
				NPN output type	PNP output type				
Rated operating voltage		Minimum	Vdd	5V DC type: 4.5V/Free-ranging power type: 5.5V					
		Typical		—					
		Maximum		5V DC type: 5.5V/Free-ranging power type: 27V					
Average current consumption (Iout = 0 mA)	No detection	Minimum	It	—					
		Typical		4.5mA		5V DC type: 4.5mA/Free-ranging power type: 5.6mA			
		Maximum		6.2mA		5V DC type: 6.2mA/Free-ranging power type: 7.8mA			
	Detection	Minimum	It	—					
		Typical		7.0mA	11.0mA	5V DC type: 7.0mA/Free-ranging power type: 9.1mA			
		Maximum		11.2mA	15.2mA	5V DC type: 11.2mA/Free-ranging power type: 14.2mA			
Measuring cycle		Minimum	T	8ms/cycle					
Output characteristics	Remain voltage	Maximum	Vr	1 V DC	1.2 V DC	1 V DC			It = 100 mA
	Leakage current	Maximum	II	5μA		3μA			V = 30V

Note: * The thin short type is only available for 5V DC.


MA Motion Sensor (AMA1, AMB1, 2, 3)

2) External triggering type (trigger conditions: trigger pulse width = 20μs and trigger synchronization = 5ms)


Items			Symbol	Thin short type Note 1		Short type	Middle type	Long type	Measured conditions	
				NPN output type	PNP output type					
Rated operating voltage			Minimum	Vdd	5V DC type: 4.5V/Free-ranging type: 5.5V					
			Typical		—					
			Maximum		5V DC type: 5.5V/Free-ranging type: 27V					
Average current consumption	Without trigger input	Output OFF	Minimum	Ib	—					Note 2: *b
			Typical		0.1m		5V DC type: 0.1mA/Free-ranging type: 1.0mA			
			Maximum		0.3m		5V DC type: 0.3mA/Free-ranging type: 1.8mA			
		Output ON	Minimum	Id	—					Note 2: *d
			Typical		2.6mA	6.7mA	5V DC type: 0.5mA/Free-ranging type: 1.4mA			
			Maximum		6.6mA	9.6mA	5V DC type: 3.4mA/Free-ranging type: 4.5mA			
	With trigger input	Output OFF	Minimum	Ia	—					Note 2: *a
			Typical		2.2mA		5V DC type: 2.2mA/Free-ranging type: 3.1mA			
			Maximum		6.2mA		5V DC type: 6.2mA/Free-ranging type: 7.2mA			
		Output ON	Minimum	Ic	—					Note 2: *c
			Typical		4.2mA	6.2mA	5V DC type: 2.4mA/Free-ranging type: 3.3mA			
			Maximum		8.2mA	12.5mA	5V DC type: 8.2mA/Free-ranging type: 9.3mA			
Measuring cycle (Trigger interval)			Minimum	Tt	5ms/cycle					
External trigger	Pulse width	Minimum	Tw	20μs					Half off the distance period	
		Maximum		1/2Tt						
	Level	Maximum	V _{TL}	0.8V					Note 3	
		Minimum	V _{TH}	3V						
Response performance: time from trigger pulse fall to detection output			Maximum	Tr	5ms					
Output characteristics	Remain voltage	Maximum	Vr	1 V DC	1.2 V DC	1 V			I = 10 mA	
	Leakage current	Maximum	II	5μA		3μA			V = 30 mA	

Notes: 1. The thin short type is only available for 5V DC.
2. The ratio between the 4 operating modes (*a to *d) depends on the external trigger period and detector time, and the current consumption corresponds with this varying ratio.

4. The output transistor is open collector.
The output transistor is turned ON by the sensor detection status and turned OFF by its non-detection status.





3. A high level is established in the open state due to pull-up by the internal circuit. (Refer to the connector wiring diagram.)





TIMING CHART

1. Built-in oscillation circuit type



Notes: 1. Circuit stability time : Max. 12 ms
2. During the time taken for the circuit to stabilize after the power is turned on, the ON/OFF status of the output transistor is not determined by whether the sensor is in the detection status or non-detection status.

2. External triggering type




Note: The sensor recognizes at the $V_{TH} \rightarrow V_{TL}$ edge of an external trigger that the external trigger has been input.

- Notes: 1. Circuit stability time: Max. 12 ms
2. During the time taken for the circuit to stabilize after the power is turned on, the ON/OFF status of the output transistor is not determined by whether the sensor is in the detection status or non-detection status.

HOW TO USE

1. Wiring diagram of connector



- Notes: 1. The output transistor has an open collector structure.
• Detection status: Output transistor ON (connected to GND)
• Non-detection status: Output transistor OFF (open state)
2. The status of the external trigger input is as follows:
• Open at the high level
• GND (less than 0.8V) at the low level
Under no circumstances must a high-level voltage be applied.
3. To maintain the power supply superimposed noise performance, be certain to connect a capacitor (33 μ F or more) to the sensor power supply input terminal in order to stabilize the power supply voltage.


MA Motion Sensor (AMA1, AMB1, 2, 3)

REFERENCE DATA

Operating region characteristics


- How to interpret the graph

Example: Operating area of the Short Type
with rated detection distance of
8 cm 3.150 inch.



Operating area within the dotted lines


Objects that enter the entire area are detected.




Note: If only part of the object is in the detection area, it is not detected.

Operating area within the solid lines


Objects that even partially enter the area are detected.




1.-(1) Thin short type (AMA14□□□□□) Short type (AMB14□□□□□)



1.-(2) Middle type (AMB24□□□□□)



1.-(3) Long type (AMB34□□□□□)




DIMENSIONS (mm inch)

The CAD data of the products with a **CAD Data** mark can be downloaded from: <http://industrial.panasonic.com/ac/e/>

(Common to the Built-in oscillation circuit type and External triggering type)

1. Thin short type (V type)


CAD Data



*Rear side connector protrusion: Max. 0.4mm


2. Short type (H type)

CAD Data




3. Middle type (H type)

CAD Data




MA Motion Sensor (AMA1, AMB1, 2, 3)

4. Long type (H type)


CAD Data

5. Long type (V type)


CAD Data

WIRING DIAGRAM (Connector surface view)


1. Thin short type (V type)




2. Short type (H type)




3. Middle type (H type)



4. Long type (H type)




5. Long type (V type)



OPTIONS (mm inch)

1. Connector with cable (for Short, Middle and Long type)


AMV9001



Note: Mistaken cable assembly can cause damage to the internal circuits, so please check the power cord before switching ON. (Particular care must be taken as to avoid reverse connection of the power.)

2. Connector with cable (for Thin short type)

AMV9002



MA Motion Sensor (AMA1, AMB1, 2, 3)

NOTES

1. Environment

- 1) Avoid using the sensor in environments containing excessive amounts of steam, dust, corrosive gas, or where organic solvents are present.
- 2) When the sensor is used in noisy environments, implement a countermeasure such as connecting a capacitor (Min. 33 μ F) across the power input terminals. Only use the sensor after verifying actual operation.

2. Wiring

- 1) Check all wiring before applying power. Incorrect wiring may damage the internal circuit (in particular, check that the connection to the power supply is not reversed.)
- 2) Avoid excessive removing and replacing of the connector.

3. Detector surface (Optical surface)


- 1) Keep the detector surface clean. Excessive dust or dirt on the detector surface will deteriorate the sensing performance.
- 2) Do not allow condensation or freezing to occur on the surface of the sensor. If condensation or freezing does occur at low temperatures, the sensor may not detect objects correctly.
- 3) This product is designed to detect the existence of human bodies. The sensor may not detect properly or the detection distance may become unstable if the objects consist of a low reflective material (e.g., an object coated with black rubber, etc.) or of a highly reflective material (e.g., mirror, glass, coated paper, etc.).

- 4) The front surface of the lens and case are made of polycarbonate resin and can withstand water, alcohol, oils, salts and weak acids. Other fluids such as alkalines, aromatic hydrocarbons and halogenated hydrocarbons may melt or swell the lens and case, please do not have such fluids touch the lens and case.
- 5) If you use the sensor with a cover or filter connected to the front of the sensor, the sensor may detect the cover itself, the detection distance can change, and unstable operation can result.
- 6) If this sensor is used in a position where it will be facing another sensor, light will be received from the other sensor which can cause mutual interference and malfunction. Therefore, please verify the installation conditions before use.
- 7) When multiple sensors are to be used side by side, please verify that there will be no mutual interference by installing them with the proper spacing, depending on the type as shown below.

Model number	Sensor spacing
AMB1 series	5 cm 1.969 inch
AMA1 series	8 cm 3.150 inch
AMB2 series	10 cm 3.937 inch
AMB3 series	20 cm 7.874 inch

4. Recommended installation procedure

Install the sensor so that it is orientated correctly in relation to the pass directions of the target objects as shown in the figure below.



* → stands for pass direction of the target object.

For the general precautions, refer to “NOTES FOR USING MOTION SENSOR (Common)” on next page.