



Product number
SEE TABLE, SHEET 5





spec ref		dr		wcadmin	2007/04/20	projection		MM		size	A3	scale	1:1
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED	eng		Yong-Keat Lim	2011/09/14					ecn no	ELX-S-005941-1		
		chr		-	-								
ASME Y14.5			appr		Chen-Hong Tan	2011/09/20	product family		rel level		Released		
surface		linear	0.X	±		title	AirMax VS R/A IO HDR ASSY		dwg no	10041398		rev	B
			0.XX	±									
			0.XXX	±									
ASME Y14.5	angular	0°	±°	www.fci.com	cat. no.		Product - Customer Drw			sheet 1 of 5			




Copyright FCI.

DESCRIPTION	DIM A	DIM B	DIM C
2X20MM MODULES PLACED END-TO-END	2.00	19.90 2X	20.00



spec ref				dr		wcadmin		2007/04/20		projection		MM		size		A3		scale		1:1							
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED				eng		Yong-Keat Lim		2011/09/14						ecn no		ELX-S-005941-1									
ASME Y14.5						chr		-		-																	
-						appr		Chen-Hong Tan		2011/09/20												product family					
surface		linear				title		AirMax VS R/A IO HDR ASSY						dwg no		10041398				rev		B					
																								0.X		±	
																								0.XX		±	
		ASME Y14.5		angular		0°		±°		www.fci.com		cat. no.		Product - Customer Drw						sheet 2 of 5							



DESCRIPTION	DIM D	DIM E	DIM F
2X20MM MODULES PLACED END-TO-END	2.00	19.90 2X	20.00




spec ref				dr		wcadmin		2007/04/20		projection		MM		size		A3		scale		2:1							
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED				eng		Yong-Keat Lim		2011/09/14						ecn no		ELX-S-005941-1									
ASME Y14.5						chr		-		-																	
-						appr		Chen-Hong Tan		2011/09/20												product family					
surface		linear				title		AirMax VS R/A IO HDR ASSY						dwg no		10041398				rev		B					
																								0.X		±	
																								0.XX		±	
		ASME Y14.5		angular		0°		±°		www.fci.com		cat. no.		Product - Customer Drw						sheet 3 of 5							




Copyright FCI.



spec ref				dr	wcadmin	2007/04/20	projection 	MM 	size	A3	scale	2:1	
tolerance std				eng	Yong-Keat Lim	2011/09/14			ecn no				ELX-S-005941-1
ASME Y14.5				chr	-	-			rel level				Released
-				appr	Chen-Hong Tan	2011/09/20	product family						
surface ✓	linear	0.X	±		title	AirMax VS R/A 10 HDR ASSY PRESS-FIT, 120 POS, 20MM			dwg no	10041398		rev	B
		0.XX	±										
		0.XXX	±										
ASME Y14.5	angular	0°	±°	www.fci.com	cat. no.	Product - Customer Drw				sheet 4 of 5			

PART NUMBER	PRESS-FIT TAIL PLATING TYPE
10041398-101LF	TIN OVER NICKEL (LEAD FREE) NOTE 8 & 10



NOTES:

- CONNECTOR MATERIALS:
HOUSING & RETAINER: HIGH TEMP THERMOPLASTIC, NATURAL, UL94V-0
IMLA PLASTIC: HIGH TEMP THERMOPLASTIC, BLACK, UL94V-0
CONTACT: COPPER ALLOY
- CONTACT PLATING:
SEPARABLE INTERFACE: PERFORMANCE-BASED PLATING, QUALIFIED TO MEET THE REQUIREMENTS OF FCI PRODUCT SPECIFICATION GS-12-344 INCLUDING TELCORDIA GR-1217-CORE (NOVEMBER 1995) CENTRAL OFFICE TEST SEQUENCE

PRESS-FIT TAILS: SEE TABLE
- PRODUCT SPECIFICATION: GS-12-344
- APPLICATION SPECIFICATION: GS-20-035
- PRODUCT MARKING, (PART NUMBER & LOT CODE), ON THIS SURFACE
- THERE IS NO GROUND BUSSING WITHIN THE CONNECTOR SYSTEM
- REFER TO CUSTOMER DRAWING 10045979 FOR INFORMATION ON PCB HOLE DIAMETERS AND PLATING OPTIONS.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 40 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.
- PACKAGING MEETS GS-14-920 LEAD FREE LABELING SPECIFICATION.

spec ref				dr		wcadmin	2007/04/20		projection		MM		size		A3	scale		1:1		
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED				eng		Yong-Keat Lim		2011/09/14						ecn no		ELX-S-005941-1		
ASME Y14.5						chr		-		-										
-						appr		Chen-Hong Tan		2011/09/20						product family		rel level		Released
surface			linear				title		AirMax VS R/A IO HDR ASSY						dwg no		10041398		rev	
									PRESS-FIT, 120 POS, 20MM										B	
ASME Y14.5		angular		0°		±°		www.fci.com		cat. no.			Product - Customer Drw					sheet 5 of 5		