

50733-X128X

∅.100 [2.54] THRU, 2X
=A=

.585 [14.86] REF.

-C-
.003:1

DIM "B"

NOTE 4

.0260 [0.66]
⊕ .010/.25 ⊕ A ⊕ B | C

.100 [2.54]

.120 [3.05]
TYP.

.100 [2.54] TYP.

DIM "C"

DIM "D"

.200 [5.08]

-B-
.003:1

.462 [11.73] REF.

DIM "A" ±.010 [.25]

F
F

mat'l. code		surface		tolerance		projection		product family	
NOTE 2		ISO 1302 ✓		ISO 406 ISO 1101		⊕ ⊖		HPC	
ltr	ecn	no	dr	date		tolerances unless otherwise specified		title	
A	v41769	GIP	11/07/94	angles	linear	.xx ±.01/.3	INCH/MM		4 ROW, VERT. HDR. HSG. W/SPECIAL POCKETS
B	M06-0261	MNR	7/10/94	0°±2'		.xxx ±.005/.13	scale 3:1		
				dr		G. PETERS	11/08/94		dwg no 50733 sheet 1 of 2 size A3
				enr		W. FUNK	11/07/94		
				chr		W. FUNK	11/08/94		
				appd		S. CLARK	11/09/94		type Product Customer Drawing
sheet index	revision	B	B						
	sheet	1	2						




FCI
FCIconnect.com

Copyright FCI


form: A3

50733-X128X


DIM.	LENGTH FORMULAS
DIM "A"	.100/2.54 x NO. OF COLUMNS + .75/19.1
DIM "B"	.100/2.54 x NO. OF COLUMNS + .45/11.4
DIM "C"	.100/2.54 x NO. OF COLUMNS - .1/2.5
DIM "D"	.100/2.54 x NO. OF COLUMNS + .050/1.3



SECTION F-F



SECTION X-X



SECTION U-U

NOTES:

- PRODUCT DESCRIPTION CODE:
 50733 - X 128 X
 ALWAYS "X"
 NO. OF POSITIONS
 ALWAYS "X"
 BASE NUMBER
- MATERIALS:
 HOUSING - PPS, GLASS-FILLED.
- ALL CHAMFERS 30° UNLESS OTHERWISE SHOWN.
- BERG NAME, BERG P/N, AND LOT CODE TO APPEAR ON THIS SURFACE.

mat'l. code		surface		tolerance		projection		product family	
NOTE 2		ISO 1302 ✓		ISO 406		ISO 1101		HPC	
ltr	ecn	no	dr	tolerances unless otherwise specified		INCH/MM		title	
B				angles	linear	.xx ±.01/.3		4 ROW, VERT. HDR. HSG.	
				0°±2'		.xxx ±.005/.13		W/SPECIAL POCKETS	
						.xxxx ±.0020/.051		scale 3:1	
			dr	G. PETERS	11/08/94			dwg no	
			enr	W. FUNK	11/07/94			sheet 2 of 2	
			chr	W. FUNK	11/08/94			size	
			appd	S. CLARK	11/09/94			A3	
sheet index		revision sheet						type Product Customer Drawing	

FCJ
FCIconnect.com

Copyright FCJ