






Thermal Transfer Labels

Label Index By Size (Continued)



Part Number	Labels Per Package	Material	Color	Labels Per Row	Label Width Inch (mm) A	Label Height Inch (mm) B	Horiz. Repeat Inch (mm) C	Vert. Repeat Inch (mm) D	Web Width Inch (mm) E	Suggested Ribbon	Diagram
1.500" Label Width (Continued)											
THT-6-351-10	10,000	Tamper-Resistant Vinyl	White	2	1.500 (38.1)	0.750 (19.1)	1.650 (41.9)	0.875 (22.2)	3.350 (85.1)	R6202	Fig. 1
THT-6-352-10	10,000	Tamper-Resistant Vinyl	Silver	2	1.500 (38.1)	0.750 (19.1)	1.650 (41.9)	0.875 (22.2)	3.350 (85.1)	R6002	Fig. 1
THT-6-413-10	10,000	Polyester	Silver	2	1.500 (38.1)	0.750 (19.1)	1.650 (41.9)	0.875 (22.2)	3.350 (85.1)	R6002	Fig. 1
THT-6-423-10	10,000	Polyester	White	2	1.500 (38.1)	0.750 (19.1)	1.650 (41.9)	0.875 (22.2)	3.350 (85.1)	R6002	Fig. 1
THT-6-428-10	10,000	Metallized Polyester	Silver	2	1.500 (38.1)	0.750 (19.1)	1.650 (41.9)	0.875 (22.2)	3.350 (85.1)	R4300	Fig. 1
THT-6-434-10	10,000	Metallized Polyester	Silver	2	1.500 (38.1)	0.750 (19.1)	1.650 (41.9)	0.875 (22.2)	3.350 (85.1)	R6002	Fig. 1
THT-6-438-10	10,000	Tamper-Evident Polyester	Silver	2	1.500 (38.1)	0.750 (19.1)	1.650 (41.9)	0.875 (22.2)	3.350 (85.1)	R4300	Fig. 1
THT-6-480-10	10,000	Polyester	Silver	2	1.500 (38.1)	0.750 (19.1)	1.650 (41.9)	0.875 (22.2)	3.350 (85.1)	R6002	Fig. 1
THT-6-486-10	10,000	Metallized Polyester	Silver	2	1.500 (38.1)	0.750 (19.1)	1.650 (41.9)	0.875 (22.2)	3.350 (85.1)	R4300	Fig. 1
THT-6-7546-10	10,000	Tamper-Evident Polyester	White	2	1.500 (38.1)	0.750 (19.1)	1.650 (41.9)	0.875 (22.2)	3.350 (85.1)	R6002	Fig. 1
THT-6-7576-10	10,000	Tamper-Evident Polyester	Silver	2	1.500 (38.1)	0.750 (19.1)	1.650 (41.9)	0.875 (22.2)	3.350 (85.1)	R6002	Fig. 1
THT-105-437	1 Roll	Tedlar®	White	1	1.500 (38.1)	300 ft (91.4 m)	-	300 ft (91.4 m)	1.750 (44.5)	R4302	Fig. 3
THT-105-437-YL	1 Roll	Tedlar®	Yellow	1	1.500 (38.1)	300 ft (91.4 m)	-	300 ft (91.4 m)	1.750 (44.5)	R4302	Fig. 3
1.625" Label Width											
THT-155-490-3	3,000	Polyester	White	1	1.625 (41.3)	0.600 (15.2)	-	0.700 (17.8)	1.825 (46.4)	R4302	Fig. 2
1.750" Label Width											
THT-72-457-10	10,000	Polyimide	White	1	1.750 (44.5)	0.250 (6.4)	-	0.350 (8.9)	1.950 (49.5)	R6000	Fig. 2
THT-72-478-10	10,000	Polyimide	White	1	1.750 (44.5)	0.250 (6.4)	-	0.350 (8.9)	1.950 (49.5)	R6000	Fig. 2
THT-185-499-3	3,000	Nylon Cloth	White	1	1.750 (44.5)	1.000 (25.4)	-	1.125 (28.6)	1.950 (49.5)	R4302	Fig. 2
THT-186-499-3	3,000	Nylon Cloth	White	1	1.750 (44.5)	1.875 (47.6)	-	1.975 (50.2)	1.950 (49.5)	R4302	Fig. 2
1.900" Label Width											
THT-156-490-3	3,000	Polyester	White	1	1.900 (48.3)	1.000 (25.4)	-	1.100 (27.9)	2.100 (53.3)	R4302	Fig. 2
THT-156-492-3	3,000	Polyester	White	1	1.900 (48.3)	1.000 (25.4)	-	1.100 (27.9)	2.100 (53.3)	R6400	Fig. 2
2.000" Label Width											
THT-48-423-10	10,000	Polyester	White	1	2.000 (50.8)	0.250 (6.4)	-	0.350 (8.9)	2.200 (55.9)	R6000	Fig. 2
THT-48-426-10	10,000	Polyimide	Amber	1	2.000 (50.8)	0.250 (6.4)	-	0.350 (8.9)	2.200 (55.9)	R4302	Fig. 2
THT-48-457-10	10,000	Polyimide	White	1	2.000 (50.8)	0.250 (6.4)	-	0.350 (8.9)	2.200 (55.9)	R6000	Fig. 2
THT-48-473-10	10,000	Polyester	White	1	2.000 (50.8)	0.250 (6.4)	-	0.350 (8.9)	2.200 (55.9)	R6000	Fig. 2
THT-48-476-10	10,000	Polyimide	Light Green	1	2.000 (50.8)	0.250 (6.4)	-	0.350 (8.9)	2.200 (55.9)	R6000	Fig. 2
THT-48-477-10	10,000	Polyimide	White	1	2.000 (50.8)	0.250 (6.4)	-	0.350 (8.9)	2.200 (55.9)	R6000	Fig. 2
THT-48-478-10	10,000	Polyimide	White	1	2.000 (50.8)	0.250 (6.4)	-	0.350 (8.9)	2.200 (55.9)	R6000	Fig. 2
THT-48-479-10	10,000	Polyimide	White	1	2.000 (50.8)	0.250 (6.4)	-	0.350 (8.9)	2.200 (55.9)	R6000	Fig. 2
THT-48-497-10	10,000	Polyimide	White	1	2.000 (50.8)	0.250 (6.4)	-	0.350 (8.9)	2.200 (55.9)	R6000	Fig. 2
THT-151-499-3	3,000	Nylon Cloth	White	1	2.000 (50.8)	0.250 (6.4)	-	0.350 (8.9)	2.200 (55.9)	R4302	Fig. 2
THT-15-351-2.5	2,500	Tamper-Resistant Vinyl	White	1	2.000 (50.8)	0.250 (6.4)	-	0.375 (9.5)	2.200 (55.9)	R6200	Fig. 2

Tedlar® is a registered trademark of DuPont.

Note: Labels in chart are sorted in order by width, height, vertical repeat, die number and material number.