

## **Contents**

|                                                |    |
|------------------------------------------------|----|
| Features .....                                 | 1  |
| Applications .....                             | 1  |
| Pin Assignment .....                           | 1  |
| Block Diagram .....                            | 2  |
| Selection Guide .....                          | 2  |
| Output Configurations.....                     | 5  |
| Absolute Maximum Ratings .....                 | 6  |
| Electrical Characteristics .....               | 7  |
| Test Circuits .....                            | 11 |
| Technical Terms .....                          | 12 |
| Standard Circuit.....                          | 13 |
| Operation.....                                 | 14 |
| Dimensions.....                                | 16 |
| Taping .....                                   | 17 |
| Marking .....                                  | 20 |
| Characteristics (typical characteristics)..... | 21 |
| Application Circuit Examples .....             | 28 |
| Remarks.....                                   | 29 |
| Frequently Asked Questions.....                | 30 |

The S-808 Series is a high-precision voltage detector developed using CMOS process. The detection voltage is fixed internally, with an accuracy of  $\pm 2.0\%$ . Two output types, Nch open-drain and CMOS output, are available.

## ■ Features

- Ultra-low current consumption  
 $1.3\ \mu\text{A typ. (V}_{\text{DD}}=1.5\ \text{V})$   
 Products with detection voltage of 1.4 V or less electronic  
 $0.8\ \mu\text{A typ. (V}_{\text{DD}}=3.5\ \text{V})$   
 Products with detection voltage of 1.5 V or more
- High-precision detection voltage  
 $\pm 2.0\%$
- Low operating voltage  
 $0.7\ \text{to}\ 5.0\ \text{V}$   
 Products with detection voltage of 1.4 V or less  
 $0.95\ \text{to}\ 10.0\ \text{V}$   
 Products with a detection voltage of 1.5 V or more
- Hysteresis characteristics  
 $5\%\ \text{typ.}$
- Detection voltage  
 $0.8\ \text{to}\ 6.0\ \text{V}$   
 $(0.1\ \text{V step})$
- Nch open-drain active low and CMOS active low output
- SC-82AB Super-small plastic package
- TO-92 Plastic package
- SOT-89-3 Miniaturized power mold plastic package
- SOT-23-5 Very-small plastic package

## ■ Applications

- Battery checker
- Power failure detector
- Power monitor for pagers, calculators, organizers,
- Constant voltage power monitor for cameras, video equipment, communication devices
- Power monitor for microcomputers and reset CPUs

## ■ Pin Assignment




Figure 1

SUPER-SMALL PACKAGE HIGH-PRECISION VOLTAGE DETECTOR  
S-808 Series

■ Block Diagram





Figure 2

■ Selection Guide



# SUPER-SMALL PACKAGE HIGH-PRECISION VOLTAGE DETECTOR

## S-808 Series

**Table 1**

| Detection voltage range<br>(V) | Hysteresis width<br>V <sub>HYS</sub> typ.(V) | Nch Open Drain(Low) |            |                    |                    |
|--------------------------------|----------------------------------------------|---------------------|------------|--------------------|--------------------|
|                                |                                              | SC-82AB             | TO-92      | SOT-89-3           | SOT-23-5           |
| 0.8V±2.0%                      | 0.034                                        | S-80808ANNP-E7Y-T2  | —          | —                  | —                  |
| 0.9V±2.0%                      | 0.044                                        | S-80809ANNP-E7Z-T2  | —          | —                  | —                  |
| 1.0V±2.0%                      | 0.054                                        | S-80810ANNP-E70-T2  | —          | —                  | —                  |
| 1.1V±2.0%                      | 0.064                                        | S-80811ANNP-E71-T2  | —          | —                  | —                  |
| 1.2V±2.0%                      | 0.073                                        | S-80812ANNP-E72-T2  | —          | —                  | —                  |
| 1.3V±2.0%                      | 0.083                                        | S-80813ANNP-EDA-T2  | —          | —                  | —                  |
| 1.4V±2.0%                      | 0.093                                        | S-80814ANNP-EDB-T2  | —          | —                  | —                  |
| 1.5V±2.0%                      | 0.075                                        | S-80815ANNP-EDC-T2  | S-80815ANY | S-80815ANUP-EDC-T2 | —                  |
| 1.6V±2.0%                      | 0.080                                        | S-80816ANNP-EDD-T2  | S-80816ANY | S-80816ANUP-EDD-T2 | —                  |
| 1.7V±2.0%                      | 0.085                                        | S-80817ANNP-EDE-T2  | S-80817ANY | S-80817ANUP-EDE-T2 | S-80817ANMP-EDE-T2 |
| 1.8V±2.0%                      | 0.090                                        | S-80818ANNP-EDF-T2  | S-80818ANY | S-80818ANUP-EDF-T2 | S-80818ANMP-EDF-T2 |
| 1.9V±2.0%                      | 0.095                                        | S-80819ANNP-EDG-T2  | S-80819ANY | S-80819ANUP-EDG-T2 | S-80819ANMP-EDG-T2 |
| 2.0V±2.0%                      | 0.100                                        | S-80820ANNP-EDH-T2  | S-80820ANY | S-80820ANUP-EDH-T2 | S-80820ANMP-EDH-T2 |
| 2.1V±2.0%                      | 0.105                                        | S-80821ANNP-EDJ-T2  | S-80821ANY | S-80821ANUP-EDJ-T2 | S-80821ANMP-EDJ-T2 |
| 2.2V±2.0%                      | 0.110                                        | S-80822ANNP-EDK-T2  | S-80822ANY | S-80822ANUP-EDK-T2 | S-80822ANMP-EDK-T2 |
| 2.3V±2.0%                      | 0.115                                        | S-80823ANNP-EDL-T2  | S-80823ANY | S-80823ANUP-EDL-T2 | S-80823ANMP-EDL-T2 |
| 2.4V±2.0%                      | 0.120                                        | S-80824ANNP-EDM-T2  | S-80824ANY | S-80824ANUP-EDM-T2 | S-80824ANMP-EDM-T2 |
| 2.5V±2.0%                      | 0.125                                        | S-80825ANNP-EDN-T2  | S-80825ANY | S-80825ANUP-EDN-T2 | S-80825ANMP-EDN-T2 |
| 2.6V±2.0%                      | 0.130                                        | S-80826ANNP-EDP-T2  | S-80826ANY | S-80826ANUP-EDP-T2 | —                  |
| 2.7V±2.0%                      | 0.135                                        | S-80827ANNP-EDQ-T2  | S-80827ANY | S-80827ANUP-EDQ-T2 | S-80827ANMP-EDQ-T2 |
| 2.8V±2.0%                      | 0.140                                        | S-80828ANNP-EDR-T2  | S-80828ANY | S-80828ANUP-EDR-T2 | S-80828ANMP-EDR-T2 |
| 2.9V±2.0%                      | 0.145                                        | S-80829ANNP-EDS-T2  | S-80829ANY | S-80829ANUP-EDS-T2 | —                  |
| 3.0V±2.0%                      | 0.150                                        | S-80830ANNP-EDT-T2  | S-80830ANY | S-80830ANUP-EDT-T2 | S-80830ANMP-EDT-T2 |
| 3.1V±2.0%                      | 0.155                                        | S-80831ANNP-EDV-T2  | S-80831ANY | S-80831ANUP-EDV-T2 | —                  |
| 3.2V±2.0%                      | 0.160                                        | S-80832ANNP-EDW-T2  | S-80832ANY | S-80832ANUP-EDW-T2 | S-80832ANMP-EDW-T2 |
| 3.3V±2.0%                      | 0.165                                        | S-80833ANNP-EDX-T2  | S-80833ANY | S-80833ANUP-EDX-T2 | S-80833ANMP-EDX-T2 |
| 3.4V±2.0%                      | 0.170                                        | S-80834ANNP-EDY-T2  | S-80834ANY | S-80834ANUP-EDY-T2 | S-80834ANMP-EDY-T2 |
| 3.5V±2.0%                      | 0.175                                        | S-80835ANNP-EDZ-T2  | S-80835ANY | S-80835ANUP-EDZ-T2 | S-80835ANMP-EDZ-T2 |
| 3.6V±2.0%                      | 0.180                                        | S-80836ANNP-ED0-T2  | S-80836ANY | S-80836ANUP-ED0-T2 | S-80836ANMP-ED0-T2 |
| 3.7V±2.0%                      | 0.185                                        | S-80837ANNP-ED1-T2  | S-80837ANY | S-80837ANUP-ED1-T2 | —                  |
| 3.8V±2.0%                      | 0.190                                        | S-80838ANNP-ED2-T2  | S-80838ANY | S-80838ANUP-ED2-T2 | —                  |
| 3.9V±2.0%                      | 0.195                                        | S-80839ANNP-ED3-T2  | S-80839ANY | S-80839ANUP-ED3-T2 | S-80839ANMP-ED3-T2 |
| 4.0V±2.0%                      | 0.200                                        | S-80840ANNP-ED4-T2  | S-80840ANY | S-80840ANUP-ED4-T2 | S-80840ANMP-ED4-T2 |
| 4.1V±2.0%                      | 0.205                                        | S-80841ANNP-ED5-T2  | S-80841ANY | S-80841ANUP-ED5-T2 | —                  |
| 4.2V±2.0%                      | 0.210                                        | S-80842ANNP-ED6-T2  | S-80842ANY | S-80842ANUP-ED6-T2 | S-80842ANMP-ED6-T2 |
| 4.3V±2.0%                      | 0.215                                        | S-80843ANNP-ED7-T2  | S-80843ANY | S-80843ANUP-ED7-T2 | —                  |
| 4.4V±2.0%                      | 0.220                                        | S-80844ANNP-ED8-T2  | S-80844ANY | S-80844ANUP-ED8-T2 | S-80844ANMP-ED8-T2 |
| 4.5V±2.0%                      | 0.225                                        | S-80845ANNP-ED9-T2  | S-80845ANY | S-80845ANUP-ED9-T2 | S-80845ANMP-ED9-T2 |
| 4.6V±2.0%                      | 0.230                                        | S-80846ANNP-EJA-T2  | S-80846ANY | S-80846ANUP-EJA-T2 | —                  |
| 4.7V±2.0%                      | 0.235                                        | S-80847ANNP-EJB-T2  | S-80847ANY | S-80847ANUP-EJB-T2 | —                  |
| 4.8V±2.0%                      | 0.240                                        | S-80848ANNP-EJC-T2  | S-80848ANY | S-80848ANUP-EJC-T2 | —                  |
| 4.9V±2.0%                      | 0.245                                        | S-80849ANNP-EJD-T2  | S-80849ANY | S-80849ANUP-EJD-T2 | —                  |
| 5.0V±2.0%                      | 0.250                                        | S-80850ANNP-EJE-T2  | S-80850ANY | S-80850ANUP-EJE-T2 | S-80850ANMP-EJE-T2 |
| 5.1V±2.0%                      | 0.255                                        | S-80851ANNP-EJF-T2  | S-80851ANY | S-80851ANUP-EJF-T2 | S-80851ANMP-EJF-T2 |
| 5.2V±2.0%                      | 0.260                                        | S-80852ANNP-EJG-T2  | —          | S-80852ANUP-EJG-T2 | —                  |
| 5.3V±2.0%                      | 0.265                                        | S-80853ANNP-EJH-T2  | S-80853ANY | —                  | —                  |
| 5.4V±2.0%                      | 0.270                                        | S-80854ANNP-EJJ-T2  | —          | —                  | —                  |
| 5.5V±2.0%                      | 0.275                                        | S-80855ANNP-EJK-T2  | —          | —                  | —                  |
| 5.6V±2.0%                      | 0.280                                        | S-80856ANNP-EJL-T2  | —          | —                  | —                  |
| 5.7V±2.0%                      | 0.285                                        | S-80857ANNP-EJM-T2  | —          | —                  | —                  |
| 5.8V±2.0%                      | 0.290                                        | S-80858ANNP-EJN-T2  | —          | —                  | —                  |
| 5.9V±2.0%                      | 0.295                                        | S-80859ANNP-EJP-T2  | —          | —                  | —                  |
| 6.0V±2.0%                      | 0.300                                        | S-80860ANNP-EJQ-T2  | —          | S-80860ANUP-EJQ-T2 | —                  |

# SUPER-SMALL PACKAGE HIGH-PRECISION VOLTAGE DETECTOR

## S-808 Series

| Detection voltage range<br>(V) | Hysteresis width<br>$V_{HYS}$ typ.(V) | CMOS Output Drain(Low) |            |                    |                    |
|--------------------------------|---------------------------------------|------------------------|------------|--------------------|--------------------|
|                                |                                       | SC-82AB                | TO-92      | SOT-89-3           | SOT-23-5           |
| 0.8V±2.0%                      | 0.034                                 | S-80808ALNP-E5Y-T2     | —          | —                  | —                  |
| 0.9V±2.0%                      | 0.044                                 | S-80809ALNP-E5Z-T2     | —          | —                  | —                  |
| 1.0V±2.0%                      | 0.054                                 | S-80810ALNP-E50-T2     | —          | —                  | —                  |
| 1.1V±2.0%                      | 0.064                                 | S-80811ALNP-E51-T2     | —          | —                  | —                  |
| 1.2V±2.0%                      | 0.073                                 | S-80812ALNP-E52-T2     | —          | —                  | —                  |
| 1.3V±2.0%                      | 0.083                                 | S-80813ALNP-EAA-T2     | —          | —                  | —                  |
| 1.4V±2.0%                      | 0.093                                 | S-80814ALNP-EAB-T2     | —          | —                  | —                  |
| 1.5V±2.0%                      | 0.075                                 | S-80815ALNP-EAC-T2     | S-80815ALY | S-80815ALUP-EAC-T2 | S-80815ALMP-EAC-T2 |
| 1.6V±2.0%                      | 0.080                                 | S-80816ALNP-EAD-T2     | S-80816ALY | S-80816ALUP-EAD-T2 | —                  |
| 1.7V±2.0%                      | 0.085                                 | S-80817ALNP-EAE-T2     | S-80817ALY | S-80817ALUP-EAE-T2 | —                  |
| 1.8V±2.0%                      | 0.090                                 | S-80818ALNP-EAF-T2     | S-80818ALY | S-80818ALUP-EAF-T2 | S-80818ALMP-EAF-T2 |
| 1.9V±2.0%                      | 0.095                                 | S-80819ALNP-EAG-T2     | S-80819ALY | S-80819ALUP-EAG-T2 | S-80819ALMP-EAG-T2 |
| 2.0V±2.0%                      | 0.100                                 | S-80820ALNP-EAH-T2     | S-80820ALY | S-80820ALUP-EAH-T2 | S-80820ALMP-EAH-T2 |
| 2.1V±2.0%                      | 0.105                                 | S-80821ALNP-EAJ-T2     | S-80821ALY | S-80821ALUP-EAJ-T2 | S-80821ALMP-EAJ-T2 |
| 2.2V±2.0%                      | 0.110                                 | S-80822ALNP-EAK-T2     | S-80822ALY | S-80822ALUP-EAK-T2 | —                  |
| 2.3V±2.0%                      | 0.115                                 | S-80823ALNP-EAL-T2     | S-80823ALY | S-80823ALUP-EAL-T2 | S-80823ALMP-EAL-T2 |
| 2.4V±2.0%                      | 0.120                                 | S-80824ALNP-EAM-T2     | S-80824ALY | S-80824ALUP-EAM-T2 | —                  |
| 2.5V±2.0%                      | 0.125                                 | S-80825ALNP-EAN-T2     | S-80825ALY | S-80825ALUP-EAN-T2 | S-80825ALMP-EAN-T2 |
| 2.6V±2.0%                      | 0.130                                 | S-80826ALNP-EAP-T2     | S-80826ALY | S-80826ALUP-EAP-T2 | —                  |
| 2.7V±2.0%                      | 0.135                                 | S-80827ALNP-EAQ-T2     | S-80827ALY | S-80827ALUP-EAQ-T2 | S-80827ALMP-EAQ-T2 |
| 2.8V±2.0%                      | 0.140                                 | S-80828ALNP-EAR-T2     | S-80828ALY | S-80828ALUP-EAR-T2 | S-80828ALMP-EAR-T2 |
| 2.9V±2.0%                      | 0.145                                 | S-80829ALNP-EAS-T2     | S-80829ALY | S-80829ALUP-EAS-T2 | —                  |
| 3.0V±2.0%                      | 0.150                                 | S-80830ALNP-EAT-T2     | S-80830ALY | S-80830ALUP-EAT-T2 | S-80830ALMP-EAT-T2 |
| 3.1V±2.0%                      | 0.155                                 | S-80831ALNP-EAV-T2     | S-80831ALY | S-80831ALUP-EAV-T2 | —                  |
| 3.2V±2.0%                      | 0.160                                 | S-80832ALNP-EAW-T2     | S-80832ALY | S-80832ALUP-EAW-T2 | S-80832ALMP-EAW-T2 |
| 3.3V±2.0%                      | 0.165                                 | S-80833ALNP-EAX-T2     | S-80833ALY | S-80833ALUP-EAX-T2 | S-80833ALMP-EAX-T2 |
| 3.4V±2.0%                      | 0.170                                 | S-80834ALNP-EAY-T2     | S-80834ALY | S-80834ALUP-EAY-T2 | —                  |
| 3.5V±2.0%                      | 0.175                                 | S-80835ALNP-EAZ-T2     | S-80835ALY | S-80835ALUP-EAZ-T2 | S-80835ALMP-EAZ-T2 |
| 3.6V±2.0%                      | 0.180                                 | S-80836ALNP-EA0-T2     | S-80836ALY | S-80836ALUP-EA0-T2 | —                  |
| 3.7V±2.0%                      | 0.185                                 | S-80837ALNP-EA1-T2     | S-80837ALY | S-80837ALUP-EA1-T2 | —                  |
| 3.8V±2.0%                      | 0.190                                 | S-80838ALNP-EA2-T2     | S-80838ALY | S-80838ALUP-EA2-T2 | —                  |
| 3.9V±2.0%                      | 0.195                                 | S-80839ALNP-EA3-T2     | S-80839ALY | S-80839ALUP-EA3-T2 | —                  |
| 4.0V±2.0%                      | 0.200                                 | S-80840ALNP-EA4-T2     | S-80840ALY | S-80840ALUP-EA4-T2 | S-80840ALMP-EA4-T2 |
| 4.1V±2.0%                      | 0.205                                 | S-80841ALNP-EA5-T2     | S-80841ALY | S-80841ALUP-EA5-T2 | —                  |
| 4.2V±2.0%                      | 0.210                                 | S-80842ALNP-EA6-T2     | S-80842ALY | S-80842ALUP-EA6-T2 | S-80842ALMP-EA6-T2 |
| 4.3V±2.0%                      | 0.215                                 | S-80843ALNP-EA7-T2     | S-80843ALY | S-80843ALUP-EA7-T2 | —                  |
| 4.4V±2.0%                      | 0.220                                 | S-80844ALNP-EA8-T2     | S-80844ALY | S-80844ALUP-EA8-T2 | —                  |
| 4.5V±2.0%                      | 0.225                                 | S-80845ALNP-EA9-T2     | S-80845ALY | S-80845ALUP-EA9-T2 | S-80845ALMP-EA9-T2 |
| 4.6V±2.0%                      | 0.230                                 | S-80846ALNP-EEA-T2     | S-80846ALY | S-80846ALUP-EEA-T2 | —                  |
| 4.7V±2.0%                      | 0.235                                 | S-80847ALNP-EEB-T2     | S-80847ALY | S-80847ALUP-EEB-T2 | —                  |
| 4.8V±2.0%                      | 0.240                                 | S-80848ALNP-EEC-T2     | S-80848ALY | S-80848ALUP-EEC-T2 | —                  |
| 4.9V±2.0%                      | 0.245                                 | S-80849ALNP-EED-T2     | S-80849ALY | S-80849ALUP-EED-T2 | S-80849ALMP-EED-T2 |
| 5.0V±2.0%                      | 0.250                                 | S-80850ALNP-EEE-T2     | S-80850ALY | S-80850ALUP-EEE-T2 | S-80850ALMP-EEE-T2 |
| 5.1V±2.0%                      | 0.255                                 | S-80851ALNP-EEF-T2     | S-80851ALY | S-80851ALUP-EEF-T2 | S-80851ALMP-EEF-T2 |
| 5.2V±2.0%                      | 0.260                                 | S-80852ALNP-EEG-T2     | —          | S-80852ALUP-EEG-T2 | S-80852ALMP-EEG-T2 |
| 5.3V±2.0%                      | 0.265                                 | S-80853ALNP-EEH-T2     | —          | —                  | —                  |
| 5.4V±2.0%                      | 0.270                                 | S-80854ALNP-EEJ-T2     | —          | —                  | —                  |
| 5.5V±2.0%                      | 0.275                                 | S-80855ALNP-EEK-T2     | —          | S-80855ALUP-EEK-T2 | —                  |
| 5.6V±2.0%                      | 0.280                                 | S-80856ALNP-EEL-T2     | —          | —                  | —                  |
| 5.7V±2.0%                      | 0.285                                 | S-80857ALNP-EEM-T2     | —          | —                  | —                  |
| 5.8V±2.0%                      | 0.290                                 | S-80858ALNP-EEN-T2     | —          | —                  | —                  |
| 5.9V±2.0%                      | 0.295                                 | S-80859ALNP-EEP-T2     | —          | —                  | —                  |
| 6.0V±2.0%                      | 0.300                                 | S-80860ALNP-EEQ-T2     | —          | —                  | —                  |

Remark: Some products described here in are under development. Please contact us for Samples.

■ **Output Configurations**

1. S-808 Series model numbering system

|              | Nch open-drain<br>("L" reset type)                               | CMOS output<br>("L" reset type)                                  |
|--------------|------------------------------------------------------------------|------------------------------------------------------------------|
| S-808 Series | "N" is the last letter of the<br>model number.<br>e.g. S-80808AN | "L" is the last letter of the<br>model number.<br>e.g. S-80808AL |

2. Output configurations and their implementation

| Implementation                          | Nch("L") | CMOS("L") |
|-----------------------------------------|----------|-----------|
| With different power supplies           | Yes      | No        |
| With active low reset CPUs              | Yes      | Yes       |
| With active high reset CPUs             | No       | No        |
| With voltage divider variable resistors | Yes      | No        |




Figure 3

## SUPER-SMALL PACKAGE HIGH-PRECISION VOLTAGE DETECTOR

### S-808 Series

#### ■ Absolute Maximum Ratings

- Products with detection voltage of 1.4 V or less

(Unless otherwise specified: Ta=25°C)

| Parameter             |                | Symbol            | Ratings                      | Unit |
|-----------------------|----------------|-------------------|------------------------------|------|
| Power supply voltage  |                | $V_{DD} - V_{SS}$ | 7                            | V    |
| Output voltage        | Nch open-drain | $V_{OUT}$         | $V_{SS}-0.3$ to 7            | V    |
|                       | CMOS           |                   | $V_{SS}-0.3$ to $V_{DD}+0.3$ | V    |
| Output current        |                | $I_{OUT}$         | 50                           | mA   |
| Power dissipation     |                | $P_d$             | 150                          | mW   |
| Operating temperature |                | $T_{opr}$         | -20 to +70                   | °C   |
| Storage temperature   |                | $T_{stg}$         | -40 to +125                  | °C   |

- Products with detection voltage of 1.5 V or more

(Unless otherwise specified: Ta=25°C)

| Parameter             |                | Symbol                            | Ratings                                      | Unit |
|-----------------------|----------------|-----------------------------------|----------------------------------------------|------|
| Power supply voltage  |                | V <sub>DD</sub> - V <sub>SS</sub> | 12                                           | V    |
| Output voltage        | Nch open-drain | V <sub>OUT</sub>                  | V <sub>SS</sub> -0.3 to 12                   | V    |
|                       | CMOS           |                                   | V <sub>SS</sub> -0.3 to V <sub>DD</sub> +0.3 | V    |
| Output current        |                | I <sub>OUT</sub>                  | 50                                           | mA   |
| Power dissipation     | Pd             | TO-92                             | 400                                          | mW   |
|                       |                | SOT-89-3                          | 500                                          |      |
|                       |                | SC-82AB,SOT-23-5                  | 150                                          |      |
| Operating temperature |                | Topr                              | -40 to +85                                   | °C   |
| Storage temperature   |                | Tstg                              | -40 to +125                                  | °C   |

Remark: This IC has a built-in protection circuit for static electricity. However, prevent contact with a large static electricity or electrostatic voltage which exceeds the performance of the protection circuit

# SUPER-SMALL PACKAGE HIGH-PRECISION VOLTAGE DETECTOR

## S-808 Series

### ■ Electrical Characteristics

#### 1. Detection voltage (0.8 V to 1.4 V)

(Unless otherwise specified: Ta=25°C)

| Parameter                                | Symbol                          | Conditions           |                                | Min.  | Typ.  | Max.  | Unit    | Test circuit |
|------------------------------------------|---------------------------------|----------------------|--------------------------------|-------|-------|-------|---------|--------------|
| Detection voltage                        | $-V_{DET}$                      | S-80808AX            |                                | 0.784 | 0.800 | 0.816 | V       | 1            |
|                                          |                                 | S-80809AX            |                                | 0.882 | 0.900 | 0.918 |         |              |
|                                          |                                 | S-80810AX            |                                | 0.980 | 1.000 | 1.020 |         |              |
|                                          |                                 | S-80811AX            |                                | 1.078 | 1.100 | 1.122 |         |              |
|                                          |                                 | S-80812AX            |                                | 1.176 | 1.200 | 1.224 |         |              |
|                                          |                                 | S-80813AX            |                                | 1.274 | 1.300 | 1.326 |         |              |
|                                          |                                 | S-80814AX            |                                | 1.372 | 1.400 | 1.428 |         |              |
| Release voltage                          | $+V_{DET}$                      | S-80808AX            |                                | 0.802 | 0.834 | 0.867 | V       | 1            |
|                                          |                                 | S-80809AX            |                                | 0.910 | 0.944 | 0.979 |         |              |
|                                          |                                 | S-80810AX            |                                | 1.017 | 1.054 | 1.091 |         |              |
|                                          |                                 | S-80811AX            |                                | 1.125 | 1.164 | 1.203 |         |              |
|                                          |                                 | S-80812AX            |                                | 1.232 | 1.273 | 1.315 |         |              |
|                                          |                                 | S-80813AX            |                                | 1.340 | 1.383 | 1.427 |         |              |
|                                          |                                 | S-80814AX            |                                | 1.448 | 1.493 | 1.538 |         |              |
| Hysteresis width                         | $V_{HYS}$                       | S-80808AX            |                                | 0.018 | 0.034 | 0.051 | V       | 1            |
|                                          |                                 | S-80809AX            |                                | 0.028 | 0.044 | 0.061 |         |              |
|                                          |                                 | S-80810AX            |                                | 0.037 | 0.054 | 0.071 |         |              |
|                                          |                                 | S-80811AX            |                                | 0.047 | 0.064 | 0.081 |         |              |
|                                          |                                 | S-80812AX            |                                | 0.056 | 0.073 | 0.091 |         |              |
|                                          |                                 | S-80813AX            |                                | 0.066 | 0.083 | 0.101 |         |              |
|                                          |                                 | S-80814AX            |                                | 0.076 | 0.093 | 0.110 |         |              |
| Current consumption                      | $I_{SS}$                        | $V_{DD}=1.5V$        | S-80808AX                      | —     | 1.3   | 3.7   | $\mu A$ | 2            |
|                                          |                                 |                      | S-80809AX                      |       |       |       |         |              |
|                                          |                                 |                      | S-80810AX                      |       |       |       |         |              |
|                                          |                                 | $V_{DD}=2.0V$        | S-80811AX                      |       |       |       |         |              |
|                                          |                                 |                      | S-80812AX                      |       |       |       |         |              |
|                                          |                                 |                      | S-80813AX                      |       |       |       |         |              |
|                                          |                                 |                      | S-80814AX                      |       |       |       |         |              |
| Operating voltage                        | $V_{DD}$                        |                      |                                | 0.7   | —     | 5.0   | V       | 1            |
| Output current                           | $I_{OUT}$                       | Nch                  | $V_{DS}=0.5V$<br>$V_{DD}=0.7V$ | 0.04  | 0.2   | —     | mA      | 3            |
|                                          |                                 | Pch(CMOS output)     | $V_{DS}=2.1V$<br>$V_{DD}=4.5V$ | 2.9   | 5.8   | —     |         | 4            |
| Leakage current of output transistor     | $I_{LEAK}$                      | Nch(Nch open drain)  | $V_{DS}=5.0V$<br>$V_{DD}=5.0V$ | —     | —     | 60    | nA      | 3            |
| Temperature characteristic of $-V_{DET}$ | $\Delta V_{DET}$<br>$\Delta Ta$ | Ta=-20°C<br>to +70°C | S-80808AX                      | —     | ±0.18 | —     | mV/°C   | 1            |
|                                          |                                 |                      | S-80809AX                      | —     | ±0.20 | —     |         |              |
|                                          |                                 |                      | S-80810AX                      | —     | ±0.22 | —     |         |              |
|                                          |                                 |                      | S-80811AX                      | —     | ±0.24 | —     |         |              |
|                                          |                                 |                      | S-80812AX                      | —     | ±0.27 | —     |         |              |
|                                          |                                 |                      | S-80813AX                      | —     | ±0.29 | —     |         |              |
|                                          |                                 |                      | S-80814AX                      | —     | ±0.31 | —     |         |              |



# SUPER-SMALL PACKAGE HIGH-PRECISION VOLTAGE DETECTOR

## S-808 Series

### 2. Detection voltage (1.5 V to 2.6 V)

(Unless otherwise specified: Ta=25°C)

| Parameter                                | Symbol                               | Conditions                        |                                  | Min.                   | Typ.                   | Max.                   | Unit    | Test circuit |
|------------------------------------------|--------------------------------------|-----------------------------------|----------------------------------|------------------------|------------------------|------------------------|---------|--------------|
| Detection voltage                        | $-V_{DET}$                           | S-80815AX                         |                                  | 1.470                  | 1.500                  | 1.530                  | V       | 1            |
|                                          |                                      | S-80816AX                         |                                  | 1.568                  | 1.600                  | 1.632                  |         |              |
|                                          |                                      | S-80817AX                         |                                  | 1.666                  | 1.700                  | 1.734                  |         |              |
|                                          |                                      | S-80818AX                         |                                  | 1.764                  | 1.800                  | 1.836                  |         |              |
|                                          |                                      | S-80819AX                         |                                  | 1.862                  | 1.900                  | 1.938                  |         |              |
|                                          |                                      | S-80820AX                         |                                  | 1.960                  | 2.000                  | 2.040                  |         |              |
|                                          |                                      | S-80821AX                         |                                  | 2.058                  | 2.100                  | 2.142                  |         |              |
|                                          |                                      | S-80822AX                         |                                  | 2.156                  | 2.200                  | 2.244                  |         |              |
|                                          |                                      | S-80823AX                         |                                  | 2.254                  | 2.300                  | 2.346                  |         |              |
|                                          |                                      | S-80824AX                         |                                  | 2.352                  | 2.400                  | 2.448                  |         |              |
|                                          |                                      | S-80825AX                         |                                  | 2.450                  | 2.500                  | 2.550                  |         |              |
|                                          |                                      | S-80826AX                         |                                  | 2.548                  | 2.600                  | 2.652                  |         |              |
| Hysteresis width                         | $V_{HYS}$                            |                                   |                                  | $-V_{DET} \times 0.03$ | $-V_{DET} \times 0.05$ | $-V_{DET} \times 0.08$ | V       | 1            |
| Current consumption                      | $I_{SS}$                             | $V_{DD}=3.5V$                     |                                  | —                      | 0.8                    | 2.4                    | $\mu A$ | 2            |
| Operating voltage                        | $V_{DD}$                             |                                   |                                  | 0.95                   | —                      | 10.0                   | V       | 1            |
| Output current                           | $I_{OUT}$                            | Nch<br>$V_{DS}=0.5V$              | $V_{DD}=1.2V$                    | 0.23                   | 0.50                   | —                      | mA      | 3            |
|                                          |                                      | Pch(CMOS output)<br>$V_{DS}=0.5V$ | $V_{DD}=4.8V$                    | 0.36                   | 0.62                   | —                      |         | 4            |
| Leakage current of output transistor     | $I_{LEAK}$                           | Nch(Nch open drain)               | $V_{DS}=10.0V$<br>$V_{DD}=10.0V$ | —                      | —                      | 0.1                    | $\mu A$ | 3            |
| Response time                            | tPLH                                 |                                   |                                  | —                      | —                      | 60                     | $\mu s$ | 1            |
| Temperature characteristic of $-V_{DET}$ | $\frac{\Delta -V_{DET}}{\Delta T_a}$ | Ta=-40°C to +85°C                 | S-80815AX                        | —                      | ±0.18                  | ±0.54                  | mV/°C   | 1            |
|                                          |                                      |                                   | S-80816AX                        | —                      | ±0.19                  | ±0.57                  |         |              |
|                                          |                                      |                                   | S-80817AX                        | —                      | ±0.20                  | ±0.60                  |         |              |
|                                          |                                      |                                   | S-80818AX                        | —                      | ±0.21                  | ±0.63                  |         |              |
|                                          |                                      |                                   | S-80819AX                        | —                      | ±0.22                  | ±0.66                  |         |              |
|                                          |                                      |                                   | S-80820AX                        | —                      | ±0.24                  | ±0.72                  |         |              |
|                                          |                                      |                                   | S-80821AX                        | —                      | ±0.25                  | ±0.75                  |         |              |
|                                          |                                      |                                   | S-80822AX                        | —                      | ±0.26                  | ±0.78                  |         |              |
|                                          |                                      |                                   | S-80823AX                        | —                      | ±0.27                  | ±0.81                  |         |              |
|                                          |                                      |                                   | S-80824AX                        | —                      | ±0.28                  | ±0.84                  |         |              |
|                                          |                                      |                                   | S-80825AX                        | —                      | ±0.29                  | ±0.87                  |         |              |
|                                          |                                      |                                   | S-80826AX                        | —                      | ±0.31                  | ±0.93                  |         |              |

**SUPER-SMALL PACKAGE HIGH-PRECISION VOLTAGE DETECTOR**  
**S-808 Series**

3. Detection voltage (2.7 V to 3.9 V)

(Unless otherwise specified: Ta=25°C)

| Parameter                                | Symbol                              | Conditions                                              |                                | Min.               | Typ.                | Max.                | Unit  | Test circuit |
|------------------------------------------|-------------------------------------|---------------------------------------------------------|--------------------------------|--------------------|---------------------|---------------------|-------|--------------|
| Detection voltage                        | $-V_{DET}$                          | S-80827AX                                               |                                | 2.646              | 2.700               | 2.754               | V     | 1            |
|                                          |                                     | S-80828AX                                               |                                | 2.744              | 2.800               | 2.856               |       |              |
|                                          |                                     | S-80829AX                                               |                                | 2.842              | 2.900               | 2.958               |       |              |
|                                          |                                     | S-80830AX                                               |                                | 2.940              | 3.000               | 3.060               |       |              |
|                                          |                                     | S-80831AX                                               |                                | 3.038              | 3.100               | 3.162               |       |              |
|                                          |                                     | S-80832AX                                               |                                | 3.136              | 3.200               | 3.264               |       |              |
|                                          |                                     | S-80833AX                                               |                                | 3.234              | 3.300               | 3.366               |       |              |
|                                          |                                     | S-80834AX                                               |                                | 3.332              | 3.400               | 3.468               |       |              |
|                                          |                                     | S-80835AX                                               |                                | 3.430              | 3.500               | 3.570               |       |              |
|                                          |                                     | S-80836AX                                               |                                | 3.528              | 3.600               | 3.672               |       |              |
|                                          |                                     | S-80837AX                                               |                                | 3.626              | 3.700               | 3.774               |       |              |
|                                          |                                     | S-80838AX                                               |                                | 3.724              | 3.800               | 3.876               |       |              |
|                                          |                                     | S-80839AX                                               |                                | 3.822              | 3.900               | 3.978               |       |              |
| Hysteresis width                         | $V_{HYS}$                           |                                                         |                                | $-V_{DET}$<br>0.03 | $-V_{DET}$<br>×0.05 | $-V_{DET}$<br>×0.08 | V     | 1            |
| Current consumption                      | $I_{SS}$                            | $V_{DD}=4.5V$                                           |                                | —                  | 0.9                 | 2.7                 | μA    | 2            |
| Operating voltage                        | $V_{DD}$                            |                                                         |                                | 0.95               | —                   | 10.0                | V     | 1            |
| Output current                           | $I_{OUT}$                           | Nch                                                     | $V_{DD}=1.2V$                  | 0.23               | 0.50                | —                   | mA    | 3            |
|                                          |                                     |                                                         | $V_{DS}=0.5V$<br>$V_{DD}=2.4V$ | 1.60               | 3.70                | —                   |       |              |
|                                          |                                     | Pch(CMOS output)                                        | $V_{DD}=4.8V$                  | 0.36               | 0.62                | —                   |       | 4            |
|                                          |                                     |                                                         | $V_{DS}=0.5V$                  |                    |                     |                     |       |              |
| Leakage current of output transistor     | $I_{LEAK}$                          | Nch(Nch open drain)<br>$V_{DS}=10.0V$<br>$V_{DD}=10.0V$ |                                | —                  | —                   | 0.1                 | μA    | 3            |
| Response time                            | tPLH                                |                                                         |                                | —                  | —                   | 60                  | μs    | 1            |
| Temperature characteristic of $-V_{DET}$ | $\frac{\Delta -V_{DET}}{\Delta Ta}$ | Ta=-40°C to +85°C                                       | S-80827AX                      | —                  | ±0.32               | ±0.96               | mV/°C | 1            |
|                                          |                                     |                                                         | S-80828AX                      | —                  | ±0.33               | ±0.99               |       |              |
|                                          |                                     |                                                         | S-80829AX                      | —                  | ±0.34               | ±1.02               |       |              |
|                                          |                                     |                                                         | S-80830AX                      | —                  | ±0.35               | ±1.05               |       |              |
|                                          |                                     |                                                         | S-80831AX                      | —                  | ±0.36               | ±1.08               |       |              |
|                                          |                                     |                                                         | S-80832AX                      | —                  | ±0.38               | ±1.14               |       |              |
|                                          |                                     |                                                         | S-80833AX                      | —                  | ±0.39               | ±1.17               |       |              |
|                                          |                                     |                                                         | S-80834AX                      | —                  | ±0.40               | ±1.20               |       |              |
|                                          |                                     |                                                         | S-80835AX                      | —                  | ±0.41               | ±1.23               |       |              |
|                                          |                                     |                                                         | S-80836AX                      | —                  | ±0.42               | ±1.26               |       |              |
|                                          |                                     |                                                         | S-80837AX                      | —                  | ±0.44               | ±1.32               |       |              |
|                                          |                                     |                                                         | S-80838AX                      | —                  | ±0.45               | ±1.35               |       |              |
|                                          |                                     |                                                         | S-80839AX                      | —                  | ±0.46               | ±1.38               |       |              |

# SUPER-SMALL PACKAGE HIGH-PRECISION VOLTAGE DETECTOR

## S-808 Series

### 4. Detection voltage (4.0 V to 5.6 V)

(Unless otherwise specified: Ta=25°C)

| Parameter                                | Symbol                              | Conditions                                              | Min.                   | Typ.                   | Max.                   | Unit    | Test circuit |
|------------------------------------------|-------------------------------------|---------------------------------------------------------|------------------------|------------------------|------------------------|---------|--------------|
| Detection voltage                        | $-V_{DET}$                          | S-80840AX                                               | 3.920                  | 4.000                  | 4.080                  | V       | 1            |
|                                          |                                     | S-80841AX                                               | 4.018                  | 4.100                  | 4.182                  |         |              |
|                                          |                                     | S-80842AX                                               | 4.116                  | 4.200                  | 4.284                  |         |              |
|                                          |                                     | S-80843AX                                               | 4.214                  | 4.300                  | 4.386                  |         |              |
|                                          |                                     | S-80844AX                                               | 4.312                  | 4.400                  | 4.488                  |         |              |
|                                          |                                     | S-80845AX                                               | 4.410                  | 4.500                  | 4.590                  |         |              |
|                                          |                                     | S-80846AX                                               | 4.508                  | 4.600                  | 4.692                  |         |              |
|                                          |                                     | S-80847AX                                               | 4.606                  | 4.700                  | 4.794                  |         |              |
|                                          |                                     | S-80848AX                                               | 4.704                  | 4.800                  | 4.896                  |         |              |
|                                          |                                     | S-80849AX                                               | 4.802                  | 4.900                  | 4.998                  |         |              |
|                                          |                                     | S-80850AX                                               | 4.900                  | 5.000                  | 5.100                  |         |              |
|                                          |                                     | S-80851AX                                               | 4.998                  | 5.100                  | 5.202                  |         |              |
|                                          |                                     | S-80852AX                                               | 5.096                  | 5.200                  | 5.304                  |         |              |
|                                          |                                     | S-80853AX                                               | 5.194                  | 5.300                  | 5.406                  |         |              |
|                                          |                                     | S-80854AX                                               | 5.292                  | 5.400                  | 5.508                  |         |              |
|                                          |                                     | S-80855AX                                               | 5.390                  | 5.500                  | 5.610                  |         |              |
|                                          |                                     | S-80856AX                                               | 5.488                  | 5.600                  | 5.712                  |         |              |
| Hysteresis width                         | $V_{HYS}$                           |                                                         | $-V_{DET} \times 0.03$ | $-V_{DET} \times 0.05$ | $-V_{DET} \times 0.08$ | V       | 1            |
| Current consumption                      | $I_{SS}$                            | $V_{DD}=6.0V$                                           | —                      | 1.0                    | 3.0                    | $\mu A$ | 2            |
| Operating voltage                        | $V_{DD}$                            |                                                         | 0.95                   | —                      | 10.0                   | V       | 1            |
| Output current                           | $I_{OUT}$                           | Nch<br>$V_{DS}=0.5V$                                    | $V_{DD}=1.2V$<br>0.23  | 0.50                   | —                      | mA      | 3            |
|                                          |                                     |                                                         | $V_{DD}=2.4V$<br>1.60  | 3.70                   | —                      |         |              |
|                                          |                                     | Pch(CMOS output)<br>$V_{DS}=0.5V$                       | $V_{DD}=6.0V$<br>0.46  | 0.75                   | —                      |         | 4            |
| Leakage current of output transistor     | $I_{LEAK}$                          | Nch(Nch open drain)<br>$V_{DS}=10.0V$<br>$V_{DD}=10.0V$ | —                      | —                      | 0.1                    | $\mu A$ | 3            |
| Response time                            | tPLH                                |                                                         | —                      | —                      | 60                     | $\mu s$ | 1            |
| Temperature characteristic of $-V_{DET}$ | $\frac{\Delta -V_{DET}}{\Delta Ta}$ | Ta=-40°C to +85°C                                       | S-80840AX              | —                      | $\pm 0.47$             | mV/°C   | 1            |
|                                          |                                     |                                                         | S-80841AX              | —                      | $\pm 0.48$             |         |              |
|                                          |                                     |                                                         | S-80842AX              | —                      | $\pm 0.49$             |         |              |
|                                          |                                     |                                                         | S-80843AX              | —                      | $\pm 0.51$             |         |              |
|                                          |                                     |                                                         | S-80844AX              | —                      | $\pm 0.52$             |         |              |
|                                          |                                     |                                                         | S-80845AX              | —                      | $\pm 0.53$             |         |              |
|                                          |                                     |                                                         | S-80846AX              | —                      | $\pm 0.54$             |         |              |
|                                          |                                     |                                                         | S-80847AX              | —                      | $\pm 0.55$             |         |              |
|                                          |                                     |                                                         | S-80848AX              | —                      | $\pm 0.56$             |         |              |
|                                          |                                     |                                                         | S-80849AX              | —                      | $\pm 0.58$             |         |              |
|                                          |                                     |                                                         | S-80850AX              | —                      | $\pm 0.59$             |         |              |
|                                          |                                     |                                                         | S-80851AX              | —                      | $\pm 0.60$             |         |              |
|                                          |                                     |                                                         | S-80852AX              | —                      | $\pm 0.61$             |         |              |
|                                          |                                     |                                                         | S-80853AX              | —                      | $\pm 0.62$             |         |              |
|                                          |                                     |                                                         | S-80854AX              | —                      | $\pm 0.64$             |         |              |
|                                          |                                     |                                                         | S-80855AX              | —                      | $\pm 0.65$             |         |              |
|                                          |                                     |                                                         | S-80856AX              | —                      | $\pm 0.66$             |         |              |

# SUPER-SMALL PACKAGE HIGH-PRECISION VOLTAGE DETECTOR

## S-808 Series


### 5. Detection voltage (5.7 V to 6.0 V)

(Unless otherwise specified:  $T_a=25^\circ\text{C}$ )

| Parameter                                       | Symbol                                      | Conditions                                                                          | Min.                                | Typ.                          | Max.                          | Unit                       | Test circuit |
|-------------------------------------------------|---------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------|-------------------------------|-------------------------------|----------------------------|--------------|
| Detection voltage                               | $-V_{\text{DET}}$                           | S-80857AX                                                                           | 5.586                               | 5.700                         | 5.814                         | V                          | 1            |
|                                                 |                                             | S-80858AX                                                                           | 5.684                               | 5.800                         | 5.916                         |                            |              |
|                                                 |                                             | S-80859AX                                                                           | 5.782                               | 5.900                         | 6.018                         |                            |              |
|                                                 |                                             | S-80860AX                                                                           | 5.880                               | 6.000                         | 6.120                         |                            |              |
| Hysteresis width                                | $V_{\text{HYS}}$                            |                                                                                     | $-V_{\text{DET}} \times 0.03$       | $-V_{\text{DET}} \times 0.05$ | $-V_{\text{DET}} \times 0.08$ | V                          | 1            |
| Current consumption                             | $I_{\text{SS}}$                             | $V_{\text{DD}}=7.5\text{V}$                                                         | —                                   | 1.0                           | 3.0                           | $\mu\text{A}$              | 2            |
| Operating voltage                               | $V_{\text{DD}}$                             |                                                                                     | 0.95                                | —                             | 10.0                          | V                          | 1            |
| Output current                                  | $I_{\text{OUT}}$                            | Nch<br>$V_{\text{DS}}=0.5\text{V}$                                                  | $V_{\text{DD}}=1.2\text{V}$<br>0.23 | 0.50                          | —                             | mA                         | 3            |
|                                                 |                                             |                                                                                     | $V_{\text{DD}}=2.4\text{V}$<br>1.60 | 3.70                          | —                             |                            |              |
|                                                 |                                             | Pch(CMOS output)<br>$V_{\text{DS}}=0.5\text{V}$                                     | $V_{\text{DD}}=8.4\text{V}$<br>0.59 | 0.96                          | —                             |                            | 4            |
|                                                 |                                             |                                                                                     |                                     |                               |                               |                            |              |
| Leakage current of output transistor            | $I_{\text{LEAK}}$                           | Nch(Nch open drain)<br>$V_{\text{DS}}=10.0\text{V}$<br>$V_{\text{DD}}=10.0\text{V}$ | —                                   | —                             | 0.1                           | $\mu\text{A}$              | 3            |
| Response time                                   | $t_{\text{PLH}}$                            |                                                                                     | —                                   | —                             | 60                            | $\mu\text{s}$              | 1            |
| Temperature characteristic of $-V_{\text{DET}}$ | $\frac{\Delta -V_{\text{DET}}}{\Delta T_a}$ | $T_a=-40^\circ\text{C}$<br>to $+85^\circ\text{C}$                                   | S-80857AX                           | —                             | $\pm 0.67$                    | $\text{mV}/^\circ\text{C}$ | 1            |
|                                                 |                                             |                                                                                     | S-80858AX                           | —                             | $\pm 0.68$                    |                            |              |
|                                                 |                                             |                                                                                     | S-80859AX                           | —                             | $\pm 0.69$                    |                            |              |
|                                                 |                                             |                                                                                     | S-80860AX                           | —                             | $\pm 0.71$                    |                            |              |


### ■ Test Circuits

(1)




\* R is unnecessary for CMOS output products.

(2)



(3)



(4)




Figure 4

## SUPER-SMALL PACKAGE HIGH-PRECISION VOLTAGE DETECTOR

### S-808 Series

#### ■ Technical Terms

##### 1. Detection voltage ( $-V_{DET}$ )

The detection voltage  $-V_{DET}$  is the voltage at which the output switches to low. This detection voltage varies slightly among products of the same type. The variation of voltages between the specified minimum  $[(-V_{DET})_{min.}]$  and maximum  $[(-V_{DET})_{max.}]$  values is called the detection voltage range (See Figure 5).

**Example :** For the S-80808AN, detection voltage lies in the range of  $0.784 \leq (-V_{DET}) \leq 0.816$ .

This means that  $-V_{DET}$  is 0.784 in a product while  $-V_{DET}$  is 0.816 in another of the same S-80808AN.

##### 2. Release voltage ( $+V_{DET}$ )

The release voltage  $+V_{DET}$  is the voltage at which the output returns (is “released”) to high. This release voltage varies slightly among products of the same type. The variation of voltages between the specified minimum  $[(+V_{DET})_{min.}]$  and maximum  $[(+V_{DET})_{max.}]$  values is called the release voltage range (See Figure 6).

**Example :** For the S-80808AN, the release voltage lies in the range of  $0.802 \leq (+V_{DET}) \leq 0.867$ . This means that  $+V_{DET}$  is 0.802 in a product while  $+V_{DET}$  is 0.867 in another of the same S-80808AN.

**Remark:** Although the detection voltage and release voltage overlap in the range of 0.802 V to 0.816 V,  $+V_{DET}$  will always be larger than  $-V_{DET}$ .




Figure 5




Figure 6

##### 3. Hysteresis width ( $V_{HYS}$ )

The hysteresis width is the voltage difference between the detection voltage and the release voltage ( $B-A=V_{HYS}$  in Figure 10). By giving a device hysteresis, trouble such as noise at the input is avoided.

##### 4. Through-type current

Through-type current refers to the current which flows instantaneously at the time of detection and release of a voltage detector. Through-type current is large in CMOS output devices, and also flows to some extent in Nch open-drain output devices.

## 5. Oscillation

In applications where a resistor is connected to the voltage detector input (Figure 7), in the CMOS active low products for example, the through-type current generated when the output goes from low to high (release) causes a voltage drop equal to [through-type current]×[input resistance] across the resistor. When the resultant input voltage drops below the detection voltage  $-V_{DET}$ , the output voltage returns to its low level. In this state, the through-type current and its resultant voltage drop have disappeared, and the output goes back from low to high. A through-type current is again generated, a voltage drop appears, and the process repeats. This unstable condition is referred to as oscillation.

- Misimplementation with input voltage divider




Figure 7

## ■ Standard Circuit




Figure 8

# SUPER-SMALL PACKAGE HIGH-PRECISION VOLTAGE DETECTOR

## S-808 Series

### ■ Operation

#### 1. Basic operation : CMOS active low output

- (1) When power supply voltage  $V_{DD}$  is greater than the release voltage  $+V_{DET}$ , the Nch transistor is OFF and the Pch transistor ON, causing  $V_{DD}$  (high) to appear at the output. With the Nch transistor N1 of Figure 9 OFF, the comparator input voltage is  $(RB+RC)/(RA+RB+RC) \times V_{DD}$ .
- (2) When power supply voltage  $V_{DD}$  goes below  $+V_{DET}$ , the output maintains the power supply voltage level, as long as  $V_{DD}$  remains above the detection voltage  $-V_{DET}$ . When  $V_{DD}$  does fall below  $-V_{DET}$  (A in Figure 10), the Nch transistor goes ON, the Pch transistor goes OFF, and  $V_{SS}$  appears at the output. With the Nch transistor N 1 of Figure 9 ON, the comparator input voltage is  $RB/(RA+RB) \times V_{DD}$ .
- (3) When  $V_{DD}$  falls below the minimum operating voltage, the output becomes undefined. However, output will revert to  $V_{DD}$  if a pull-up has been employed.
- (4)  $V_{SS}$  will again be output when  $V_{DD}$  rises above the minimum operating voltage.  $V_{SS}$  will continue to be output even when  $V_{DD}$  surpasses  $-V_{DET}$ , as long as it does not exceed the release voltage  $+V_{DET}$ .
- (5) When  $V_{DD}$  rises above  $+V_{DET}$  (B in Figure 10), the Nch transistor goes OFF, the Pch transistor goes ON, and  $V_{DD}$  appears at the output.




Figure 9





Figure 10

2. Other characteristics

(1) Temperature characteristic of detection voltage

The temperature characteristics of the detection voltage are expressed by the oblique line parts in Figure 11.

S-80815AXNP:



**Figure 11**

(2) Temperature characteristics of release voltage

The temperature factor  $\left(\frac{\Delta+V_{DET}}{\Delta T_a}\right)$  of the release voltage is calculated by the temperature factor of the detection voltage as follows:

$$\frac{\Delta+V_{DET}}{\Delta T_a} = \frac{+V_{DET}}{-V_{DET}} \times \frac{\Delta-V_{DET}}{\Delta T_a}$$

The temperature factor of the release voltage has a same sign characteristics as the temperature factor of the detection voltage.

(3) Temperature characteristics of hysteresis voltage

The temperature characteristics of hysteresis voltage  $\left(\frac{\Delta+V_{DET}}{\Delta T_a} - \frac{\Delta-V_{DET}}{\Delta T_a}\right)$  is calculated as

$$\frac{\Delta+V_{DET}}{\Delta T_a} - \frac{\Delta-V_{DET}}{\Delta T_a} = \frac{V_{HY}}{-V_{DET}} \times \frac{\Delta-V_{DET}}{\Delta T_a}$$


Remark: An example of temperature characteristics of (1) to (3) is shown on pages 21 and 22.



SUPER-SMALL PACKAGE HIGH-PRECISION VOLTAGE DETECTOR  
S-808 Series


■ Dimensions

(1) SC-82AB




The surface of lead wire is plated or dipped with solder.


(2) TO-92



(3) SOT-89-3



(4) SOT-23-5



Unit: mm

Figure 12

■ Taping

1.SC-82AB

1.1 Tape specifications




Figure 13

1.2 Reel specifications

1 reel holds 3000 detectors.




Figure 14

**SUPER-SMALL PACKAGE HIGH-PRECISION VOLTAGE DETECTOR**  
**S-808 Series**

2. SOT-89-3

2.1 Tape specifications

There are two color (white and blue) labels depending upon the presence of holes at center of the emboss.

Two types of tape (T1 and T2) are available depending upon the direction of the IC on the tape.





Figure 15

## 2.2 Reel specifications


1 reel holds 1000 detectors.



## 3. SOT-23-5

### 3.1 Tape specifications

The emboss cover tape comes in two tones (milk white/transparent and transparent).



SUPER-SMALL PACKAGE HIGH-PRECISION VOLTAGE DETECTOR

S-808 Series

3.2 Reel Specifications

1 reel holds 3000 detectors.





Figure 18

■ Marking

1. SC-82AB




(1) to (3) Product name (abbreviation)  
(4) to (11) Lot No. (indicated by dots)

3. SOT-89-3


(1) White label

(2) Blue label




① Product name (abbreviation)  
② Lot No.

2. TO-92



① Product name  
② Last digit of the year  
③ Lot No.

4. SOT-23-5







① and ② Product name (abbreviation)  
③ and ④ Lot No.  
③: Alphabet  
④: Dot on one side

Figure 19


■ **Characteristics** (typical characteristics)

(1) Detection voltage ( $V_{DET}$ ) - Temperature ( $T_a$ )




**SUPER-SMALL PACKAGE HIGH-PRECISION VOLTAGE DETECTOR**  
**S-808 Series**





(2) Hysteresis voltage width ( $V_{HYS}$ ) - Temperature ( $T_a$ )



(3) Current consumption ( $I_{SS}$ ) - Input voltage ( $V_{DD}$ )



(4) Current consumption ( $I_{SS}$ ) - Temperature ( $T_a$ )







**SUPER-SMALL PACKAGE HIGH-PRECISION VOLTAGE DETECTOR**  
**S-808 Series**

(5) Nch transistor output current ( $I_{OUT}$ ) -  $V_{DS}$

(a) S-80814AL




(b) S-80860AL




(6) Pch transistor output current ( $I_{OUT}$ ) -  $V_{DS}$

(a) S-80808AL




(b) S-80815AL




(7) Nch transistor output current ( $I_{OUT}$ ) - Input voltage ( $V_{DD}$ )


(a) S-80814AL




(b) S-80860AL



(8) Pch transistor output current( $I_{OUT}$ ) - Input voltage( $V_{DD}$ )




(9) Minimum operating voltage



Remark:







$V_{DDMIN}$  is defined with  $V_{DD}$  when  $V_{OUT}$  goes below 10% of the PULL UP voltage as shown in Figure 20 when raising  $V_{DD}$  from 0 V.




**Figure 20**

**SUPER-SMALL PACKAGE HIGH-PRECISION VOLTAGE DETECTOR**  
**S-808 Series**

(10) Dynamic response





**Figure 22**

**Figure 21**

SUPER-SMALL PACKAGE HIGH-PRECISION VOLTAGE DETECTOR  
S-808 Series

■ Application Circuit Examples

1. Microcomputer reset circuits

If the power supply voltage to a microcomputer falls below the specified level, an unspecified operation may be performed or the contents of the memory register may be lost. When power supply voltage returns to normal, the microcomputer needs to be initialized before normal operations can be done.

Reset circuits protect microcomputers in the event of current being momentarily switched off or lowered. With the S-808 Series which has a low operating voltage, a high-precision detection voltage and hysteresis characteristic, the reset circuits shown in Figures 19 to 20 can be easily constructed.




Figure 23





Figure 24

2. Addition of power-on reset circuit

A power-on reset circuit can be constructed using Nch open-drain product of S-808 Series.



- Note 1:  $R$  should be  $75\text{ k}\Omega$  or less for purpose of protection against oscillation.  
Note 2:  $D_i$  instantaneously discharges the electric charge stored by  $C$  at the falling of the power.  
 $D_i$  is not necessary if delay in falling time is normal.




Figure 25


- Note 3: When the power steeply rises, output may goes high for a instant due to the IC inconstant region characteristics (output voltage is unstable in the region under minimum operating voltage) as shown in Figure. 26.



Figure 26

### 3. Change of detection voltage

In Nch open-drain output products of the S-808 Series, detection voltage can be changed using resistance dividers or diodes as shown in Figures 27 and 28. In Figure 27, hysteresis width is also changed.




$$\text{Detection voltage} = \frac{RA+RB}{RB} \cdot -V_{DET}$$

$$\text{Hysteresis width} = \frac{RA+RB}{RB} \cdot V_{HYS}$$

Note1: If RA and RB are large, the hysteresis width may be larger than the value given by the formula above due to through-type current (which flows slightly in Nch open-drain circuit).

Note2: RA should be 75kΩ or less for purpose of protection against oscillation.

**Figure 27**



$$\text{Detection voltage} = V_{f1} + V_{f2} + (-V_{DET})$$

**Figure 28**

### ■ Remarks

- In CMOS output products of the S-808 Series, through-type current flows when the device is detecting or releasing. If a high impedance is connected to the input, oscillation may be caused due to the fall of the voltage by the through-type current when lowering the voltage during releasing.
- When designing for mass production using an application circuit described herein, take the product deviation and temperature characteristic into consideration.
- Seiko Instruments Inc. shall not bear any responsibility for the patents on the circuits described herein.

# Collection of Product FAQs

Author: Imura Yukihiro

Date : 99/05/27 (Thursday) 13:43 (Modified: 99/05/28 (Friday) 09:55)

## <Information level>

A: Public (Printing O.K.)

Index: A: General

## <Product>

Division name: 01 IC

Category 1: 11 Power Supply

Category 2: 1. Voltage Detectors

Cal No.: S-808

Related Documents:

## Question:

What is the table for S-8053/S-8054 series to S-808 series replacement?

## Answer:

Use the following table as a guide.

| Type       | Upper Line:S-805<br>Lower Line: S-808 | Package | Detection Voltage (V) |       |       | Release Voltage (V) |       |       | Operation Voltage (V) |     |      | Point to be noted |
|------------|---------------------------------------|---------|-----------------------|-------|-------|---------------------|-------|-------|-----------------------|-----|------|-------------------|
|            |                                       |         | Min                   | Typ   | Max   | Min                 | Typ   | Max   | Min                   | Typ | Max  |                   |
| S-8053ALB  |                                       | TO-92   | 2.795                 | 2.950 | 3.105 | 2.851               | 3.098 | 3.353 | 1.6                   | —   | 10.0 |                   |
| S-80829ALY |                                       | TO-92   | 2.842                 | 2.900 | 2.958 | 2.927               | 3.045 | 3.195 | 0.95                  | —   | 10.0 |                   |

|                 |  |          |       |       |       |       |       |       |      |   |      |  |
|-----------------|--|----------|-------|-------|-------|-------|-------|-------|------|---|------|--|
| S-8053ALB-LI    |  | SOT-89-3 | 2.795 | 2.950 | 3.105 | 2.851 | 3.098 | 3.353 | 1.6  | — | 10.0 |  |
| S-80829ALUP-EAS |  | SOT-89-3 | 2.842 | 2.900 | 2.958 | 2.927 | 3.045 | 3.195 | 0.95 | — | 10.0 |  |

|            |  |       |       |       |       |       |       |       |      |   |      |  |
|------------|--|-------|-------|-------|-------|-------|-------|-------|------|---|------|--|
| S-8053HLB  |  | TO-92 | 2.895 | 3.000 | 3.105 | 2.953 | 3.150 | 3.353 | 1.6  | — | 10.0 |  |
| S-80830ALY |  | TO-92 | 2.940 | 3.000 | 3.060 | 3.028 | 3.150 | 3.305 | 0.95 | — | 10.0 |  |

|            |  |       |       |       |       |       |       |       |      |   |      |  |
|------------|--|-------|-------|-------|-------|-------|-------|-------|------|---|------|--|
| S-8053HNB  |  | TO-92 | 2.895 | 3.000 | 3.105 | 2.953 | 3.150 | 3.353 | 1.6  | — | 10.0 |  |
| S-80830ANY |  | TO-92 | 2.940 | 3.000 | 3.060 | 3.028 | 3.150 | 3.305 | 0.95 | — | 10.0 |  |

|            |  |       |       |       |       |       |       |       |      |   |      |  |
|------------|--|-------|-------|-------|-------|-------|-------|-------|------|---|------|--|
| S-8053ALR  |  | TO-92 | 3.095 | 3.250 | 3.405 | 3.157 | 3.413 | 3.677 | 1.6  | — | 10.0 |  |
| S-80832ALY |  | TO-92 | 3.136 | 3.200 | 3.264 | 3.230 | 3.360 | 3.525 | 0.95 | — | 10.0 |  |

|                 |          |       |       |       |       |       |       |      |   |      |  |
|-----------------|----------|-------|-------|-------|-------|-------|-------|------|---|------|--|
| S-8053ALR-LJ    | SOT-89-3 | 3.095 | 3.250 | 3.405 | 3.157 | 3.413 | 3.677 | 1.6  | — | 10.0 |  |
| S-80832ALUP-EAW | SOT-89-3 | 3.136 | 3.200 | 3.264 | 3.230 | 3.360 | 3.525 | 0.95 | — | 10.0 |  |

|            |       |       |       |       |       |       |       |      |   |      |  |
|------------|-------|-------|-------|-------|-------|-------|-------|------|---|------|--|
| S-8053ANO  | TO-92 | 3.395 | 3.550 | 3.705 | 3.463 | 3.728 | 4.001 | 1.6  | — | 10.0 |  |
| S-80835ANY | TO-92 | 3.430 | 3.500 | 3.570 | 3.533 | 3.675 | 3.856 | 0.95 | — | 10.0 |  |

|            |       |       |       |       |       |       |       |      |   |      |  |
|------------|-------|-------|-------|-------|-------|-------|-------|------|---|------|--|
| S-8054ALB  | TO-92 | 3.995 | 4.150 | 4.305 | 4.075 | 4.358 | 4.649 | 1.6  | — | 10.0 |  |
| S-80841ALY | TO-92 | 4.018 | 4.100 | 4.182 | 4.139 | 4.305 | 4.517 | 0.95 | — | 10.0 |  |

|                 |          |       |       |       |       |       |       |      |   |      |  |
|-----------------|----------|-------|-------|-------|-------|-------|-------|------|---|------|--|
| S-8054ALB-LM    | SOT-89-3 | 3.995 | 4.150 | 4.305 | 4.075 | 4.358 | 4.649 | 1.6  | — | 10.0 |  |
| S-80841ALUP-EA5 | SOT-89-3 | 4.018 | 4.100 | 4.182 | 4.139 | 4.305 | 4.517 | 0.95 | — | 10.0 |  |

|            |       |       |       |       |       |       |       |      |   |      |  |
|------------|-------|-------|-------|-------|-------|-------|-------|------|---|------|--|
| S-8054ALR  | TO-92 | 4.295 | 4.450 | 4.605 | 4.381 | 4.673 | 4.973 | 1.6  | — | 10.0 |  |
| S-80844ALY | TO-92 | 4.312 | 4.400 | 4.488 | 4.441 | 4.620 | 4.847 | 0.95 | — | 10.0 |  |

|                 |          |       |       |       |       |       |       |      |   |      |  |
|-----------------|----------|-------|-------|-------|-------|-------|-------|------|---|------|--|
| S-8054ALR-LN    | SOT-89-3 | 4.295 | 4.450 | 4.605 | 4.381 | 4.673 | 4.973 | 1.6  | — | 10.0 |  |
| S-80844ALUP-EA8 | SOT-89-3 | 4.312 | 4.400 | 4.488 | 4.441 | 4.620 | 4.847 | 0.95 | — | 10.0 |  |

|            |       |       |       |       |       |       |       |      |   |      |  |
|------------|-------|-------|-------|-------|-------|-------|-------|------|---|------|--|
| S-8054ALO  | TO-92 | 4.595 | 4.750 | 4.905 | 4.687 | 4.988 | 5.297 | 1.6  | — | 10.0 |  |
| S-80847ALY | TO-92 | 4.606 | 4.700 | 4.794 | 4.744 | 4.935 | 5.178 | 0.95 | — | 10.0 |  |

|                 |          |       |       |       |       |       |       |      |   |      |  |
|-----------------|----------|-------|-------|-------|-------|-------|-------|------|---|------|--|
| S-8054ALO-LO    | SOT-89-3 | 4.595 | 4.750 | 4.905 | 4.687 | 4.988 | 5.297 | 1.6  | — | 10.0 |  |
| S-80847ALUP-EEB | SOT-89-3 | 4.606 | 4.700 | 4.794 | 4.744 | 4.935 | 5.178 | 0.95 | — | 10.0 |  |

|            |       |       |       |       |       |       |       |      |   |      |  |
|------------|-------|-------|-------|-------|-------|-------|-------|------|---|------|--|
| S-8054ALY  | TO-92 | 4.895 | 5.100 | 5.205 | 4.993 | 5.355 | 5.621 | 1.6  | — | 10.0 |  |
| S-80851ALY | TO-92 | 4.998 | 5.100 | 5.202 | 5.148 | 5.355 | 5.618 | 0.95 | — | 10.0 |  |

|                 |          |       |       |       |       |       |       |      |   |      |  |
|-----------------|----------|-------|-------|-------|-------|-------|-------|------|---|------|--|
| S-8054ALY-LP    | SOT-89-3 | 4.895 | 5.100 | 5.205 | 4.993 | 5.355 | 5.621 | 1.6  | — | 10.0 |  |
| S-80851ALUP-EEF | SOT-89-3 | 4.998 | 5.100 | 5.202 | 5.148 | 5.355 | 5.618 | 0.95 | — | 10.0 |  |

|            |       |       |       |       |       |       |       |      |   |      |  |
|------------|-------|-------|-------|-------|-------|-------|-------|------|---|------|--|
| S-8054HNN  | TO-92 | 3.800 | 4.000 | 4.200 | 3.876 | 4.200 | 4.536 | 1.6  | — | 10.0 |  |
| S-80839ANY | TO-92 | 3.822 | 3.900 | 3.978 | 3.937 | 4.095 | 4.296 | 0.95 | — | 10.0 |  |

|                 |          |       |       |       |       |       |       |      |   |      |  |
|-----------------|----------|-------|-------|-------|-------|-------|-------|------|---|------|--|
| S-8054HNN-CB    | SOT-89-3 | 3.800 | 4.000 | 4.200 | 3.876 | 4.200 | 4.536 | 1.6  | — | 10.0 |  |
| S-80839ANUP-ED3 | SOT-89-3 | 3.822 | 3.900 | 3.978 | 3.937 | 4.095 | 4.296 | 0.95 | — | 10.0 |  |



|                 |          |       |       |       |       |       |       |      |   |      |                                 |
|-----------------|----------|-------|-------|-------|-------|-------|-------|------|---|------|---------------------------------|
| S-8054HNM       | TO-92    | 4.500 | 4.600 | 4.700 | —     | 4.650 | 4.800 | 1.6  | — | 10.0 |                                 |
| S-80846ANY      | TO-92    | 4.508 | 4.600 | 4.692 | 4.643 | 4.830 | 5.067 | 0.95 | — | 10.0 | Max. value of release voltage   |
| S-80845ANY      | TO-92    | 4.410 | 4.500 | 4.590 | 4.542 | 4.725 | 4.957 | 0.95 | — | 10.0 | Max. value of release voltage   |
| S-80844ANY      | TO-92    | 4.312 | 4.400 | 4.488 | 4.441 | 4.620 | 4.847 | 0.95 | — | 10.0 | Min. value of detection voltage |
|                 |          |       |       |       |       |       |       |      |   |      |                                 |
| S-8054HNM-CQ    | SOT-89-3 | 4.500 | 4.600 | 4.700 | —     | 4.650 | 4.800 | 1.6  | — | 10.0 |                                 |
| S-80846ANUP-EJA | SOT-89-3 | 4.508 | 4.600 | 4.692 | 4.643 | 4.830 | 5.067 | 0.95 | — | 10.0 | Max. value of release voltage   |
| S-80845ANUP-ED9 | SOT-89-3 | 4.410 | 4.500 | 4.590 | 4.542 | 4.725 | 4.957 | 0.95 | — | 10.0 | Max. value of release voltage   |
| S-80844ANUP-ED8 | SOT-89-3 | 4.312 | 4.400 | 4.488 | 4.441 | 4.620 | 4.847 | 0.95 | — | 10.0 | Min. value of detection voltage |

The production of the S8054HNM will be continued, but this product cannot be newly employed.

<Remarks>

FAQ No.: 11S808002

# Collection of Product FAQs

Author: Imura Yukihiro

Date: 99/05/27 (Thursday) 13:12 (Modified: 99/05/27 (Thursday) 13:37)

<Information level>

A: Public (Printing O.K.)

Index: A: General

<Product>

Division name: 01 IC

Category 1: 11 Power Supply

Category 2: 1. Voltage Detectors

Cal No.: S-808

Related Documents:

## Question:

What is the table for S-8051/S-8052 series to S-808 series replacement?

## Answer:

Use the following table as a guide.

| Type            | Upper Line: S-805<br>Lower Line: S-808 | Package | Detection Voltage (V) |       |       | Release Voltage (V) |       |       | Operation Voltage (V) |     |     | Point to be noted     |
|-----------------|----------------------------------------|---------|-----------------------|-------|-------|---------------------|-------|-------|-----------------------|-----|-----|-----------------------|
|                 |                                        |         | Min                   | Typ   | Max   | Min                 | Typ   | Max   | Min                   | Typ | Max |                       |
| S-8051ANB       |                                        | TO-92   | 0.995                 | 1.050 | 1.105 | 1.015               | 1.103 | 1.193 | 0.9                   | —   | 5.0 |                       |
| S-80810ANNP-E70 |                                        | SC-82AB | 0.980                 | 1.000 | 1.020 | 1.017               | 1.054 | 1.091 | 0.7                   | —   | 5.0 | Difference in package |

|                 |  |          |       |       |       |       |       |       |     |   |     |                       |
|-----------------|--|----------|-------|-------|-------|-------|-------|-------|-----|---|-----|-----------------------|
| S-8051ANB-NA    |  | SOT-89-3 | 0.995 | 1.050 | 1.105 | 1.015 | 1.103 | 1.193 | 0.9 | — | 5.0 |                       |
| S-80810ANNP-E70 |  | SC-82AB  | 0.980 | 1.000 | 1.020 | 1.017 | 1.054 | 1.091 | 0.7 | — | 5.0 | Difference in package |

|                 |  |         |       |       |       |       |       |       |     |   |     |                       |
|-----------------|--|---------|-------|-------|-------|-------|-------|-------|-----|---|-----|-----------------------|
| S-8051ANR       |  | TO-92   | 1.095 | 1.150 | 1.205 | 1.117 | 1.208 | 1.301 | 1.0 | — | 5.0 |                       |
| S-80811ANNP-E71 |  | SC-82AB | 1.078 | 1.100 | 1.122 | 1.125 | 1.164 | 1.203 | 0.7 | — | 5.0 | Difference in package |

|                 |  |          |       |       |       |       |       |       |     |   |     |                       |
|-----------------|--|----------|-------|-------|-------|-------|-------|-------|-----|---|-----|-----------------------|
| S-8051ANR-NB    |  | SOT-89-3 | 1.095 | 1.150 | 1.205 | 1.117 | 1.208 | 1.301 | 1.0 | — | 5.0 |                       |
| S-80811ANNP-E71 |  | SC-82AB  | 1.078 | 1.100 | 1.122 | 1.125 | 1.164 | 1.203 | 0.7 | — | 5.0 | Difference in package |

|                 |  |          |       |       |       |       |       |       |      |   |      |  |
|-----------------|--|----------|-------|-------|-------|-------|-------|-------|------|---|------|--|
| S-8051HN-CD     |  | SOT-89-3 | 1.795 | 1.900 | 2.005 | 1.831 | 1.995 | 2.165 | 1.5  | — | 10.0 |  |
| S-80819ANUP-EDG |  | SOT-89-3 | 1.862 | 1.900 | 1.938 | 1.918 | 1.995 | 2.093 | 0.95 | — | 10.0 |  |

|                 |          |       |       |       |       |       |       |      |   |      |  |
|-----------------|----------|-------|-------|-------|-------|-------|-------|------|---|------|--|
| S-8052ANB-NE    | SOT-89-3 | 1.995 | 2.100 | 2.205 | 2.035 | 2.205 | 2.381 | 1.5  | — | 10.0 |  |
| S-80821ANUP-EDJ | SOT-89-3 | 2.058 | 2.100 | 2.142 | 2.120 | 2.205 | 2.313 | 0.95 | — | 10.0 |  |

|            |       |       |       |       |       |       |       |      |   |      |  |
|------------|-------|-------|-------|-------|-------|-------|-------|------|---|------|--|
| S-8052ALB  | TO-92 | 1.995 | 2.100 | 2.205 | 2.035 | 2.205 | 2.381 | 1.5  | — | 10.0 |  |
| S-80821ALY | TO-92 | 2.058 | 2.100 | 2.142 | 2.120 | 2.205 | 2.313 | 0.95 | — | 10.0 |  |

|                 |          |       |       |       |       |       |       |      |   |      |  |
|-----------------|----------|-------|-------|-------|-------|-------|-------|------|---|------|--|
| S-8052ALB-LE    | SOT-89-3 | 1.995 | 2.100 | 2.205 | 2.035 | 2.205 | 2.381 | 1.5  | — | 10.0 |  |
| S-80821ALUP-EAJ | SOT-89-3 | 2.058 | 2.100 | 2.142 | 2.120 | 2.205 | 2.313 | 0.95 | — | 10.0 |  |

|            |       |       |       |       |       |       |       |      |   |      |  |
|------------|-------|-------|-------|-------|-------|-------|-------|------|---|------|--|
| S-8052ALR  | TO-92 | 2.195 | 2.300 | 2.405 | 2.239 | 2.415 | 2.597 | 1.5  | — | 10.0 |  |
| S-80823ALY | TO-92 | 2.254 | 2.300 | 2.346 | 2.322 | 2.415 | 2.534 | 0.95 | — | 10.0 |  |

|                 |          |       |       |       |       |       |       |      |   |      |  |
|-----------------|----------|-------|-------|-------|-------|-------|-------|------|---|------|--|
| S-8052ALR-LF    | SOT-89-3 | 2.195 | 2.300 | 2.405 | 2.239 | 2.415 | 2.597 | 1.5  | — | 10.0 |  |
| S-80823ALUP-EAL | SOT-89-3 | 2.254 | 2.300 | 2.346 | 2.322 | 2.415 | 2.534 | 0.95 | — | 10.0 |  |

|            |       |       |       |       |       |       |       |      |   |      |  |
|------------|-------|-------|-------|-------|-------|-------|-------|------|---|------|--|
| S-8052ALO  | TO-92 | 2.395 | 2.500 | 2.605 | 2.443 | 2.625 | 2.813 | 1.5  | — | 10.0 |  |
| S-80825ALY | TO-92 | 2.450 | 2.500 | 2.550 | 2.524 | 2.625 | 2.754 | 0.95 | — | 10.0 |  |

|                 |          |       |       |       |       |       |       |      |   |      |  |
|-----------------|----------|-------|-------|-------|-------|-------|-------|------|---|------|--|
| S-8052ALO-LG    | SOT-89-3 | 2.395 | 2.500 | 2.605 | 2.443 | 2.625 | 2.813 | 1.5  | — | 10.0 |  |
| S-80825ALUP-EAN | SOT-89-3 | 2.450 | 2.500 | 2.550 | 2.524 | 2.625 | 2.754 | 0.95 | — | 10.0 |  |

|            |       |       |       |       |       |       |       |      |   |      |  |
|------------|-------|-------|-------|-------|-------|-------|-------|------|---|------|--|
| S-8052ALY  | TO-92 | 2.595 | 2.700 | 2.805 | 2.647 | 2.835 | 3.029 | 1.5  | — | 10.0 |  |
| S-80827ALY | TO-92 | 2.646 | 2.700 | 2.754 | 2.725 | 2.835 | 2.974 | 0.95 | — | 10.0 |  |

|                 |          |       |       |       |       |       |       |      |   |      |  |
|-----------------|----------|-------|-------|-------|-------|-------|-------|------|---|------|--|
| S-8052ALY-LH    | SOT-89-3 | 2.595 | 2.700 | 2.805 | 2.647 | 2.835 | 3.029 | 1.5  | — | 10.0 |  |
| S-80827ALUP-EAQ | SOT-89-3 | 2.646 | 2.700 | 2.754 | 2.725 | 2.835 | 2.974 | 0.95 | — | 10.0 |  |

|                 |          |       |       |       |       |       |       |      |   |      |  |
|-----------------|----------|-------|-------|-------|-------|-------|-------|------|---|------|--|
| S-8052ANY-NH    | SOT-89-3 | 2.595 | 2.700 | 2.805 | 2.647 | 2.835 | 3.029 | 1.5  | — | 10.0 |  |
| S-80827ANUP-EDQ | SOT-89-3 | 2.646 | 2.700 | 2.754 | 2.725 | 2.835 | 2.974 | 0.95 | — | 10.0 |  |

|            |       |       |       |       |       |       |       |      |   |      |                 |
|------------|-------|-------|-------|-------|-------|-------|-------|------|---|------|-----------------|
| S-8052HNM  | TO-92 | 2.295 | 2.400 | 2.505 | 4.300 | 4.400 | 4.500 | 1.5  | — | 10.0 |                 |
| S-80824ANY | TO-92 | 2.352 | 2.400 | 2.448 | 2.423 | 2.520 | 2.644 | 0.95 | — | 10.0 | Release voltage |

|                 |          |       |       |       |       |       |       |      |   |      |                 |
|-----------------|----------|-------|-------|-------|-------|-------|-------|------|---|------|-----------------|
| S-8052HNM-CR    | SOT-89-3 | 2.295 | 2.400 | 2.505 | 4.300 | 4.400 | 4.500 | 1.5  | — | 10.0 |                 |
| S-80824ANUP-EDM | SOT-89-3 | 2.352 | 2.400 | 2.448 | 2.423 | 2.520 | 2.644 | 0.95 | — | 10.0 | Release voltage |

The production of the S8052HNM will be continued, but this product cannot be newly employed.

<Remarks>

FAQ No.: 11S808001