




THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
	G	REV PER EC 0G3B-0963-03	12/11/03	SS	GS	



SECTION B-B



SECTION A-A



- WIRE RANGE 24-20 AWG.
 - INSULATION RANGE 1.02-2.03 [.040-.080] DIA.
 - FOR LOOSE PIECE PART SEE DWG 66593.
- △ 0.76μm [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA,
1.27μm [.000050] MIN TIN-LEAD IN LOCALIZED TIN-LEAD PLATE AREA,
BOTH OVER 1.27μm [.000050] MIN NICKEL.
- △ TIN PLATED.
- △ GOLD PLATING PER MIL-G-45204, TIN PER MIL-T-10727 AND NICKEL PER QQ-N-290.
- △ 0.76μm [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA,
1.27μm [.000050] MIN TIN IN LOCALIZED TIN PLATE AREA,
BOTH OVER 1.27μm [.000050] MIN NICKEL.

OBSOLETE

REVERSE REELED FOR MINI-APPLICATOR	△	1-66583-0
REVERSE REELED FOR MINI-APPLICATOR	△	66583-4
-	△	66583-3
REVERSE REELED FOR MINI-APPLICATOR	△	66583-2
-	△	66583-1
DESCRIPTION	FINISH	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: MM [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -	
1 PLC ± -	
2 PLC ± 0.13 [.005]	
3 PLC ± -	
4 PLC ± -	
ANGLES ± -	
MATERIAL	FINISH
BRASS MIL-C-50	SEE TABLE

DWN V. FURLER 16MAY2003	Tyco Electronics Corporation Harrisburg, PA 17105	
CHK G. STEINHAUER 16MAY03	NAME	
APVD G. STEINHAUER 16MAY03	CONTACT, PIN, STRIP, TYPE VI, MULTIMATE	
PRODUCT SPEC	SIZE	CAGE CODE
APPLICATION SPEC	A3	00779
WEIGHT	—	DRAWING NO
CUSTOMER DRAWING	—	©-66583
SCALE	NTS	SHEET 1 OF 1
REV	G	