

CATALOG

➔ Cross Reference

[Competitive Products](#)
[Military Spec P/Ns](#)
[Tyco Brand P/Ns](#)

➔ [Part Number Search](#)
 ➔ [Document Search](#)
 ➔ [Product Type Search](#)
 ➔ [Product Family Search](#)
 ➔ [Alphabetical Search](#)
 ➔ [RoHS/ELV Compliance & Alternates](#)
 ➔ [CAD Model Search](#)
 ➔ [Brand Search](#)
 ➔ [Tool Search](#)
 ➔ [Multiple Part Comparison](#)
 ➔ [Lead Free Solutions](#)
 ➔ [Help/Glossary](#)

[Home](#)

e-bulletin newsletter
SUBSCRIBE NOW!
 click here

EMI/RFI Filter Products

➔ Filters and Accessories

corcom 6EEJ2  [Active](#)
[Not ELV or RoHS Compliant](#)**(Corporate P/N: 1-1609006-0)**[Search for Compliant \(RoHS/ELV\)](#)[Alternates](#)[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information

General Information	eCommerce	Related Part Information
➔ General Info ➔ Sales Info	➔ Pricing ➔ Product Availability	➔ Tooling

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)[Insertion Loss/Specifications](#)

Searchable Features:

Brand:	Corcom
RoHS/ELV Compliance:	Not ELV/ RoHS compliant
Lead Free Solder Processes:	Not relevant for lead free process
Product Type:	Power Line
Series:	EEJ (1-20 Amp)
Application:	General Purpose
Mount Style:	Flange

Other Properties:

Approved Standards:	UL Recognized, CSA Certified, VDE Approved
Facility Installation:	No
Need Min Size With IEC Connector:	Yes
Need Optional Switch, Fusing, Or Voltage Selector:	No
Leakage Current (Line-to-Ground) Max. @ 250 VAC 50 Hz (mA):	0.38

	Current Rating (Amps.):	6	Leakage Current (Line-to-Ground) Max. @ 120 VAC 60 Hz (mA):	0.22
	Shield Type:	N/ A		
	Terminal Input - Output Combination:	IEC - 1/4" Faston	Terminal Style Output:	Right Angle
	Filtered:	Yes		
	Connector Type:	IEC 320/C14		
	Voltage ≤ (VAC):	250		

[Copyright and Privacy Statement](#)
Visit [Tyco International Ltd.](#)

[[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)]