

REV. J

DIMENSIONS ARE IN INCHES

UNLESS OTHERWISE NOTED


TOLERANCES ARE:

ONE PLACE DECIMALS: $\pm .1$ [2.5] THREE PLACE DECIMALS: $\pm .005$ [.127]
 TWO PLACE DECIMALS: $\pm .01$ [.25] FOUR PLACE DECIMALS: $\pm .0020$ [.0508]

ANGLES
 $\pm 2^\circ$

TITLE:
 SSA-WIRE WRAP TAIL
 ASSEMBLY

DWG NO:
 SSA-1XX-W-X-XX
 SHEET 1 OF 1



SSA-1XX-W-X-XX

No. OF POSITIONS _____
 01 THRU 32 AVAILABLE

LEAD STYLE: _____
 WIRE WRAP CONTACT
 C-6-W-X

CONTACT PLATING _____
 -G: GOLD
 -T: TIN

OPTION _____
 -RA: RIGHT ANGLE
 (SEE FIGURE 1)

FIGURE 1
 RIGHT ANGLE ASSEMBLY

Do not scale
 from this print

NOTES:

1. MINIMUM CONTACT PUSH-OUT FORCE: 16 oz.
2. INSERTION FORCE: 3.0 oz. AVG. PER CONTACT USING .018 [.46] DIA PIN.
3. WITHDRAWAL FORCE: 1.5 oz. AVG. PER CONTACT USING .018 [.46] DIA PIN.
4. C REPRESENTS A CRITICAL DIMENSION.

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
 CONFIDENTIAL AND PROPRIETARY TO
 SAMTEC INC. AND SHALL NOT BE
 REPRODUCED OR TRANSFERRED TO
 OTHER DOCUMENTS OR DISCLOSED TO
 OTHERS OR USED FOR ANY PURPOSE
 OTHER THAN THAT FOR WHICH IT WAS
 OBTAINED WITHOUT THE EXPRESSED
 WRITTEN CONSENT OF SAMTEC INC.

MATERIAL:
 INSULATOR:
 DUPONT FR-530 RYNITE
 CONTACT:
 PHOSPHOR BRONZE

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
 PHONE (812) 944-6733 P.O. BOX 1147
 CODE 55322

MADE BY: MARK CHILTON 11-19-88

SSA-1XX-W-X-XX
 SHEET 1 OF 1