

















## Insulating clamping parts for power transistors

### Plastic insulating clamping parts for mounting transistors in cases TO 220, TO 218 and TO 247 for enhanced dielectric strengths

- electrically insulating assembly of the transistor by means of a plastic clamping part
- pin with a reaching into the hole of the transistor plate
- fastening of clamping part onto the mounting plate by screws, no electroinsulating connection to the transistor
- dielectric strength only determined by the insulating washer between transistor and mounting surface
- no insulating bush necessary, thus no dielectric breakdown

art. no.				
<b>ISP 220</b>				
art. no.				
<b>ISP 220 V</b>				
art. no.				
<b>ISP 218</b>				
art. no.				
<b>ISP 247</b>				

<b>material</b>	polycarbonate, GF reinforced
<b>heat distortion</b>	140 °C
<b>dielectric strength</b>	>30 KV/mm
<b>colour</b>	black
<b>flammability</b>	UL 94 V-0