

8737 Multi-Conductor - Single-Pair Cable

For more Information
please call

1-800-Belden1

**General Description:**

22 AWG stranded (7x30) tinned copper conductors, PVC insulation, twisted pair, tinned copper spiral wrapped shield (85% coverage), PVC jacket.

Physical Characteristics (Overall)**Conductor**

AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (in.)
1	22	7x30	TC - Tinned Copper	.030

Total Number of Conductors:

2

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
PVC - Polyvinyl Chloride	.060

Outer Shield

Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Spiral Serve	TC - Tinned Copper	85

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter:

0.180 in.

Pair

Pair Color Code Chart:

Number	Color
1	Black & Red

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +80°C
UL Temperature Rating:	80°C (UL AWM Style 2095)
Bulk Cable Weight:	18 lbs/1000 ft.
Max. Recommended Pulling Tension:	20 lbs.
Min. Bend Radius/Minor Axis:	1.750 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	CMG
CEC/C(UL) Specification:	CMG
AWM Specification:	UL Style 2095 (300 V 80°C)
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes

8737 Multi-Conductor - Single-Pair Cable

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Flame Test

CSA Flame Test: FT4

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

49

Nom. Inductance:

Inductance (µH/ft)

0.17

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

40

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)

70

Nominal Velocity of Propagation:

VP (%)

66

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

16

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

11.7

Max. Operating Voltage - UL:

Voltage

300 V RMS

Max. Recommended Current:

Current

3 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8737 060U1000	1,000 FT	20.000 LB	CHROME		1 PR#22 PVC SHLD PVC
8737 060U500	500 FT	10.500 LB	CHROME		2 #22 PVC SHLD PVC
8737 0601000	1,000 FT	20.000 LB	CHROME	C	1 PR#22 PVC SHLD PVC
8737 060500	500 FT	10.000 LB	CHROME		1 PR#22 PVC SHLD PVC
8737 0605000	5,000 FT	100.000 LB	CHROME	C	1 PR #22 PVC SHLD PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 10-03-2012

© 2014 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[8737 060500](#) [8737 060U1000](#) [8737 060U500](#)