

Type DMMA Polyester Film Capacitors

Metallized Radial Leads



AC Applications Low ESR

Type DMMA radial-leaded, metallized polyester capacitors are designed for AC rated applications. Self healing, low DF, and corona-free at high AC voltages, **Type DMMA** is the preferred value for medium current, AC applications.

Specifications

Voltage Range: 125-480 Vac, 60 Hz (250-1000 Vdc)

Capacitance Range: .01-5 μF

Capacitance Tolerance: $\pm 10\%$ (K) standard
 $\pm 5\%$ (J) optional

Operating Temperature Range: -55 °C to 70 °C


Dielectric Strength: 160% (1 minute)

Dissipation Factor: .60% Max. (25 °C, 1 kHz)

Insulation Resistance: 10,000 $\text{M}\Omega \times \mu\text{F}$
30,000 $\text{M}\Omega$ Min.

Life Test: 500 Hours at 70 °C at 115%
Rated Voltage

Pulse Capability					
Rated Volts	Body Length				
	0.625	.750-.937	1.062-1.125	1.250-1.500	≥ 1.687
	dV/dt – volts per microsecond, maximum				
125	62	34	16	12	
240		46	22	16	10
360		111	72	58	29
480		221	122	85	47



NOTE: Other capacitance values, sizes and performance specifications are available. Contact us.

Ratings

RoHS Compliant

Cap. (μF)	Catalog Part Number	T Maximum In. (mm)	H Maximum In. (mm)	L Maximum In. (mm)	S $\pm .062$ (1.6) In. (mm)
125 Vac (250 Vdc)					
0.047	DMMAAS47K-F	.325 (8.3)	.450 (11.4)	.625 (15.9)	.375 (9.5)
0.068	DMMAAS68K-F	.325 (8.3)	.450 (11.4)	.750 (19.0)	.500 (12.7)
0.100	DMMAAP1K-F	.325 (8.3)	.480 (12.2)	.750 (19.0)	.500 (12.7)
0.150	DMMAAP15K-F	.375 (9.5)	.530 (13.5)	.750 (19.0)	.500 (12.7)
0.220	DMMAAP22K-F	.420 (10.7)	.590 (15.0)	.750 (19.0)	.500 (12.7)
0.330	DMMAAP33K-F	.485 (12.3)	.650 (16.5)	.750 (19.0)	.500 (12.7)
0.470	DMMAAP47K-F	.440 (11.2)	.610 (15.5)	1.062 (27.0)	.812 (20.6)
0.680	DMMAAP68K-F	.480 (12.2)	.670 (17.0)	1.062 (27.0)	.812 (20.6)
1.000	DMMAAW1K-F	.545 (13.8)	.750 (19.0)	1.062 (27.0)	.812 (20.6)
1.500	DMMAAW1P5K-F	.575 (14.6)	.800 (20.3)	1.250 (31.7)	1.000 (25.4)
2.000	DMMAAW2K-F	.655 (16.6)	.860 (21.8)	1.250 (31.7)	1.000 (25.4)
3.000	DMMAAW3K-F	.685 (17.4)	.905 (23.0)	1.500 (38.1)	1.250 (31.7)
4.000	DMMAAW4K-F	.710 (18.0)	.925 (23.5)	1.500 (38.1)	1.250 (31.7)
5.000	DMMAAW5K-F	.775 (19.7)	1.050 (26.7)	1.500 (38.1)	1.250 (31.7)

Cap. (μF)	Catalog Part Number	T Maximum In. (mm)	H Maximum In. (mm)	L Maximum In. (mm)	S $\pm .062$ (1.6) In. (mm)
240 Vac (400 Vdc)					
0.022	DMMABS22K-F	.325 (8.3)	.455 (11.6)	0.750 (19)	.500 (12.7)
0.033	DMMABS33K-F	.325 (8.3)	.455 (11.6)	0.750 (19)	.500 (12.7)
0.047	DMMABS47K-F	.325 (8.3)	.47 (11.9)	0.750 (19)	.500 (12.7)
0.068	DMMABS68K-F	.325 (8.3)	.515 (13.1)	0.750 (19)	.500 (12.7)
0.100	DMMABP1K-F	.325 (8.3)	.485 (12.3)	1.062 (27)	.812 (20.6)
0.150	DMMABP15K-F	.355 (9.0)	.515 (13.1)	1.062 (27)	.812 (20.6)
0.220	DMMABP22K-F	.405 (10.3)	.565 (14.3)	1.062 (27)	.812 (20.6)
0.330	DMMABP33K-F	.450 (11.4)	.640 (16.3)	1.062 (27)	.812 (20.6)
0.470	DMMABP47K-F	.465 (11.8)	.655 (16.6)	1.250 (31.7)	1.000 (25.4)
0.680	DMMABP68K-F	.530 (13.5)	.735 (18.7)	1.250 (31.7)	1.000 (25.4)
1.000	DMMABW1K-F	.590 (15.0)	.845 (21.5)	1.250 (31.7)	1.000 (25.4)
1.500	DMMABW1P5K-F	.640 (16.3)	.875 (22.2)	1.500 (38.1)	1.250 (31.7)
2.000	DMMABW2K-F	.720 (18.3)	.955 (24.2)	1.500 (38.1)	1.250 (31.7)
3.000	DMMABW3K-F	.780 (19.8)	1.020 (25.9)	1.500 (38.1)	1.250 (31.7)

Type DMMA Polyester Film Capacitors

RoHS Compliant

Cap. (μ F)	Catalog Part Number	T Maximum In. (mm)	H Maximum In. (mm)	L Maximum In. (mm)	S $\pm .062$ (1.6) In. (mm)
360 Vac (800 Vdc)					
0.015	DMMACS15K-F	.295 (7.5)	.460 (11.7)	.937 (23.8)	.687 (17.4)
0.022	DMMACS22K-F	.343 (8.7)	.500 (12.7)	.937 (23.8)	.687 (17.4)
0.033	DMMACS33K-F	.375 (9.5)	.530 (13.5)	.937 (23.8)	.687 (17.4)
0.047	DMMACS47K-F	.405 (10.3)	.565 (14.3)	.937 (23.8)	.687 (17.4)
0.068	DMMACS68K-F	.465 (11.8)	.640 (16.3)	.937 (23.8)	.687 (17.4)
0.100	DMMACP1K-F	.450 (11.4)	.610 (15.5)	1.125 (28.6)	.875 (22.2)
0.150	DMMACP15K-F	.515 (13.1)	.690 (17.5)	1.125 (28.6)	.875 (22.2)
0.220	DMMACP22K-F	.590 (15.0)	.765 (19.4)	1.125 (28.6)	.875 (22.2)
0.330	DMMACP33K-F	.685 (17.4)	.890 (22.6)	1.125 (28.6)	.875 (22.2)
0.470	DMMACP47K-F	.685 (17.4)	.890 (22.6)	1.312 (33.3)	1.000 (25.4)
0.680	DMMACP68K-F	.810 (20.6)	1.015 (25.8)	1.312 (33.3)	1.000 (25.4)
1.000	DMMACW1K-F	.860 (21.8)	1.070 (27.2)	1.500 (38.1)	1.250 (31.7)
1.500	DMMACW1P5K-F	.860 (21.8)	1.140 (28.9)	1.937 (49.2)	1.656 (42.0)
2.000	DMMACW2K-F	.965 (24.5)	1.265 (32.1)	1.937 (49.2)	1.656 (42.0)

Cap. (μ F)	Catalog Part Number	T Maximum In. (mm)	H Maximum In. (mm)	L Maximum In. (mm)	S $\pm .062$ (1.6) In. (mm)
480 Vac (1,000 Vdc)					
0.010	DMMADS1K-F	.325 (8.3)	.485 (12.3)	.937 (23.8)	.687 (17.4)
0.015	DMMADS15K-F	.375 (9.5)	.530 (13.5)	.937 (23.8)	.687 (17.4)
0.022	DMMADS22K-F	.440 (11.2)	.595 (15.1)	.937 (23.8)	.687 (17.4)
0.033	DMMADS33K-F	.480 (12.2)	.655 (16.6)	.937 (23.8)	.687 (17.4)
0.047	DMMADS47K-F	.440 (11.2)	.610 (15.5)	1.125 (28.6)	.875 (22.2)
0.068	DMMADS68K-F	.500 (12.7)	.675 (17.1)	1.125 (28.6)	.875 (22.2)
0.100	DMMADP1K-F	.580 (14.7)	.765 (19.4)	1.125 (28.6)	.875 (22.2)
0.150	DMMADP15K-F	.670 (17.0)	.875 (22.2)	1.125 (28.6)	.875 (22.2)
0.220	DMMADP22K-F	.685 (17.4)	.875 (22.2)	1.312 (33.3)	1.000 (25.4)
0.330	DMMADP33K-F	.700 (17.8)	.905 (23.0)	1.312 (33.3)	1.000 (25.4)
0.470	DMMADP47K-F	.810 (20.6)	1.030 (26.2)	1.500 (38.1)	1.250 (31.7)
0.680	DMMADP68K-F	.875 (22.2)	1.110 (28.2)	1.687 (42.8)	1.468 (37.3)
1.000	DMMADW1K-F	.950 (24.1)	1.220 (31.0)	1.937 (49.2)	1.656 (42.0)
1.500	DMMADW1P5K-F	1.062 (27.0)	1.345 (34.2)	2.125 (54.0)	1.875 (47.6)

Notice and Disclaimer: All product drawings, descriptions, specifications, statements, information and data (collectively, the "Information") in this datasheet or other publication are subject to change. The customer is responsible for checking, confirming and verifying the extent to which the Information contained in this datasheet or other publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without any guarantee, warranty, representation or responsibility of any kind, expressed or implied. Statements of suitability for certain applications are based on the knowledge that the Cornell Dubilier company providing such statements ("Cornell Dubilier") has of operating conditions that such Cornell Dubilier company regards as typical for such applications, but are not intended to constitute any guarantee, warranty or representation regarding any such matter – and Cornell Dubilier specifically and expressly disclaims any guarantee, warranty or representation concerning the suitability for a specific customer application, use, storage, transportation, or operating environment. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by Cornell Dubilier with reference to the use of any Cornell Dubilier products is given gratis (unless otherwise specified by Cornell Dubilier), and Cornell Dubilier assumes no obligation or liability for the advice given or results obtained. Although Cornell Dubilier strives to apply the most stringent quality and safety standards regarding the design and manufacturing of its products, in light of the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies or other appropriate protective measures) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage. Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated in such warnings, cautions and notes, or that other safety measures may not be required.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cornell Dubilier:](#)

[DMMACS22K](#) [DMMACS22K-F](#)