




- A. Electrical Specifications (@ 25 °C)
- 1. Input Voltage and Frequency; 115/230V 50/60 Hz
 - 2. Output Voltage; 28VCT ±5% @ 0.375A
16VCT ±5% @ 0.72A
 - 3. Output Power; 24VA
 - 4. Insulation Resistance;
100ΩM MIN @ 500VDC, Pri to Sec, Pri to Core, Sec to Core
 - 5. Hi-Pot;
1500 Vrms 1 minute @ Pri to Sec, Pri to Core
1500 Vrms 1 minute @ Sec to Core
- B. Marking; MICROTRAN, PFT24-28, date code, country of origin, terminal numbers, safety symbols.
- C. Safety:
UL506 General Purpose, File No. E79781
- D. Schematic Diagram:



MODEL NUMBER
PFT24-28



E. Mechanical Specifications:



TOLERANCES (mm)	
≤ 4	± 0.2
4 ≤ 20	± 0.3
20 ≤ 50	± 0.4

PREPARED BY:

D. Rund

ENGINEER:

T. Shiozawa

QUALITY CONTROL:

D. Kelley

APPROVED:

J. Coleman

DWG CONTROL NO.
P-A1-12485
ACAD\XFMR\A1124851.DWG

REV
—

3 FLANGE BOBBIN
POWER TRANSFORMER

TAMURA CORPORATION OF AMERICA
43352 BUSINESS PARK DRIVE, TEMECULA, CA. 92590-6624
(909) 699-1270 FAX 9096769482

PFT24-28

MODEL SPECIFICATION

DIM: mm SCL: 3/4 SH: 1 OF 1

PROPRIETARY NOTICE: THIS DRAWING PRINT OR DOCUMENT AND SUBJECT MATTER DISCLOSED HEREIN ARE PROPRIETARY ITEMS TO WHICH TAMURA RETAINS THE EXCLUSIVE RIGHT OF DISSEMINATION, REPRODUCTION, MANUFACTURE AND SALE. THIS DRAWING, PRINT OR DOCUMENT IS SUBMITTED IN CONFIDENCE FOR CONSIDERATION BY THE RECIPIENT ALONE UNLESS PERMISSION FOR FURTHER DISCLOSURE IS EXPRESSLY GRANTED IN WRITING.