


**Part Number: 94128-5004**

1.00mm Pitch Surface Mount Module Carrier, 204 Circuits



Status:	<b>OBsolete</b>
Replacement:	NONE
Series:	94128
Category:	PCB Headers

Series image - Reference only

**Product Environmental Compliance**

EU RoHS: Not RoHS Compliant

China RoHS: 

REACH SVHC:

Low-Halogen Status: Not Reviewed

**Part Detail****General**

Status	<b>Obsolete</b>
Category	PCB Headers
Series	<b>94128</b>
Application	Board-to-Board, Signal
Comments	Module size 32x25mm
Product Name	FrameStack™

**Physical**

Breakaway	No
Circuits (Loaded)	204
Circuits (maximum)	204
Color - Resin	Black
Glow-Wire Compliant	No
Lock to Mating Part	None
Material - Plating Mating	Tin-Lead
Material - Resin	High Temperature Thermoplastic
Number of Rows	2
Orientation	Vertical
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.00mm
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	No
Stackable	Yes
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-30°C to +85°C
Termination Interface: Style	Surface Mount

**Electrical**

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	1A
Voltage - Maximum	100V AC

**Solder Process Data**

Lead-free Process Capability	Reflow Capable (SMT only)
------------------------------	---------------------------

**Material Info**

UPC	756054530122
-----	--------------

**Reference - Drawing Numbers**

Product Specification	PS-94128-001, RPS-94128-001
Sales Drawing	SD-94128-001

**Application Tooling**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

---

**Previously Available Application Tooling**

[Check our list of old tooling that used to be available for this part](#)