

QL
KTB QL 916115 S4E0

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmüller.com

**Stainless steel enclosures for the use within explosion-risk zones**

The Klippon® TB enclosure series features superior performance characteristics, even in the most extreme environmental surroundings. In addition, it meets the rigorous requirements of explosion-risk zones that can be found in the process or power generation industries. The new Klippon® TB QL enclosure series offers further improvements to a product line that is already successfully leading the market.

The Klippon® TB QL enclosure series features the following advantages:

The cover seal is protected against compression, quick-locking lid, comes with a slot as standard, Improved temperature performance IP 66 protection Earthing studs in enclosure cover and bottom section Welded-on mounting feet International approvals

- Available in 12 sizes and 3 standard depths
- Equipped with up to 4 gland plates
- The seal is protected against compression
- Quick-locking lid, comes with a slot as standard
- Improved temperature performance
- IP 66 protection
- Earthing studs in enclosure cover and bottom section

- Welded-on mounting feet
- International approvals

General ordering data

Order No.	1200880000
Type	KTB QL 916115 S4E0
Version	Enclosures, stainless steel enclosure, Stainless steel 1.4404 (316L), 914 mm, 150 mm, 610 mm
GTIN (EAN)	4032248983292
Qty.	1 pc(s).

QL
KTB QL 916115 S4E0

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Length	150 mm	Width	610 mm
Height	914 mm	Depth	150 mm
Mounting dimension - width	636 mm	Mounting dimension - height	559 mm
Net weight	18,200 g		

Cable glands, left

M12 (3)	70	M16 (3)	40
M20 (3)	34	M25 (3)	14
M32 (3)	12	M40 (3)	10
M50 (3)	8	M63 (3)	0
M75 (3)	0		

Cable glands, right

M12 (2)	70	M16 (2)	40
M20 (2)	34	M25 (2)	14
M32 (2)	12	M40 (2)	10
M50 (2)	8	M63 (2)	0
M75 (2)	0		

Cable glands, top/bottom

M12	53	M16	29
M20	25	M25	11
M32	9	M40	8
M50	6	M63	0
M75	0		

General information

AF size 1	10 mm	Access opening: height	861 mm
Access opening: width		Areas of use	Explosive risk zone, Process industry, Oil and gas industry, Chemical industry, Offshore, Onshore
	551 mm	Material thickness	1.5 mm
Installation advice	Terminal rail / mounting plate	Material thickness of flange	3 mm
Material thickness of cover	1.5 mm	Opening angle lid	125 °
Max. payload	223 kg	Position PE bolts	Page C
Overall dimensions	914 x 661 x 160	Seal material	Silicone
Material	Stainless steel 1.4404 (316L)	Operating temperature, min.	-60 °C
Surface finish	electropolished	Impact resistance	7 J ATEX version, 10 J version standard
Operating temperature, max.	135 °C	Enclosure attachment	4 welded-on mounting feet with 11-mm holes (2 slotted feet and 2 cross- shaped feet)
Protection degree		Integral fixing	4, 6 or 9 stud bolts M6 inner (female) thread
	IP 66		
Cover attachment	Quarter-turn fastener with slotted insert		

QL
KTB QL 916115 S4E0

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Housing earth

Earth, housing, internal Welded-on M6 stainless-steel earth stud in lower part of housing and lid.

horizontal assembly

WDU 10 / ZDU 10	6x52	WDU 16 / ZDU 16	5x43
WDU 2,5 / ZDU 2,5 / IDU 2,5	8x102	WDU 35 / ZDU 35	4x32
WDU 4 / ZDU 4	7x85	WDU 6 / ZDU 6	7x64

vertical assembly

WDU 10 / ZDU 10 (2)	3x82	WDU 16 / ZDU 16 (2)	3x68
WDU 2,5 / ZDU 2,5 / IDU 2,5 (2)	5x161	WDU 35 / ZDU 35 (2)	2x51
WDU 4 / ZDU 4 (2)	4x135	WDU 6 / ZDU 6 (2)	4x102

Classifications

eClass 6.2	27-14-91-07	eClass 7.1	27-14-91-07
------------	-------------	------------	-------------

Test certificates

Certificate No. (ATEX)	KEMA10ATEX0051	Certificate No. (GERMLLOYD)	11534-10
Certificate No. (IECEX)	IECEXKEM10.0020	Certificate no. (cULus)	E243298VOL1SEC5

Approvals

Approvals



QL
KTB QL 916115 S4E0

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

