

A General Specifications

Electrical Capacity (Resistive Load)

Power Level (silver): 6A @ 125V AC & 3A @ 250V AC
 4A @ 30V DC for On-None-On & On-None-Off; 3A @ 30V DC for all other circuits
Logic Level (gold): 0.4VA maximum @ 28V AC/DC maximum (Applicable Range 0.1mA ~ 0.1A @ 20mV ~ 28V)
Logic/Power Level (gold over silver): Combines silver & gold ratings
 Note: Find additional explanation of dual rating & operating range in Supplement section.

Other Ratings

Contact Resistance: 10 milliohms maximum for silver; 20 milliohms maximum for gold
Insulation Resistance: 1,000 megohms minimum @ 500V DC
Dielectric Strength: 1,000V AC minimum between contacts for 1 minute minimum;
 1,500V AC minimum between contacts and case for 1 minute minimum
Mechanical Life: 100,000 operations minimum; 50,000 operations minimum for flat, locking & splashproof devices
Electrical Life: 25,000 operations minimum for silver; 50,000 operations minimum for gold;
 50,000 operations minimum for silver at 3A @ 125V AC
Angle of Throw: 25°

Materials & Finishes

Toggle: Brass with chrome plating
Bushing: Brass with nickel plating
Case: Diallyl phthalate resin (UL94V-0)
Movable Contactor: Phosphor bronze with silver or gold plating
Movable Contacts: Silver alloy (code W); copper with gold plating (code G); or silver alloy with gold plating (code A)
Stationary Contacts: Silver with silver plating (code W); copper or brass with gold plating (code G);
 or silver with gold plating (code A)
Terminals: Copper or brass with silver plating; or copper or brass with gold plating

Frame: Stainless steel
Support Bracket: Brass with tin plating

Environmental Data

Operating Temp Range: -30°C through +85°C (-22°F through +185°F)
Humidity: 90 ~ 95% humidity for 96 hours @ 40°C (104°F)
Vibration: 10 ~ 55Hz with peak-to-peak amplitude of 1.5mm traversing the frequency range & returning in 1 minute; 3 right angled directions for 2 hours
Shock: 50G (490m/s²) acceleration (tested in 6 right angled directions, with 5 shocks in each direction)
Sealing: Splashproof bushing options B3, D3, D8, L3, & L8, which have o-rings inside & outside the bushing, meet IP67 of IEC60529 Standards.

Installation

Mounting Torque: 3.0Nm (26.55 lb•in) double nut for large bushing;
 1.5Nm (13 lb•in) double nut & 0.7Nm (6 lb•in) single nut for all other bushings

Processing

Soldering: Wave Soldering (PC version) for Gold: See Profile A in Supplement section.
 Manual Soldering for Gold: See Profile A in Supplement section.
 Wave Soldering (PC version) for Silver: See Profile B in Supplement section.
 Manual Soldering for Silver: See Profile B in Supplement section.
 Note: Lever must be in OFF (center) position while soldering.
Cleaning: These devices are not process sealed. Hand clean locally using alcohol based solution.

Standards & Certifications

Flammability Standards: UL94V-0 for case
UL: File No. E44145 - Recognized only when ordered with marking on switch.
 Add "/U" or "/CUL" before dash in part number to order UL recognized switch.
 All models recognized at 6A @ 125V AC, 3A @ 250V AC or 0.4VA maximum @ 28V DC maximum.
CSA: File No. 023535_0_000 - Certified only when ordered with marking on switch.
 Add "/C" before dash in part number to order CSA certified switch.
 All models certified at 6A @ 125V AC or 3A @ 250V AC or 0.4VA maximum @ 28V maximum.

Distinctive Characteristics

Antirotation design, standard on noncylindrical levers, mates toggle and bushing; bottom of toggle has two flattened sides which fit into a complementary opening inside bushing.

Antijamming design protects contacts from damage due to excessive downward force on actuator.

High torque bushing construction prevents rotation or separation from frame during installation.

High insulating barriers increase isolation of circuits in multipole devices and provide added protection to contact points.

Molded diallyl phthalate case has a UL flammability rating of 94V-0.

Epoxy sealed terminals prevent entry of solder flux and other contaminants.

Prominent external insulating barriers increase insulation resistance and dielectric strength.

Interlocked actuator block, lever, and interior guide prevent switch failure due to biased lever movement.

Clinching of frame to case well above base and terminals provides 1,500V dielectric strength.



Actual Size



Bushing Mount

Page A48



Bracket PC Mount

Page A60



Angle PC Mount

Page A66

A
Toggles

Rockers

Pushbuttons

Programmable
Illuminated PB

Keylocks

Rotaries

Slides

Tactiles

Tilt

Touch

Indicators

Accessories

Supplement

TYPICAL SWITCH

ORDERING EXAMPLE

M20

2

2

S

S2

Poles	
1	SPDT
2	DPDT SP3T

Circuits			
2	ON	NONE	ON
3	ON	OFF	ON
5	ON	NONE	(ON)
8	(ON)	OFF	(ON)
9	ON	OFF	(ON)
*4	ON	ON	ON
*6	(ON)	ON	(ON)
*7	ON	ON	(ON)

() = Momentary
*3-ON circuits

Small Toggles	
S	.413" (10.5mm) Bat
S2	.200" (5.08mm) Bat
S3	.256" (6.5mm) Bat
E	.450" (11.4mm) Flatted
E2	.256" (6.5mm) Flatted
E4	.840" (21.3mm) Flatted
Q	.550" (14.0mm) Cone
Q2	.640" (16.26mm) Cone
Q4	.840" (21.3mm) Cone

Toggle dimensions are based on use with a .350" (8.9mm) bushing; add .070" (1.78mm) to toggle length when combining with a .280" (7.1mm) bushing

Locking Lever	
L	.201" (5.1mm) Dia. Locking Lever

Small Bushings	
A2	.280" (7.1mm) Smooth with Keyway
S2	.350" (8.9mm) Smooth with Keyway
A1	.280" (7.1mm) Threaded with Keyway
S1	.350" (8.9mm) Threaded with Keyway

Deduct bracket thickness of .020" (0.51mm) from above dimensions

Bushing For Locking Levers	
L2	Smooth with Keyway for Lever Lock

Standard Toggle & Bushing Combinations:
SS2 & S2A2

IMPORTANT:



Switches are supplied without UL, cULus & CSA marking unless specified.
UL, cULus & CSA recognized only when ordered with marking on the switch.
Specific models, ratings, & ordering instructions are noted on General Specifications page.

G

13

—

B

C

Contact Materials & Ratings	
W	Silver; Rated 6A @ 125V AC & 3A @ 250V AC
G	Gold; Rated 0.4VA max @ 28V AC/DC max
A	Gold over Silver; Rated 6A @ 125V AC & 0.4VA max @ 28V AC/DC max


Terminals	
With Bracket	
13	.250" (6.35mm) Straight PC with .465" (11.8mm) Bracket
15	.425" (10.8mm) Straight PC with .630" (16.0mm) Bracket
17	.964" (24.5mm) Straight PC with 1.150" (29.2mm) Bracket
With Reinforced Bracket	
23	.250" (6.35mm) Straight PC with .465" (11.8mm) Bracket
25	.425" (10.8mm) Straight PC with .630" (16.0mm) Bracket
26	.750" (19.05mm) Straight PC with .953" (24.2mm) Bracket

Optional Caps	
B	For S Bat Toggle
C	Conical Cap for S Bat Toggle


Cap for Locking Lever	
No Code	Nickel Plated Supplied with Switch
A	Black
C	Red
G	Blue

Cap Colors	
A	Black
B	White
C	Red
E	Yellow
F	Green
G	Blue





DESCRIPTION FOR TYPICAL ORDERING EXAMPLE
M2022SS2G13-BC



POLES & CIRCUITS

Pole	Model	Toggle Position () = Momentary			Connected Terminals			Throw & Schematics
		Down 	Center 	Up 	Down 	Center 	Up 	
SP	M2012	ON	NONE	ON	2-3	OPEN	2-1	SPDT 
	M2013	ON	OFF	ON				
	M2015	ON	NONE	(ON)				
	M2018	(ON)	OFF	(ON)				
	M2019	ON	OFF	(ON)				
DP	M2022	ON	NONE	ON	2-3 5-6	OPEN	2-1 5-4	DPDT 
	M2023	ON	OFF	ON				
	M2025	ON	NONE	(ON)				
	M2028	(ON)	OFF	(ON)				
	M2029	ON	OFF	(ON)				

For 3 Throw (3-On)

Pole	Model	Connected Terminals & Schematics			External Connection
		Down	Center	Up	
SP	M2024 M2026 M2027	ON (ON) ON	ON ON ON	ON (ON) (ON)	The SP3T model utilizes a double pole base. External connection must be made during field installation. 
		 2-3 5-6	 2-3 5-4	 2-1 5-4	

SMALL TOGGLES

Important:


Toggle length changes based on bushing selected. All illustrations are shown with .350" (8.9mm) long bushing. When using a .280" (7.1mm) long bushing, toggle length increases .070" (1.78mm).

Standard Material & Finish:

Brass with Bright Chrome
Contact factory for optional finishes.


S

.413" (10.5mm)
Bat




S2

.200" (5.08mm)
Bat




S3

.256" (6.5mm)
Bat




E

.450" (11.4mm)
Flatted




E2

.256" (6.5mm)
Flatted




E4

.840" (21.3mm)
Flatted




Q

.550" (14.0mm)
Cone




Q2

.640" (16.26mm)
Cone



Q4

.840" (21.3mm)
Cone



SMALL BUSHINGS

A
Toggles

Rockers

Pushbuttons

Illuminated PB

Programmable

Keylocks

Rotaries

Slides

Tactiles

Tilt



Touch

Indicators



Accessories

Supplement

A2 .280" (7.1mm) Smooth with Keyway





S2 .350" (8.9mm) Smooth with Keyway





When using this bushing, toggle length is increased by .070" (1.78mm).

A1 .280" (7.1mm) Threaded with Keyway



S1 .350" (8.9mm) Threaded with Keyway




When using this bushing, toggle length is increased by .070" (1.78mm). Maximum Panel Thickness with Standard Hardware: .031" (0.8mm)


Maximum Panel Thickness with Standard Hardware: .102" (2.6mm)

Panel Cutouts

For A2, S2, A1, or S1 Bushing with Keyway



For A1 or S1 Bushing with Locking Ring




Standard Hardware:

- 2 Hex Nuts (AT513H)
- 1 Lockwasher (AT509)
- 1 Locking Ring (AT507H)

For dimensions, see Accessories & Hardware section.


LOCKING LEVER & BUSHING

LL2 Smooth with Keyway



Locking Mechanism

on-none-on




2 positions lock

on-none-(on)




1 position locks

on-off-(on)
on-on-(on)




2 positions lock

on-off-on
on-on-on




3 positions lock

(on)-off-(on)
(on)-on-(on)



1 position locks

No Code



Cap for Locking Lever

Supplied with Cap AT427
Material & Finish:

Brass with Nickel Plating

Lever Material & Finish:

Brass with Chrome Plating

Color Codes for Optional Anodized Aluminum Caps

A

Black

C

Red

G

Blue

CONTACT MATERIALS & RATINGS

W
Silver over Silver
Power Level
6A @ 125V AC & 3A @ 250V AC
G
Gold over Brass or Copper
Logic Level
0.4VA maximum @ 28V AC/DC maximum

Note: See Supplement section to find complete explanation of operating range.

A
Gold over Silver
**Power Level
or Logic Level**
**6A @ 125V AC
or 0.4VA maximum @ 28V AC/DC maximum**

Note: This dual rated option is suitable when two or more identical switches are used in logic and in power circuits within the same application. See Supplement section to find complete explanation of dual rating and operating range.

TERMINALS

Straight PC Mount with Bracket

Straight PC Mount with Reinforced Bracket

13

**.250" (6.35mm)
Terminal with
.465" (11.8mm)
Bracket**

15

**.425" (10.8mm)
Terminal with
.630" (16.0mm)
Bracket**

17

**.964" (24.5mm)
Terminal with
1.150" (29.2mm)
Bracket**

23



**.250" (6.35mm)
Terminal with
.465" (11.8mm)
Bracket**

25

**.425" (10.8mm)
Terminal with
.630" (16.0mm)
Bracket**

26

**.750" (19.05mm)
Terminal with
.953" (24.2mm)
Bracket**




PCB footprints are on the following Typical Switch Dimension page.


OPTIONAL CAPS & CAP COLORS

B
**AT415
for S Bat Toggle**

Material:
Polyethylene


C
**AT444
Conical Cap for
S Bat Toggle**

Material:
Polyethylene




Cap Colors
Available:


A
Black
B
White
C
Red
E
Yellow
F
Green
G
Blue

TYPICAL SWITCH DIMENSIONS


Straight PC • Bracket





Single Pole



Double Pole




M2012S2A2G13




Terminal Code:	Terminal Length:	Bracket Length:
13	.250" (6.35mm)	.465" (11.8mm)
15	.425" (10.8mm)	.630" (16.0mm)
17	.964" (24.5mm)	1.150" (29.2mm)


Straight PC • Reinforced Bracket





Single Pole



Double Pole



M2012S2A2G23



Terminal Code:	Terminal Length:	Bracket Length:
23	.250" (6.35mm)	.465" (11.8mm)
25	.425" (10.8mm)	.630" (16.0mm)
26	.750" (19.05mm)	.953" (24.2mm)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

NKK Switches:

[M2012EA2W13](#) [M2012SA2G13](#) [M2018SS2G13](#) [M2022SS2W23/UC](#) [M2012S2A2G13](#) [M2012S2A2W13](#)
[M2013S2A2W13](#) [M2013SS2G23](#) [M2022LL2W13](#) [M2028SS2G13](#) [M2012SS2G13-BC](#) [M2012LL2G25-RO](#)
[M2012LL2G13-RO](#) [M2012S3A2G13-RO](#) [M2012SS1W13-RO](#) [M2012SS1W13/UC](#) [M2013SS2G13-RO](#)
[M2018ES2A25-RO](#) [M2019SS2G13-RO](#) [M2022S2A2G26](#) [M2024LL4W01-C](#) [M2028SA2G15-BA](#) [M2012SS1W13/CUL](#)
[M2013S2A2G15](#) [M2022SS1W13/CUL](#) [M2023SA1W13](#) [M2024S2A2W13](#) [M2022SS2G13-RO](#) [M2028SA1W13](#)
[M2022SS2W13-RO](#) [M2024E2S2G13-RO](#) [M2012SS2W13-RO](#) [M2012SS2G13-RO](#) [M2015EA2G13-RO](#)
[M2012EA2G13-RO](#) [M2018SS1W13-RO](#) [M2012S2A2W25/UC](#) [M2012SS1W25](#) [M2012SS2W13/C-RO](#) [M2015SS2G23](#)
[M2018ES2G13-RO](#) [M2018SS2W13-RO](#) [M2022S2A2W13-RO](#) [M2022SA2A13](#) [M2022SS2W13/C-RO](#)
[M2023SS2G13-RO](#) [M2042SA2W23-RO](#) [M2013SA1W13](#) [M2012SA1W13-RO](#) [M2012SA2W13-RO](#) [M2015SA2W13-](#)
[RO](#) [M2024SS2G13-RO](#) [M2032SS1W13/UC](#) [M2013S3S1W13](#) [M2012S3S1W13](#) [M2012SS2G13-BG](#)
[M2012S2S1W13](#) [M2013S2S1W13](#) [M2022S2S1W13](#) [M2012SS2G13-BF](#) [M2012SA1G15](#) [M2012ES1A25](#)
[M2012S3S1W13/CUL](#) [M2013S3S1W13/CUL](#) [M2028LL1W01-A](#) [M2018ES2A23](#) [M2022SS1W13](#) [M2012SS1W17](#)
[M2024SS4W01BB](#) [M2012SS2W13](#) [M2015EA2G13](#) [M2022EA1G13](#) [M2012SS1G13](#) [M2012SS2G13-BE](#)
[M2022SS2G13](#) [M2022S2A2W23/U](#) [M2012SA2W13-BA](#) [M2012EA1W15](#) [M2012SS2W13-BC](#) [M2018SS1W13](#)
[M2019EA2A13](#) [M2024E2S2G13](#) [M2012SS1W15](#) [M2012LL2G13](#) [M2015SS2G13](#) [M2013SS2G13](#) [M2015SA2W13](#)
[M2012SS2G13](#) [M2012EA2G13](#) [M2012S3A2G13](#) [M2023SS2G13](#) [M2022SS2W26](#) [M2042SA2W23](#) [M2022S2A2W30](#)
[M2012SS1W15-BA](#) [M2022SS2W13/C](#) [M2018SA1G13](#) [M2022SS2W13](#) [M2012S3A1G13](#) [M2012SA2W13](#)