


SPECIFICATION CONTROL DRAWING



MATERIALS

1. INSULATION SLEEVE: Heat-shrinkable, transparent blue, radiation cross-linked modified polyvinylidene fluoride.
2. MELTABLE INSERT: Immersion resistant thermoplastic, color-gray.
3. CRIMP SPLICER: Base Metal: Copper Alloy 110 per ASTM B-152.
Plating: Tin plated per MIL-T-10727.
Wire Size Range: 2.62 – 6.64mm² (5180 – 13100 CMA, 12 –10 AWG) Solid or Stranded.

APPLICATION

1. This device is designed to provide immersion resistant 1 to 1 splices in wires having insulations rated for at least 135°C and conductor falling within the wire size range as listed above.
2. Crimp Splicer to be installed with AMP 49935 (or equivalent tool). Sealing sleeve may be installed with convection or infrared heat sources.
3. Free recovered I.D. of sealing sleeve is 1.27 (0.050) max. (through inserts).

tyco Electronics	Tyco Electronics Corporation 300 Constitution Drive, Menlo Park, CA. 94025, U.S.A.	Raychem	TITLE: IN-LINE CRIMP SPLICE, 1 TO 1, 12-10 AWG , TIN PLATED			
Unless otherwise specified dimensions are in millimeters. [Inches dimensions are shown in brackets]			DOCUMENT NO.: D-436-26			
TOLERANCES: 0.00 N/A 0.0 N/A 0 N/A	ANGLES: N/A ROUGHNESS IN MICRON	Tyco Electronics reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application.		PROD. REV.: C	DOC. ISSUE: 1	DATE: Mar. 18, 2004
PREPARED BY: mforonda	CAGE CODE : 06090	REPLACES: D010499	DCR NUMBER: D040064	SCALE: ---	SIZE: A	SHEET: 1 of 1

© 2004 Tyco Electronics Corporation. All rights reserved.

If this document is printed it becomes uncontrolled. Check for the latest revision.