

1		2		3		4		5	
					TECHNICAL CHARACTERISTICS				
					MATERIAL				
					INSULATOR MATERIAL: PET (WHITE)				
					SUPPORT TAPE: PET (BLUE)				
					CONTACT MATERIAL: COPPER				
					CONTACT PLATING: TIN				
					QUALITY CLASS: 20 MATING CYCLES MIN.				
					PITCH: 1.00 MM				
					ENVIRONMENTAL				
					OPERATING TEMPERATURE: -30°C UP TO 85°C				
					HEAT RESISTANCE: 105°C x 95 HRS				
					FLAMMABILITY RATING UL SUB.758				
					MOISTURE RESISTANCE: 40°C, 95% RH x 96 HRS				
					COMPLIANCE: LEAD FREE AND ROHS				
					ELECTRICAL				
					CURRENT RATING: 1.0 A MAX				
					WORKING VOLTAGE: 60V				
					INSULATION RESISTANCE: >1000 MOHM/M (500 VDC)				
					DIELECTRIC STRENGTH: 500 VAC/MN NO BREAKDOWN				
					CONDUCTOR RESISTANCE: <1.09 OHM/M				
					CONTACT RESISTANCE: <20 mOHMS				
					STANDARD				
					CERTIFIED: E328849				
					MECHANICAL				
					ELONGATION OF INSULATOR: > 60 %				
					TENSIL STRENGTH OF INSULATION: >3.5KG/MM²				
					FLEXING TEST: 180° >20 TIMES				
					ABRASION: >10000 TIMES				
					PULL/OUT: >20 TIMES				
					PACKAGING				
					BAG				
					DIMENSION & TOLERANCE				
					W= (N+1) x P				
					Pt=(N-1) x P				

</