


Metal Film Resistors, Industrial Power, Flameproof



FEATURES

- High power rating, small size
- Flameproof, high temperature coating
- Special filming and coating processes
- Excellent high frequency characteristics
- Low noise
- Low voltage coefficient
- Lead (Pb)-free version is RoHS compliant



RoHS*
COMPLIANT

STANDARD ELECTRICAL SPECIFICATIONS

GLOBAL MODEL	HISTORICAL MODEL	POWER RATING $P_{70^{\circ}\text{C}}$ W	LIMITING ELEMENT VOLTAGE MAX $V_{\equiv}$	RESISTANCE RANGE Ω					
				0.1 % - 1 %	0.1 % - 5 %	0.5 % - 5 %	1 % - 5 %	1 %	2 % - 5 %
				25 ppm	50 ppm	100 ppm	150 ppm	200 ppm	200 ppm
CPF1	CPF-1	1	250	5 - 150K	5 - 150K	1 - 150K	R5 - 150K	R5 - 150K	R1 - 150K
CPF2	CPF-2	2	350	5 - 150K	5 - 150K	1 - 150K	R5 - 150K	R5 - 150K	R1 - 150K
CPF3	CPF-3	3	500	8 - 150K	8 - 150K	1 - 150K	1 - 150K	1 - 150K	R1 - 150K

Note:

Marking: Print marked - DALE, Model, Resistance value, Tolerance/Temperature Coefficient, Date Code

TEMPERATURE COEFFICIENT CODES

GLOBAL TC CODE	HISTORICAL TC CODE	TEMPERATURE COEFFICIENT
E	T-9	25 ppm/ $^{\circ}\text{C}$
H	T-2	50 ppm/ $^{\circ}\text{C}$
K	T-1	100 ppm/ $^{\circ}\text{C}$
L	T-0	150 ppm/ $^{\circ}\text{C}$
N	T-00	200 ppm/ $^{\circ}\text{C}$

TECHNICAL SPECIFICATIONS

PARAMETER	UNIT	CPF1	CPF2	CPF3
Rated Dissipation at 70 $^{\circ}\text{C}$	W	1	2	3
Limiting Element Voltage ⁽¹⁾	$V_{\equiv}$	250	350	500
Insulation Voltage	V-	900	900	900
Thermal Resistance	K/W	85	60	50
Insulation Resistance	Ω	10^{10}		
Category Temperature Range	$^{\circ}\text{C}$	- 65 $^{\circ}\text{C}/+ 230^{\circ}\text{C}$		

Note:

⁽¹⁾ Rated Voltage $\sqrt{P \times R}$

GLOBAL PART NUMBER INFORMATION

New Global Part Numbering: CPF1562R00FKR36 (preferred part numbering format)


C	P	F	1	5	6	2	R	0	0	F	K	R	3	6			
GLOBAL MODEL			RESISTANCE VALUE			TOLERANCE CODE			TEMPERATURE COEFFICIENT			PACKAGING			SPECIAL		
CPF1 CPF2 CPF			R = Decimal K = Thousand R10000 = 0.1 Ω 10R000 = 10 Ω 150K00 = 150 Ω			B = $\pm 0.1\%$ C = $\pm 0.25\%$ D = $\pm 0.5\%$ F = $\pm 1\%$ G = $\pm 2\%$ J = $\pm 5\%$			E = 25 ppm H = 50 ppm K = 100 ppm L = 150 ppm N = 200 ppm			E14 = Lead (Pb)-free, Bulk E36 = Lead (Pb)-free, T/R (Full) EE6 = Lead (Pb)-free, T/R (1000 pieces) B14 = Tin/Lead, Bulk B36 = Tin/Lead, T/R (Full) BE6 = Tin/Lead, T/R (1000 pieces)			Blank = Standard (Dash Number) (up to 3 digits) From 1 - 999 as applicable		

Historical Part Number example: CPF-15620FT-1 R36 (will continue to be accepted)

CPF-1	5620	F	T-1	R36
HISTORICAL MODEL	RESISTANCE VALUE	TOLERANCE CODE	TEMP. COEFFICIENT	PACKAGING

* Pb containing terminations are not RoHS compliant, exemptions may apply.

DIMENSIONS




Notes:


(1) 1.08 ± 0.125 [27.43 ± 3.18] if tape and reel

- Surface temperatures were taken with an infrared pyrometer in + 25 °C still air. Resistors were supported by their leads in test clips at a point 0.500" [12.70 mm] out from the resistor body ends.

GLOBAL MODEL	DIMENSIONS in inches [millimeters]			
	L	D	L ₁ max.	d
CPF1	0.240 ± 0.020 [6.10 ± 0.51]	0.090 ± 0.008 [2.29 ± 0.20]	0.310 [7.87]	0.025 ± 0.002 [0.64 ± 0.05]
CPF2	0.344 ± 0.031 [8.74 ± 0.79]	0.145 ± 0.015 [3.68 ± 0.38]	0.425 [10.80]	0.032 ± 0.002 [0.81 ± 0.05]
CPF3	0.555 ± 0.041 [14.10 ± 1.04]	0.180 ± 0.015 [4.57 ± 0.381]	0.650 [16.51]	0.032 ± 0.002 [0.81 ± 0.05]



SURFACE TEMPERATURE VS. POWER



DERATING

MATERIAL SPECIFICATIONS	
Element:	Proprietary nickel-chrome alloy
Core:	Cleaned high purity ceramic
Coating:	Special high temperature conformal coat
Termination:	Standard lead material is solder-coated Solderable and weldable per MIL-STD-1276, Type C

MECHANICAL SPECIFICATIONS	
Terminal Strength:	2 pound pull test
Solderability:	Continuous satisfactory coverage when tested in accordance with MIL-STD-202, Method 208

PERFORMANCE	
TEST	MAX. ΔR (Typical Test Lots)
Thermal Shock	± 1.0 %
Short Time Overload	± 0.5 %
Low Temperature Operation	± 0.5 %
Moisture Resistance	± 1.5 %
Resistance To Soldering Heat	± 0.5 %
Shock	± 0.5 %
Vibration	± 0.5 %
Terminal Strength	± 0.5 %
Dielectric Withstanding Voltage	± 0.5 %
Life	± 2.0 %



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.