


Features

- ◆ Wide 4:1 input voltage range
- ◆ High efficiency
- ◆ Operating temperature range
–40°C to +85°C
- ◆ No minimum load required
- ◆ Models with 1'500 VDC and 3'000 VDC
I/O-isolation (functional insulation)
- ◆ Input filter meets EN 55022, class A
- ◆ Overload protection
- ◆ DIP-24 plastic package
- ◆ Industry standard pinout
- ◆ 3-year product warranty



The TEN-6WIN series is designed for an optimized cost/performance ratio of DC/DC converters with output power of 6 Watt.

General features like no minimum load requirement, overload protection, internal filter for EN55022 class A and high efficiency make these converters easy to design in. With the popular DIP-24 standard package they are also a drop in replacement for many cost critical applications.

Models

Order code		Input voltage range	Output voltage	Output current max.	Efficiency typ.
1'500 VDC isolation	3'000 VDC isolation				
TEN 6-2410WIN	TEN 6-2410WIN-HI	9 – 36 VDC (24 VDC nominal)	3.3 VDC	1200 mA	77 %
TEN 6-2411WIN	TEN 6-2411WIN-HI		5 VDC	1200 mA	80 %
TEN 6-2412WIN	TEN 6-2412WIN-HI		12 VDC	500 mA	84 %
TEN 6-2413WIN	TEN 6-2413WIN-HI		15 VDC	400 mA	84 %
TEN 6-2415WIN	TEN 6-2415WIN-HI		24 VDC	250 mA	84 %
TEN 6-2421WIN	TEN 6-2421WIN-HI		±5 VDC	±500 mA	80 %
TEN 6-2422WIN	TEN 6-2422WIN-HI		±12 VDC	±250 mA	84 %
TEN 6-2423WIN	TEN 6-2423WIN-HI		±15 VDC	±200 mA	84 %
TEN 6-4810WIN	TEN 6-4810WIN-HI	18 – 75 VDC (48 VDC nominal)	3.3 VDC	1200 mA	77 %
TEN 6-4811WIN	TEN 6-4811WIN-HI		5 VDC	1200 mA	80 %
TEN 6-4812WIN	TEN 6-4812WIN-HI		12 VDC	500 mA	84 %
TEN 6-4813WIN	TEN 6-4813WIN-HI		15 VDC	400 mA	84 %
TEN 6-4815WIN	TEN 6-4815WIN-HI		24 VDC	250 mA	84 %
TEN 6-4821WIN	TEN 6-4821WIN-HI		± 5 VDC	±500 mA	80 %
TEN 6-4822WIN	TEN 6-4822WIN-HI		±12 VDC	±250 mA	84 %
TEN 6-4823WIN	TEN 6-4823WIN-HI		±15 VDC	±200 mA	84 %

Input current at no load	24 Vin models: 20 mA typ. 48 Vin models: 10 mA typ.
Input current at full load	24 Vin, 3.3VDC models: 215 mA typ. 24 Vin other models: 300 mA typ. 48 Vin, 3.3VDC models: 110 mA typ. 48 Vin other models: 150 mA typ.
Recommended input fuse (slow blow)	24 Vin models: 1500 mA 48 Vin models: 800 mA
Start-up voltage / under voltage shut down	24 Vin models: 9 VDC / 8.5 VDC (or lower) 48 Vin models: 18 VDC / 16 VDC (or lower)
Surge voltage (1 sec. max.)	24 Vin models: 50 V max. 48 Vin models: 100 V max.
Conducted noise	EN 55022 class A

Voltage set accuracy		±2 %
Regulation	– Input variation Vin min. to Vin max. – Load variation 0 – 100 % single output models: dual output models balanced load: dual output models 50%/100% unbalanced load:	0.5 % max. 1.2 % max. 1.2 % max. 3.0 % max.
Minimum load		not required
Temperature coefficient		±0.02 %/K
Ripple and noise (20 MHz Bandwidth)		80 mVp-p max.
Dynamic load response (change from 75 % to 100 % load)		±3 % peak variation typ. 300 µS response time typ.
Current limitation		150 % of Iout max. typ., constant power
Short circuit protection		continuous, automatic recovery
Capacitive load	3.3 & 5.0 VDC models: 12 & 15 VDC models: 24 VDC models: dual output models:	470 µF max. 100 µF max. 47 µF max. 100 µF max. (each output)

Temperature ranges	– Operating – Case temperature – Storage	–40°C to +85°C +100°C max. –50°C to +125°C
Derating	3.3 & 5.0 VDC models: other models:	2.5 %/K above +60°C 3.3 %/K above +70°C
Humidity (non condensing)		95 % rel H max.
Reliability, calculated MTBF (MIL-HDBK-217F, at +25°C, ground benign)		>800'000 h
Isolation voltage (input/output, 60 sec., functional insulation)	standard models: models with suffix -H:	1'500 VDC 3'000 VDC
Isolation capacitance (input/output, 100 KHz, 1 V)		1000 pF typ.
Isolation resistance (input/output, 500 VDC)		>1'000 M Ohm
Switching frequency		330 kHz typ.

<http://www.tracopower.com>


General Specifications

Safety standards	UL/cUL 60950-1, IEC/EN 60950-1	
Safety approvals	– CSA certificate according UL 60950-1 – CB test certificate according IEC 60950-1	www.tracopower.com/products/ten6win-csa.pdf www.tracopower.com/products/ten6win-cb.pdf
Environmental compliance	– Reach – RoHS	www.tracopower.com/products/ten6win-reach.pdf RoHS directive 2002/95/EC

Physical Specifications

Casing material	non conductive plastic (UL 94V-0-rated)
Potting material	epoxy (XM-2109 & XY-2110, UL 94V-0-rated)
Weight	4.8 g (0.16 oz)
Soldering temperature (1.5mm from case for 10 sec.)	max. 260°C

Outline Dimensions



Pin-Out		
Pin	Single	Dual
2	–Vin (GND)	–Vin (GND)
3	–Vin (GND)	–Vin (GND)
9	No pin	Common
11	No function	–Vout
14	+Vout	+Vout
16	–Vout	Common
22	+Vin (Vcc)	+Vin (Vcc)
23	+Vin (Vcc)	+Vin (Vcc)

Dimensions in [mm], () = Inch
Pin diameter $\varnothing 0.5 \pm 0.05$ (0.02 ± 0.002)
Tolerances ± 0.25 (± 0.01)
Pin pitch tolerances ± 0.13 (± 0.0005)

Specifications can be changed any time without notice.