



.100 CENTERS C Series Probes


SURFACE MOUNT



THRU HOLE MOUNT



SOLDER CUP



PROBE SPECIFICATIONS

Minimum Centers: .100 (2.54)

Current Rating:

CG Series: 10 amps continuous
CP Series: 10 amps continuous
CS Series: .5 amp continuous
(Individual probe in free air @ ambient temperature)

Typical Resistances:

CG Series: < 10 mΩ
CP Series: < 10 mΩ
CS Series: < 60 mΩ

Spring Force:

3.1 oz. (88g) @ working travel for 4mm compressed length series
2.9 oz. (82g) @ working travel for 6mm compressed length series

MATERIALS

Barrel: Brass, gold plated

Spring: Stainless steel

Plunger:

CG Series: Brass, gold plated
CP Series: Brass, gold plated
CS Series: Brass, Duralloy™ plated

Special Features:

CG Series: Bias plunger design
CP Series: Bias plunger design
CS Series: Standard design

Recommendations:

Mounting hole: .064/.065 (1.62/1.65)
Pad size for Surface Mount: .085 (2.20)
Wire gage for Solder Cup: 20 gage max.
Drill size for Thru Hole Tail: .035 (0.89)

Overall Length

Series	SURFACE Mount	Thru Hole	Solder Cup
CG-2.5-4	.197 (5.00)	.295 (7.50)	.295 (7.50)
CG-2.5-6	.335 (8.50)	.433 (11.00)	.433 (11.00)
CP-2.5-4	.185 (4.70)	.283 (7.20)	.283 (7.20)
CP-2.5-6	.315 (8.00)	.413 (10.50)	.413 (10.50)
CS-2.5-4	.185 (4.70)	.283 (7.20)	.283 (7.20)
CS-2.5-6	.315 (8.00)	.413 (10.50)	.413 (10.50)

Travel

Series	Working Travel	Maximum Travel
CG-2.5-4	.039 (1.00)	.039 (1.00)
CG-2.5-6	.098 (2.50)	.098 (2.50)
CP-2.5-4	.028 (0.71)	.028 (0.71)
CP-2.5-6	.079 (2.00)	.079 (2.00)
CS-2.5-4	.028 (0.71)	.028 (0.71)
CS-2.5-6	.079 (2.00)	.079 (2.00)

HOW TO ORDER

CS

SERIES

2.5

PITCH (MM)

4

COMPRESSED LENGTH (MM)

SM

TERMINATION

SERIES:
CG: Ground Connector Probe
CP: Power Connector Probe
CS: Signal Connector Probe

4: 4 mm
6: 6 mm

SM: Surface Mount
TH: Thru Hole
SC: Solder Cup

View updates of this information at www.idinet.com

Specifications subject to change without notice. Dimensions in inches (millimeters)

