

MICRO SWITCH
a Honeywell Division


FED. MFG. CODE 91929

SWITCH-BASIC


CATALOG LISTING

V7-2B27P07-000-1



CW-B3193



PLASTIC PLUNGER



TERMINATION PATTERN




NOTE

1 - TERMINALS ARE SILVER PLATED

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE— — —75 GRAMS MAX
 RELEASE FORCE— — —10 GRAMS MIN
 DIFFERENTIAL TRAVEL— — —.002—.010
 RELEASE TRAVEL— — — —.010 MIN
 OVERTRAVEL— — — —.050 MIN
 FREE POSITION— — — —.625 MAX

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P N O

L156 11A 1/3HP 125, 250 OR 277 VAC
 1/2A 125 VDC, 1/4A 250 VDC
 4A 125 VAC "L"

SCALE FULL

DO NOT
SCALE PRINTUNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE (.0) $\pm .030$
 TWO PLACE (.00) $\pm .015$
 THREE PLACE (.000) $\pm .005$
 ANGLES $\pm$

WEIGHT



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[V7-2B27P07-000-1](#)