


Brushless DC Axial Fans



General Specifications		Part Number	Voltage (V)	Current (A)	Speed (RPM)	Power (W)	Airflow (CFM)	Max. Air Pressure (Inch-H2O)	Noise (dBA)	Weight (g)	Bearing Type
Material:		120 x 120 x 38mm (4 3/4 x 1 1/2")									
Body	PBT UL 94V-0	99484002	12	0.59	3000	7	105	0.31	45.0	323	Sleeve
	Fan PBT UL 94V-0	99484004	12	0.27	2300	3.2	83	0.18	36.0	323	Sleeve
Insulation Class E		99484006	24	0.25	3000	6	105	0.31	45.0	323	Sleeve
Approvals UL, cUL Recognized E118509		99484051	12	0.65	3150	7.8	120	0.34	48.0	323	Ball
Box Count:		99484052	12	0.59	3100	7	106	0.32	46.5	323	Ball
120 x 38 40 pieces		99484053	12	0.42	2850	5	93	0.23	42.0	323	Ball
120 x 25 40 pieces		99484055	24	0.33	3150	7.9	120	0.34	48.0	323	Ball
92 x 25 50 pieces		99484056	24	0.25	3100	6	106	0.31	46.5	323	Ball
80 x 25 50 pieces		99484057	24	0.23	2850	5.5	93	0.23	42.0	323	Ball
60 x 25 100 pieces											
60 x 15 200 pieces											
40 x 20 200 pieces											
40 x 10 400 pieces											
25 x 10 500 pieces											

120 x 120 x 25mm (4 3/4 x 1")											
99484101	12	0.42	3000	5	84	0.25	44.0	250	Sleeve		
99484102	12	0.26	2700	3.1	77	0.20	40.0	250	Sleeve		
99484104	24	0.25	3000	6	84	0.25	44.0	250	Sleeve		
99484105	24	0.22	2700	5.3	77	0.20	40.0	250	Sleeve		
99484106	24	0.17	2300	4.1	65	0.16	35.0	250	Sleeve		
99484151	12	0.42	3100	5	85	0.26	44.5	250	Ball		
99484152	12	0.26	2800	3.1	78	0.21	41.0	250	Ball		
99484153	12	0.23	2400	2.8	66	0.17	35.5	250	Ball		
99484154	24	0.25	3100	6	85	0.26	44.5	250	Ball		
99484155	24	0.22	2800	5.3	78	0.21	41.0	250	Ball		
99484156	24	0.17	2400	4.1	66	0.17	35.5	250	Ball		


92 x 92 x 25mm (3 9/16 x 1")											
99484201	12	0.22	3200	2.6	50	0.19	33.0	135	Sleeve		
99484202	12	0.16	2700	2	44	0.17	27.0	135	Sleeve		
99484203	12	0.12	2400	1.4	42	0.15	25.5	135	Sleeve		
99484204	24	0.15	3200	3.6	50	0.19	33.0	135	Sleeve		
99484205	24	0.12	2700	2.2	44	0.17	27.0	135	Sleeve		
99484206	24	0.10	2400	1.7	42	0.15	25.5	135	Sleeve		
99484251	12	0.22	3400	2.6	51	0.19	34.0	135	Ball		
99484252	12	0.16	2800	2	45	0.17	28.0	135	Ball		
99484253	12	0.12	2500	1.4	42.5	0.15	26.0	135	Ball		
99484254	24	0.22	3400	3.6	51	0.19	34.0	135	Ball		
99484256	24	0.12	2500	1.7	42.5	0.15	26.0	135	Ball		

Other Information	To Order, Specify:
For dimensions and air flow performance see pages 150-151. All DC fans are supplied with Lead wires only.	99484002 Standard, normally stocked products
	99484003 Products produced to order - minimum quantities may apply

Products and specifications subject to change without notice.

Order/Technical Support - Tel: (800) 677-5311 / FAX: (800) 677-3865 / www.crouzet-usa.com

Brushless DC Axial Fans



General Specifications		Part	Voltage	Current	Speed	Power	Airflow	Max. Air Pressure	Noise	Weight	Bearing
		Number	(V)	(A)	(RPM)	(W)	(CFM)	(Inch-H2O)	(dBA)	(g)	Type
Material:		80 x 80 x 25mm (3 1/8 x 1 1/2)									
Body	PBT UL 94V-0	99484301	12	0.22	3000	2.6	41.7	0.19	33.0	120	Sleeve
Fan	PBT UL 94V-0										
Insulation	Class E	99484303	12	0.12	2200	1.4	29.4	0.15	24.5	120	Sleeve
		99484304	24	0.15	3000	3.6	41.7	0.19	33.0	120	Sleeve
Approvals	UL, cUL Recognized E118509	99484305	24	0.12	2650	2.9	34.4	0.17	28.0	120	Sleeve
		99484306	24	0.10	2200	2.4	29.4	0.15	24.5	120	Sleeve
		99484351	12	0.22	3200	2.6	42.5	0.23	33.5	120	Ball
Box Count:											
120 x 38	40 pieces	99484353	12	0.12	2500	1.4	30	0.14	25.0	120	Ball
120 x 25	40 pieces	99484354	24	0.22	3100	2.6	38	0.23	33.5	120	Ball
92 x 25	50 pieces										
80 x 25	50 pieces										
60 x 25	100 pieces	99484356	24	0.12	2350	1.4	27	0.14	25.0	120	Ball
60 x 15	200 pieces										
40 x 20	200 pieces										
40 x 10	400 pieces										
25 x 10	500 pieces										
60 x 60 x 25 (mm)											
		99484401	12	0.19	4500	2.2	21.7	0.20	34.0	60	Sleeve
		99484402	12	0.13	3800	1.6	17.6	0.14	31.0	60	Sleeve
		99484403	12	0.09	3300	1.2	15.9	0.10	26.7	60	Sleeve
		99484404	24	0.11	4500	2.6	21.7	0.20	34.0	60	Sleeve
		99484406	24	0.06	3300	1.4	15.9	0.10	26.7	60	Sleeve
		99484451	12	0.19	4700	2.2	22.1	0.22	34.3	60	Ball
		99484454	24	0.11	4500	2.6	21.7	0.20	34.0	60	Ball
60 x 60 x 15 (mm)											
		99484501	12	0.16	4000	1.9	17.8	0.14	31.0	45	Sleeve
		99484502	12	0.09	3300	1.2	14.8	0.11	26.0	45	Sleeve
40 x 40 x 20 (mm)											
		99484601	12	0.07	6000	0.9	6.5	0.12	25.5	35	Sleeve
		99484602	12	0.50	4500	0.6	5.2	0.08	22.8	35	Sleeve
		99484603	24	0.07	6500	1.6	7.8	0.16	29.0	35	Sleeve
		99484604	24	0.05	6000	1.2	6.5	0.12	25.5	35	Sleeve
40 x 40 x 10 (mm)											
		99484701	12	0.09	5500	1.1	5.8	0.11	25.0	15.3	Sleeve
		99484751	12	0.09	6600	1.1	6.5	0.15	27.0	15.3	Ball
25 x 25 x 10 (mm)											
		99484801	12	0.10	10000	1.1	1.5	0.10	23.0	7	Sleeve

Other Information	To Order, Specify:
For dimensions and air flow performance see page 154. All DC fans are supplied with Lead wires only.	99484002 Standard, normally stocked products 99484003 Products produced to order D minimum quantities may apply


Products and specifications subject to change without notice.

Order/Technical Support - Tel: (800) 677-5311 / FAX: (800) 677-3865 / www.crouzet-usa.com

Brushless DC Axial Fans - Dimensions and Performance


Dimensions

120 x 38
120 x 25




Air performance


99 484 002 - 99 484 006




92 x 25




99 484 201 / 204 - 99 484 203 / 206




80 x 25




99 484 301 / 304 - 99 484 303 / 306



60 x 25



99 484 401 - 99 484 403




Products and specifications subject to change without notice.

Order/Technical Support - Tel: (800) 677-5311 / FAX: (800) 677-3865 / www.crouzet-usa.com

Brushless DC Axial Fans - Dimensions and Performance


Dimensions

▣ 60 x 15





Air performance

99 484 501





▣ 40 x 20

99 484 601





▣ 40 x 10

99 484 701



▣ 25 x 10

99 484 801



Products and specifications subject to change without notice.

Order/Technical Support - Tel: (800) 677-5311 / FAX: (800) 677-3865 / www.crouzet-usa.com