


FEATURES

- HIGH SURGE CAPABILITY
- HIGH ON-STATE CURRENT
- HIGH STABILITY AND RELIABILITY
- ISOLATED PACKAGE :
INSULATED VOLTAGE = 2500V_(RMS)
(UL RECOGNIZED : E81734)

DESCRIPTION

The BTW 66 and BTW 67 Family Silicon Controlled Rectifiers are high performance glass passivated chips technology.

This general purpose Family Silicon Controlled Rectifiers is designed for power supply up to 400Hz on resistive or inductive load.



ABSOLUTE RATINGS (limiting values)

Symbol	Parameter			Value	Unit
$I_T(RMS)$	RMS on-state current (180° conduction angle)	BTW 66 BTW 67	$T_c=75^\circ C$ $T_c=75^\circ C$	30 40	A
$I_T(AV)$	Average on-state current (180° conduction angle, single phase circuit)	BTW 66 BTW 67	$T_c=75^\circ C$ $T_c=75^\circ C$	20 25	A
I_{TSM}	Non repetitive surge peak on-state current (T_j initial = $25^\circ C$)	BTW 66 BTW 67	$t_p=8.3$ ms	420 525	A
		BTW 66 BTW 67	$t_p=10$ ms	400 500	
i^2t	i^2t value	BTW 66 BTW 67	$t_p=10$ ms	800 1250	A ² s
di/dt	Critical rate of rise of on-state current Gate supply : $I_G = 100$ mA $di_G/dt = 1$ A/ μ s			100	A/ μ s
T_{stg} T_j	Storage and operating junction temperature range			- 40 to + 150 - 40 to + 125	$^\circ C$ $^\circ C$
T_l	Maximum lead temperature for soldering during 10 s at 4.5 mm from case			230	$^\circ C$

Symbol	Parameter	BTW 66- / BTW 67-						Unit
		200	400	600	800	1000	1200	
V_{DRM} V_{RRM}	Repetitive peak off-state voltage $T_j = 125^\circ C$	200	400	600	800	1000	1200	V

THERMAL RESISTANCES

Symbol	Parameter		Value	Unit
Rth (c-h)	Contact (case to heatsink)		0.10	°C/W
Rth (j-c) DC	Junction to case for DC	BTW 66	1.2	°C/W
		BTW 67	1.0	

GATE CHARACTERISTICS (maximum values)

P_G (AV) = 1W P_{GM} = 40W (tp = 20 μ s) I_{FGM} = 8A (tp = 20 μ s) V_{RGM} = 5 V.

ELECTRICAL CHARACTERISTICS

Symbol	Test Conditions				Value		Unit
					BTW 66	BTW 67	
I _{GT}	V _D =12V (DC) R _L =33Ω	T _j =25°C	MAX	50	80	mA	
V _{GT}	V _D =12V (DC) R _L =33Ω	T _j =25°C	MAX	1.5		V	
V _{GD}	V _D =V _{DRM} R _L =3.3kΩ	T _j = 125°C	MIN	0.2		V	
tgt	V _D =V _{DRM} I _G = 200mA dI _G /dt = 1.5A/μs	T _j =25°C	TYP	2		μs	
I _L	I _G = 1.2 I _{GT}	T _j =25°C	TYP	50		mA	
I _H	I _T = 500mA gate open	T _j =25°C	MAX	75	150	mA	
V _{TM}	BTW 66 I _{TM} = 60A BTW 67 I _{TM} = 80A tp= 380μs	T _j =25°C	MAX	2.2	2.0	V	
I _{DRM} I _{RRM}	V _{DRM} Rated V _{RRM} Rated	T _j =25°C	MAX	0.02		mA	
		T _j = 125°C		6			
dV/dt	Linear slope up to V _D =67%V _{DRM} gate open	V _{DRM} ≤ 800V V _{DRM} ≥ 1000V	T _j = 125°C	MIN	500 250	V/μs	
tq	V _D =67%V _{DRM} I _{TM} = 60A V _R = 75V dI _{TM} /dt=30 A/μs dV _D /dt= 20V/μs	T _j = 125°C	TYP	100		μs	

Package	$I_{T(RMS)}$	V_{DRM} / V_{RRM}	Sensitivity Specification
	A	V	BTW
BTW 66 (Insulated)	30	200	X
		400	X
		600	X
		800	X
		1000	X
		1200	X
BTW 67 (Insulated)	40	200	X
		400	X
		600	X
		800	X
		1000	X
		1200	X

Fig.1 : Maximum average power dissipation versus average on-state current (BTW 66).




Fig.3 : Maximum average power dissipation versus average on-state current (BTW 67).




Fig.2 : Correlation between maximum average power dissipation and maximum allowable temperatures (T_{amb} and T_{case}) for different thermal resistances heatsink + contact (BTW 66).




Fig.4 : Correlation between maximum average power dissipation and maximum allowable temperatures (T_{amb} and T_{case}) for different thermal resistances heatsink + contact (BTW 67).




Fig.5 : Average on-state current versus case temperature (BTW 66).




Fig.6 : Average on-state current versus case temperature (BTW 67).




Fig.7 : Relative variation of thermal impedance junction to case versus pulse duration.




Fig.8 : Relative variation of gate trigger current versus junction temperature.




Fig.9 : Non repetitive surge peak on-state current versus number of cycles (BTW 66).




Fig.10 : Non repetitive surge peak on-state current versus number of cycles (BTW 67).




Fig.11 : Non repetitive surge peak on-state current for a sinusoidal pulse with width : $t \leq 10$ ms, and corresponding value of I^2t (BTW 66).




Fig.12 : Non repetitive surge peak on-state current for a sinusoidal pulse with width : $t \leq 10$ ms, and corresponding value of I^2t (BTW 67).




Fig.13 : On-state characteristics (maximum values) (BTW 66).






Fig.14 : On-state characteristics (maximum values) (BTW 67).



PACKAGE MECHANICAL DATA

RD 91 Plastic



Marking : type number

Weight : 20 g

Information furnished is believed to be accurate and reliable. However, SGS-THOMSON Microelectronics assumes no responsibility for the consequences of use of such information nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of SGS-THOMSON Microelectronics. Specifications mentioned in this publication are subject to change without notice. This publication supersedes and replaces all information previously supplied.

SGS-THOMSON Microelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of SGS-THOMSON Microelectronics.

© 1995 SGS-THOMSON Microelectronics - Printed in Italy - All rights reserved.

SGS-THOMSON Microelectronics GROUP OF COMPANIES

Australia - Brazil - France - Germany - Hong Kong - Italy - Japan - Korea - Malaysia - Malta - Morocco - The Netherlands - Singapore - Spain - Sweden - Switzerland - Taiwan - Thailand - United Kingdom - U.S.A.