



1. MATERIALS AND FINISHES:
 - BODY - ZINC ALLOY, NICKEL PLATING
 - CONTACT -PHOPHOR BRONZE, GOLD PLATING (.000003 THICK)
 - @CONTACT AREA ONLY, TIN PLATING AT TAIL, NICKEL PLATED OVERALL
 - INSULATOR - POLYPROPYLENE
 - HOUSING- PBT, BLACK, 15% G.F.
 - GROUNDING TERMINAL-STEEL, TIN PLATING
 - ROUND PIN-BRASS, TIN PLATING
2. ELECTRICAL:
 - A. IMPEDANCE: 50 OHM
 - B. FREQUENCY RANGE: DC - 1GHz
 - C. DIELECTRIC WITHSTANDING VOLTAGE: 1500 VRMS, MIN.
3. MECHANICAL:
 - A. DURABILITY: 500 CYCLES MIN.
 - B. TEMPERATURE RANGE: -55° C TO 85° C
4. PACKAGING:
 - A. PACKAGED IN PACKING TRAY
 - B. QUANTITY PER TRAY: 40

REVISIONS



REV	DESCRIPTION	DATE	ECO	APPR
A	RELEASE TO MFG	4/12/91	38057	DR
E	SEE SHEET I	10/11/96	41588	CPM
F	SEE SHEET I	2/3/05	45257	CPM
G	UPDATED FORMAT AND NOMINAL ENVELOPE DIMENSIONS	7/26/12	49146	CW
H	SYNCH THE DRAWING WITH ARFA	15-Aug-12	49198	SH



RECOMMENDED PCB LAYOUT



RECOMMENDED PANEL CUTOUT



CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm 0.5 - 6mm 6 - 30mm 30 - 120mm ANGLES ± 0.05mm ±0.1mm ±0.2mm ± 0.3mm ±1° NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other sperson to manufacture, use or sell any product, process or design, patented or otherwisle, that may in any way be related to or disclosed by said drawings, specifications, or other data.	MATERIAL	DRAWN	DATE	TITLE		Amphenol RF www.amphenolrf.com		
	SEE NOTES	S.LI	15-Aug-12					
			ENGINEER	DATE	BNC JACK, 50 OHM LOW-PROFILE PCB RECEPTACLE, BLACK RIGHT ANGLE MOUNT		DRAWING NO. 31-5540	
			D. ROYCE	4/8/91				
		REFERENCE	APPROVED	DATE	SCALE: 3.0:1.0		SHEET	1 OF 2
	EAR 71004-5	S.HSIEH	15-Aug-12	DWG SIZE		REV		
	FINISH			B		H	PART NO.31-5540	