







PART NO.

PSG01538

REVISIONS

ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
-	A	RELEASED	Jagan	11/2/08	Suresh	11/2/08	G. C	26/2/08



Pin Hole Layout
(Jack Bottom View)

Dimensions : Millimetres

This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. SPC pro-SIGNAL is the registered trademark of the Group © Premier Farnell plc 2008.

TOLERANCES:

UNLESS OTHERWISE
SPECIFIED,
DIMENSIONS ARE
FOR REFERENCE
PURPOSES ONLY.

DRAWN BY:

Jagan

DATE:

11/02/08

CHECKED BY:

Suresh

DATE:

11/02/08

APPROVED BY:

G. Cook

DATE:

26/02/08

DRAWING TITLE:

3.5mm Jack - PCB Stereo

SIZE
A

DWG NO.

ELECTRONIC FILE

1280746_DWG

REV

A

SCALE: NTS

U.O.M.: mm

SHEET: 1 OF 2



PART NO.

PSG01538

REVISIONS

ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
-	A	RELEASED	Jagan	11/2/08	Surash	11/2/08	G. C	26/2/08

Specifications:

Maximum Contact Resistance : 30mΩ.
Minimum Insulation Resistance : 100MΩ at 500V dc.
Dielectric Withstand Voltage : 500V ac for one minute.

Specification Table

Number	Designation	Material	Finish	Part Number
1	Earth Terminal	0.25T Phosphor Bronze	Silver Plated	PSG01538
2	Ring Spring	0.2T TicuR1 - M - EH		
3	Tip Spring	0.25T TicuR1 - M - EH		
4	Barrel	Brass	Nickel Plated	
5	Housing	PBT	Black Color	

<http://www.farnell.com><http://www.newark.com><http://www.cpc.co.uk>

This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness; any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. SPC pro-SIGNAL is the registered trademark of the Group © Premier Farnell plc 2008.

TOLERANCES:

UNLESS OTHERWISE
SPECIFIED,
DIMENSIONS ARE
FOR REFERENCE
PURPOSES ONLY.

DRAWN BY:

Jagan

DATE:

11/02/08

CHECKED BY:

Surash

DATE:

11/02/08

APPROVED BY:

G. Cook

DATE:

26/02/08

DRAWING TITLE:

3.5mm Jack - PCB Stereo

SIZE
A

DWG NO.

ELECTRONIC FILE

1280746_DWG

REV

A

SCALE: NTS

U.O.M.: mm

SHEET: 2 OF 2