




NYLON 6/6 (RMS-01) COLOR: NATURAL PART NO.	FLAME RET. (RMS-19) COLOR: NATURAL PART NO.	DIM. "A"
MSPE-2-01	MSPE-2-19	1/8 (3.2)
MSPE-3-01	MSPE-3-19	3/16 (4.8)
MSPE-4-01	MSPE-4-19	1/4 (6.4)
MSPE-5-01	MSPE-5-19	5/16 (7.9)
MSPE-6-01	MSPE-6-19	3/8 (9.5)
MSPE-7-01	MSPE-7-19	7/16 (11.1)
MSPE-8-01	MSPE-8-19	1/2 (12.7)
MSPE-10-01	MSPE-10-19	5/8 (15.9)
MSPE-11-01	MSPE-11-19	11/16 (17.5)
MSPE-12-01	MSPE-12-19	3/4 (19.1)
MSPE-14-01	MSPE-14-19	7/8 (22.2)
MSPE-16-01	MSPE-16-19	1 (25.4)
MSPE-20-01	MSPE-20-19	1 1/4 (31.8)
MSPE-22-01	MSPE-22-19	1 3/8 (34.9)

G	SEE CO 200692 FOR CHANGES	SK 07.11.11
F	SEE CO 200685 FOR CHANGES	SK 06.21.11
E	SEE ECN #862 FOR CHANGES	SM 10.04.04
D	SEE ECN #535 FOR CHANGES	SM 12.04.02
C	REMOVED NOTES; ADDED COLUMN "-19" AND CHANGED FILE NO.	SM 05.01.01
B	CHANGED FILE NUMBER	SM 05.01.01
A	ADDED -01 TO PART NO.	JL 3.30.99
REV	DESCRIPTION	ENGR DATE

TITLE:

MINIATURE SUPPORT POST

TOLERANCES
UNLESS NOTED
.XX=±.010
.XXX=±.005
FRAC=±1/64
ANG=±1°

FILE # MSPE
MAT'L: SEE TABLE
RE: RICHCO, INC.

DWN: P.B.
DT: 04-19-94 DT:
RICHCO INC.
PO BOX 804238, CHICAGO, 60680
(773) 539-4060



DWG IN
IN (MM)
FINAL



PART #
SEE TABLE

PRINT
TYPE
CA