


HBL2430 -- Twist-Lock Receptacle




3P4W, 20A 3PH 480V AC, L16-20R, Black Nylon Face

Product Specifications

Product Type	 Twist-Lock Devices	
Product Item	Single Receptacle	
Wiring Scheme	3 Pole, 4 Wire Grounding	
Amperage	20A	
Voltage	3 Phase 480V AC	
NEMA Configuration	L16-20R	
Item Style	Standard	
Device Color	Black	
Horsepower	5	
Terminal Clamp Material	.040" (1.0) Brass	
Terminal Screw Material	#10-32 Bronze (White finish on neutral screw when used)	

Ground Screw Material	#10-32 Bronze (Green)
Contact Spring Material	.040" Brass
Mounting Screw Material	Steel-zinc-plated
Cover (Top) Material	Black Nylon
Base Material	Nylon Polyester
Ground Contact Material	.040" Brass
Bridge (Mounting Strap) Material	.050" Brass
Back Plate Material	.040" Brass
Rivet Material	Brass
Auto Ground Clip Material	Stainless Steel
Ratings	Molded into face.
Dielectric Voltage Withstand	2,000 V minimum.
Current Interrupting	Certified for current interrupting at full rated current.
Temperature Rise	Max 30 C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of .75.
Terminal Accommodation	20A-#12AWG
Terminal Identification	Terminals identified in accordance with UL 498 (X, Y, Z, White, Green)
Flammability	HB or better per UL 94 or CSA 22.2 No. 0.6
Operating Temperatures	Maximum Continuous 75 C Minimum -40 C (w/o impact)
Listings	FED SPEC UL/CSA
Feature Info	Black nylon face.
Catalog Page	Click here for catalog page B37
Brochures	Click here for product brochure
Hubbellnet	Click here for Hubbellnet
Catalog Section	Click here for Section-B
UPC Number	78358523577
Weight in LBs	0.3



NEMA L16-20R
20A 3Ø 480V AC
UL/CSA
5 HP

NEMA
Configuration

Hubbell Incorporated (Delaware)

185 Plains Road

Milford, CT 06460-2420

Ph: (203) 882-4800

Fax: (800) 255-1031



Wiring Device-Kellems