




Features

- RoHS compliant*
- Conductive plastic or cermet
- Linear and audio tapers
- PC board and bushing mount
- Gangable
- Metal bushing and shaft
- Sealed for board washing



51/53 - Sealed 1/2 " (12.5 mm) Square Control

Electrical Characteristics ¹	Conductive Plastic	Cermet
Standard Resistance Range		
Linear	1 K ohms to 1 megohm.....	150 ohms to 1 megohm
Audio	1 K ohms to 1 megohm.....	1 K ohms to 1 megohm
Total Resistance Tolerance		
Linear Tapers	±10 % or ±20 %	±10 % or ±5 %
Audio Tapers	±10 % or ±20 %	±10 %
Independent Linearity	±5 %	±5 %
Absolute Minimum Resistance	2 ohms maximum	2 ohms maximum
Effective Electrical Angle	270 ° ±5 °	270 ° ±5 °
Contact Resistance Variation	2 %	2 %
Dielectric Withstanding Voltage (MIL-STD-202 – Method 301)		
Sea Level	1,500 VAC minimum	1,500 VAC minimum
70,000	500 VAC minimum	500 VAC minimum
Insulation Resistance	1,000 megohms minimum	1,000 megohms minimum
Power Rating At 70 °C (Derate To 0 At 125 °C)		
(Voltage Limited By Power Dissipation or 350 VAC, Whichever Is Less)		
Linear Tapers	0.5 watt	1.0 watt
Audio Tapers	0.25 watt	0.5 watt
Theoretical Resolution	Essentially infinite	Essentially infinite
Environmental Characteristics ¹		
Operating Temperature Range	+1 °C to +125 °C	+1 °C to +125 °C
Storage Temperature Range	-55 °C to +125 °C	-55 °C to +125 °C
Temperature Coefficient Over Storage Temperature Range	±1,000 ppm/°C	±150 ppm/°C
Vibration (Single Section)	15 G	15 G
Total Resistance Shift	±2 % maximum	±2 % maximum
Voltage Ratio Shift	±5 % maximum	±5 % maximum
Shock (Single Section)	30 G	30 G
Total Resistance Shift	±2 % maximum	±2 % maximum
Voltage Ratio Shift	±5 % maximum	±5 % maximum
Load Life	1,000 hours	1,000 hours
Total Resistance Shift	±10 % TRS maximum	±5 % TRS maximum
Rotational Life (No Load)	50,000 cycles	25,000 cycles
Total Resistance Shift	±10 % TRS maximum	±10 % TRS maximum
Contact Resistance Variation @ 25,000 Cycles	±2 %	±4 %
Moisture Resistance (MIL-STD-202, Method 103, Condition B)		
Total Resistance Shift	±10 % TRS	±5 % TRS
IP Rating	IP 64	IP 64
Mechanical Characteristics		
Stop Strength	56 N-cm (5 lb.-in.)	
Mechanical Angle	290 ° ±5 °	
Torque		
Starting (Dual Sections)	+0.35 N-cm (+0.5 oz.-in.) maximum	
Running (Single Section)	0.15 to 1.4 N-cm (0.2 to 2.0 oz.-in.)	
Running (Dual Section)	0.35 to 1.8 N-cm (0.5 to 2.5 oz.-in.)	
Mounting (Torque on Bushing)	1.7 to 2.0 N-m (15 to 18 lb.-in.) maximum	
Weight (Single Section)	5.5 grams	
(Additional Section)	3.0 grams	
Terminals	PC pin or solder lug	
Soldering Condition	Recommended hand soldering using Sn95/Ag5 no clean solder, 0.025 " wire diameter.	
	Maximum temperature 399 °C (750 °F) for 3 seconds. No wash process to be used with no clean flux.	
	Part can be wave soldered at 260 °C (500 °F) for 5 seconds, no wash process with no clean flux.	
Marking	Manufacturer's trademark, part number, resistance value and date code.	
Ganging (Multiple Section Potentiometer)	2 sections maximum**	
Hardware	One lockwasher and one mounting nut is shipped with each potentiometer, except where noted in the part number.	

¹At room ambient: +25 °C nominal and 50 % relative humidity nominal, except as noted.

** Additional sections available on special request with higher minimum order quantities.

*RoHS Directive 2002/95/EC Jan 27, 2003 including Annex.

Specifications are subject to change without notice.


Customers should verify actual device performance in their specific applications.

51/53 - Sealed 1/2 " (12.5 mm) Square Control


BOURNS®

Product Dimensions

PACKAGE DIMENSIONS




PACKAGE DIMENSIONS PCB MOUNTING BRACKET




SOLDER LUG TERMINALS

MODEL 53




ELECTRICAL SCHEMATIC




ANTI-ROTATION LUG

(Style "A", 90 CW Shown)




DIMENSIONS: $\frac{\text{MM}}{\text{(INCHES)}}$

SHAFT FLAT ORIENTATION



SUGGESTED PANEL LAYOUTS

The Model 50 can be used with either of the two panel layouts shown below.




FOR TOLERANCES SHOWN: .XX = ± $\frac{.25}{(.010)}$
 .XXX = ± $\frac{.13}{(.005)}$
 SHAFT DIMENSIONS ± $\frac{.80}{(.132)}$

Specifications are subject to change without notice.
 Customers should verify actual device performance in their specific applications.

51/53 - Sealed 1/2 " (12.5 mm) Square Control


BOURNS®

Shaft/Bushing Styles




A Style Bushing

STD. LENGTH "L"
.500 (12.7)
.625 (15.88)
.750 (19.05)
.875 (22.23)
1.000 (25.4)




C Style Bushing

STD. LENGTH "L"
.375 (9.53)
.500 (12.7)
.625 (15.88)
.750 (19.05)
.875 (22.23)
1.000 (25.4)




A Style Bushing - Flatted Shaft

STD. LENGTH "L"
.625 (15.88)
.750 (19.05)
.875 (22.23)
1.000 (25.4)




S Style Bushing

STD. LENGTH "L"
.394 (10.0)
.512 (13.0)
.630 (16.0)
.866 (22.0)
.984 (25.0)



U Style Bushing

STD. LENGTH "L"
.394 (10.0)
.512 (13.0)
.630 (16.0)
.866 (22.0)
.984 (25.0)



R Style Bushing

STD. LENGTH "L"
.512 (13.0)
.630 (16.0)
.866 (22.0)
.984 (25.0)

DIMENSIONS: $\frac{\text{MM}}{\text{(INCHES)}}$

How To Order

51	A	A	D	-	B	28	-	A	15	L
----	---	---	---	---	---	----	---	---	----	---

MOUNTING BRACKET/ ANTI-ROTATION LUG

Code	Description
A	AR Lug 90 °CW
D	No AR Lug or Bracket
L	Front Bracket
M	Rear Bracket
N	Front and Rear Bracket

SECTIONS/DETENTS

Code	Description
A	Single No Detent
B	Double No Detent
E	Single w/Center Detent
F	Double w/Center Detent

BUSHING CONFIGURATION

Code	Description
A	3/8 " D x 3/8 " L
C	1/4 " D x 1/4 " L
R	10 mm D x 9.5 mm L
S	6 mm D x 8 mm L
U	7 mm D x 8 mm L

MODEL

Code	Description
51	PC Pins (.100 " centers)
53	Solder Lugs

RoHS IDENTIFIER	
Code	Description
L	Compliant

ELEMENT TAPER TYPE/TOLERANCE		RESISTANCE (CODE)	
Code	Description	VALUE IN OHMS	
(A)	Linear Cermet $\pm 10\%$	(28) — 150	(14) — 7.5 K
(H)	Linear Cermet $\pm 5\%$	(06) — 200	(15) — 10 K
		(07) — 250	(30) — 15 K
		(08) — 500	(16) — 20 K
		(09) — 750	(17) — 25 K
		(10) — 1 K	(18) — 50 K
		(29) — 1.5 K	(19) — 75 K
		(11) — 2 K	(20) — 100 K
		(12) — 2.5 K	(23) — 500 K
		(13) — 5 K	(25) — 1 M
(B)	Linear C-P $\pm 20\%$	(10) — 1 K	(18) — 50 K
(E)	Linear C-P $\pm 10\%$	(12) — 2.5 K	(20) — 100 K
		(13) — 5 K	(22) — 250 K
		(15) — 10 K	(23) — 500 K
		(16) — 20 K	(25) — 1 M
		(17) — 25 K	
(C)	CW Audio Cermet $\pm 10\%$	(10) — 1 K	(18) — 50 K
(F)	CCW Audio Cermet $\pm 10\%$	(12) — 2.5 K	(20) — 100 K
		(13) — 5 K	(23) — 500 K
		(15) — 10 K	(25) — 1 M
		(17) — 25 K	
(D)	CW Audio C-P $\pm 20\%$	(10) — 1 K	(18) — 50 K
(S)	CW Audio C-P $\pm 10\%$	(12) — 2.5 K	(20) — 100 K
		(13) — 5 K	(22) — 250 K
		(15) — 10 K	(23) — 500 K
		(17) — 25 K	(25) — 1 M
(G)	CCW Audio C-P $\pm 20\%$	(10) — 1 K	(18) — 50 K
(T)	CCW Audio C-P $\pm 10\%$	(12) — 2.5 K	(20) — 100 K
		(13) — 5 K	(22) — 250 K
		(15) — 10 K	(23) — 500 K
		(17) — 25 K	(25) — 1 M
(Y)	CW Dual Audio Taper C-P $\pm 20\%$	(10) — 1 K	(18) — 50 K
		(12) — 2.5 K	(20) — 100 K
		(13) — 5 K	(22) — 250 K
		(15) — 10 K	(23) — 500 K
		(17) — 25 K	(25) — 1 M

SHAFT TYPE		AVAILABLE ONLY IN BUSHINGS	
Code	Description	Code	Description
B	Single Slotted 1/4 "D	A	24,28
C	Single Flatted 1/4 "D	A	20,24,28,32
D	Single Plain 1/8 "D	C	16,20,24,28
E	Single Slotted 1/8 "D	C	12,16,20,24,28
R	Single Slotted 6 mmD	R	16,22,25
T	Single Slotted 4 mmD	U	16,22,25
U	Single Slotted 3 mmD	S	16,22,25

SHAFT LENGTH (FMS)		AVAILABLE ONLY IN BUSHING
Code	Description	Code
12	3/8 "	C
16	1/2 "	A, C
20	5/8 "	A, C
24	3/4 "	A, C
28	7/8 "	A, C
32	1 "	A, C
Metric		
16	16 mm	R, S, U
22	22 mm	R, S, U
25	25 mm	R, S, U

Boldface features are Bourns standard options. All others are available with higher minimum order quantities.

REV. 09/11

Specifications are subject to change without notice. Customers should verify actual device performance in their specific applications.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bourns:

[51RAA-R25-D20](#) [53CAD-E20-D15](#) [51AAD-B24-B15](#) [51CAN-E28-A15](#) [51CAN-D20-D13](#) [51SAD-U25-A13](#) [51AAD-B28-S15](#) [51AAA-B28-A15](#) [51AAA-B28-A18](#) [51AAA-B24-B18](#) [51AAA-B24-B13](#) [51AAA-B24-D10](#) [51AAA-B24-D13](#) [51AAD-B24-A25](#) [51CAA-E16-B15](#) [53CAD-E28-A15](#) [53CAA-E20-A08L](#) [53CAA-E20-A12L](#) [53CAA-E20-A13L](#) [53CAA-E20-A15L](#) [53CAA-E20-A17L](#) [53CAA-E20-A18L](#) [53CAA-E20-A20L](#) [53CAA-E20-A25L](#) [51CAD-E24-D20](#) [53AAA-B24-D20](#) [53AAA-B28-A22](#) [51SAD-U25-A20](#) [51CAD-E20-A10](#) [51AAD-B28-A10](#) [51AAD-B28-A15](#) [53RAA-R25-A13](#) [53RAD-R22-B15](#) [51CAD-E24-B13](#) [51CAD-E24-A15](#) [51CAD-E28-B15](#) [51CAD-E28-B18](#) [51AAA-B28-D15](#) [51AAA-B28-D18](#) [51AAD-B28-B10](#) [51AAD-B28-B13](#) [51AAD-B28-B20](#)