

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [38-00-7487](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: KK® Header, Vertical, with Polarizing Backwall, 5 Circuits, Tin (Sn) Plating, Circuit 5 Voided

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-99020-0087 \(PDF\)](#)

Agency Certification

UL E29179

General

Product Family PCB Headers
Series [2599](#)
Application Signal, Wire-to-Board
Overview [KK® Interconnect System - Molex](#)
Product Name KK®
UPC 822348026470

Physical

Breakaway No
Circuits (Loaded) 4
Circuits (maximum) 5
Color - Resin Natural
Durability (mating cycles max) 25
First Mate / Last Break No
Flammability 94V-2
Glow-Wire Compliant No
Guide to Mating Part No
Keying to Mating Part None
Lock to Mating Part None
Material - Metal Brass
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin Nylon
Net Weight 1.171/g
Number of Rows 1
Orientation Vertical
PC Tail Length 4.45mm
PCB Locator No
PCB Retention None
PCB Thickness - Recommended 1.60mm
Packaging Type Bag
Pitch - Mating Interface 5.08mm
Pitch - Termination Interface 5.08mm
Plating min - Mating 5.080µm
Plating min - Termination 5.080µm
Polarized to Mating Part Yes
Polarized to PCB No
Shrouded Partial
Stackable No
Surface Mount Compatible (SMC) No
Temperature Range - Operating See Product Specification
Termination Interface: Style Through Hole




image - Reference only

Series

EU RoHS

**ELV and RoHS
Compliant**
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series
[2599Series](#)

Electrical

Current - Maximum per Contact	4.5A
Voltage - Maximum	250V

Solder Process Data

Duration at Max. Process Temperature (seconds)	5
Lead-free Process Capability	Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	235

Material Info

Old Part Number	AE-2599M-5-A5
-----------------	---------------

Reference - Drawing Numbers

Product Specification	PS-99020-0087
Sales Drawing	SDAE-2599M-N*

This document was generated on 09/10/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

38-00-7487