

Customer Information Sheet

DRAWING No.: M20-789XXXX

SHEET 2 OF 2

IF IN DOUBT - ASK

(C)

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm

SPECIFICATION:**MATERIAL:**

MOULDING = PA6T UL94V-0, BLACK

CONTACTS = PHOSPHOR BRONZE

FINISH (OVER NICKEL):

42 = GOLD FLASH ON CONTACT AREA,

2.54µ 100% TIN ON TAILS

46 = 2.54µ 100% TIN

ELECTRICAL:

CURRENT RATING = 3A

VOLTAGE PROOF = 500V AC FOR ONE MINUTE

CONTACT RESISTANCE = 20mΩ MAX

INSULATION RESISTANCE = 1,000MΩ MIN.

MECHANICAL:

DURABILITY = 300 CYCLES MIN (GOLD),

50 CYCLES MIN (TIN)

INSERTION FORCE = 2.0N MAX PER PIN




WITHDRAWAL FORCE = 0.5N MIN PER PIN

ENVIRONMENTAL:

TEMPERATURE RANGE = -40° TO +105°

PACKING:

TUBE


FOR COMPLETE SPECIFICATION SEE COMPONENT
SPECIFICATION C001XX (LATEST ISSUE)**PART SECTION X-X****ORDER CODE:****M20-789XXXX****No. OF CONTACTS:**

02 TO 20, 25, 36, 40

FINISH:

42 = SELECTIVE GOLD + 100% TIN

46 = 100% TIN

**NOTES:**1. ALL TOLERANCES ARE ±0.15
UNLESS OTHERWISE STATED.

WJP	14	01.08.17	20398
NAME	ISS.	DATE	C/NOTE
APPROVED: W. J. PRESTON			
CHECKED: S. BENNETT			
DRAWN: J. EVANS			
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWINwww.harwin.com
technical@harwin.comTHIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.**TOLERANCES**X = ±1mm
X.X = ±0.50mm
X.XX = ±0.10mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED**MATERIAL:**

SEE ABOVE

FINISH:

SEE ABOVE

S/AREA:mm²**TITLE:**2.54mm PITCH SIL PC TAIL
HORIZONTAL SOCKET ASSEMBLY**DRAWING NUMBER:****M20-789XXXX**SHT
2 OF 2