



# ROHS-CPMPLIANT

| LTR | REV. | DESCRIPTION                                       | DATE      |
|-----|------|---------------------------------------------------|-----------|
| 1*2 | B    | ECR # 081203-5<br>EDIT PACKING, ADD BARCODE LABEL | 12/03/08' |



## NOTE:

- CABLE:  
UL2725 80°C 30V [26AWG(1/0.404)\*2F  
+AL/MY+DRAIN WIRE(1/0.32)\*2]TIN  
INS: FOAM-PE OD:  $\phi 1.1 \pm 0.05$ mm  
PVC JACKET OD:  $\phi (2.2 \pm 0.1) * (7.8 \pm 0.2)$ mm COLOR: RED (PANTONE 200C)  
IMPEDANCE:  $100 \pm 5$  OHM
- CONNECTOR:  
2-1 MATERIAL:  
HOUSING: HIGH TEMPERATURE POLYESTER & GLASS FIBER UL 94V-0  
TERMINAL: COPPER ALLOY, CRIMP TYPE  
2-1 PLATING:  
CONTACT AREA: G/F
- HOOD: MOLDED TYPE, PVC 45P, COLOR: BLACK(NK-K01)
- CABLE ASS'Y ELECTRICAL TEST:  
4-1 100% OPEN SHORT & MIS WIRE TEST  
4-2 CONTACT RESISTANCE 3 OHM MAX  
4-3 INSULATION RESISTANCE 10M OHM MIN  
4-4 HI-POT DC300V/0.01SEC.
- PACKING: EACH PC / POLYBAG + HEADER CARD + BAR CODE LABEL  
100 PCS / INNER CARTON, 2 INNER CARTON / MASTER CARTON



| Tolerance | Inch | M/M |
|-----------|------|-----|
| .X        | .015 | .30 |
| .XX       | .010 | .10 |
| .XXX      | .005 | .05 |

Draw  
FANNIE 12/03/08'

Check

Engr

## Rotronic Co., Ltd.

Title  
SERIAL ATA SIGNAL CABLE

Customer P/N

App'd Customer T-RAG

Scale NONE Units m/m Third Angle Projection

Dwg No. 140-1483 REV: B Sheet 1/1

|            |            |        |        |               |                |               |
|------------|------------|--------|--------|---------------|----------------|---------------|
| 140-1483-2 | 11.03.1560 | 1000   | 20     | 360*310*150   | 380*330*340    | 7611990148790 |
| 140-1483-1 | 11.03.1555 | 500    | 20     | 360*310*100   | 380*330*240    |               |
| DWG        | P/N        | L (mm) | T (mm) | INNER CTN(mm) | MASTER CTN(mm) | BAR CODE NO.  |