







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
B	3	REVISED PER ECO-15-010004	13JUL2015	NK	MZ
C		REVISED PER ECO-16-018352	24MAR2017	RS	MZ



1. CONNECTOR CAN BE FRONT OR REAR PANEL MOUNTED.
2. MAX PANEL THICKNESS-3.18

OBSOLETE	YELLOW	Ø0.75	130°	1445538-04
	NATURAL	Ø1.5	115°	1445538-03
OBSOLETE	NATURAL	Ø1.5	130°	1445538-02
	YELLOW	Ø0.75	115°	1445538-01
SEAL, WIRE ENTRY COLOR		ØX REF	K REF	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. WIEST 08MAY2001	 TE Connectivity	
DIMENSIONS:		CHK G. DOUITY 08MAY2001		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD H. WAKEEM 13JUN2003	NAME	
	0 PLC ±.5	PRODUCT SPEC	ASSEMBLY, RECEPTACLE, SIZE 8, 2 POSITION, PANEL MOUNT MINI CPC	
	1 PLC ±0.13	APPLICATION SPEC		
MATERIAL	2 PLC ±0.13	WEIGHT	RESTRICTED TO	
SEE CALLOUT	3 PLC ±0.013	CUSTOMER DRAWING		
	4 PLC ±0.0001	SCALE 4:1	SHEET 1 OF 1	REV C
	ANGLES FINISH			