

## 9423 Multi-Conductor - Audio, Control and Instrumentation Cable



For more Information  
please call

1-800-Belden1

**General Description:**

22 AWG stranded (7x30) tinned copper conductors, conductors cabled, PVC insulation, PVC Jacket.

**Physical Characteristics (Overall)****Conductor**

AWG:

| # Conductors | AWG | Stranding | Conductor Material |
|--------------|-----|-----------|--------------------|
| 9            | 22  | 7x30      | TC - Tinned Copper |

Total Number of Conductors:

9

**Insulation**

Insulation Material:

| Insulation Material      | Wall Thickness (in.) |
|--------------------------|----------------------|
| PVC - Polyvinyl Chloride | 0.011                |

**Outer Shield**

Outer Shield Material:

| Outer Shield Material |
|-----------------------|
| Unshielded            |

**Outer Jacket**

Outer Jacket Material:

| Outer Jacket Material    | Nom. Wall Thickness (in.) |
|--------------------------|---------------------------|
| PVC - Polyvinyl Chloride | .032                      |

**Overall Cable**

Overall Cabling Color Code Chart:

| Color  |
|--------|
| Black  |
| White  |
| Red    |
| Green  |
| Brown  |
| Blue   |
| Orange |
| Yellow |
| Purple |

Overall Nominal Diameter:

0.244 in.

**Mechanical Characteristics (Overall)**

|                                   |                          |
|-----------------------------------|--------------------------|
| Operating Temperature Range:      | -20°C To +80°C           |
| UL Temperature Rating:            | 80°C (UL AWM Style 2576) |
| Bulk Cable Weight:                | 39 lbs/1000 ft.          |
| Max. Recommended Pulling Tension: | 80 lbs.                  |
| Min. Bend Radius/Minor Axis:      | 2.500 in.                |

**Applicable Specifications and Agency Compliance (Overall)****Applicable Standards & Environmental Programs**

|                                    |                            |
|------------------------------------|----------------------------|
| NEC/(UL) Specification:            | CMG                        |
| CEC/C(UL) Specification:           | CMG                        |
| AWM Specification:                 | UL Style 2576 (150 V 80°C) |
| CSA Specification:                 | FT4                        |
| EU Directive 2011/65/EU (ROHS II): | Yes                        |
| EU CE Mark:                        | Yes                        |

## 9423 Multi-Conductor - Audio, Control and Instrumentation Cable

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 04/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire &amp; Cable): Yes

MIL Order #39 (China RoHS): Yes

## Flame Test

UL Flame Test: UL1685 FT4 Loading

CSA Flame Test: FT4

## Plenum/Non-Plenum

Plenum (Y/N): No

## Electrical Characteristics (Overall)

## Nom. Inductance:

Inductance (µH/ft)

.17

## Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

34

## Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

15.6

## Max. Operating Voltage - UL:

| Voltage   | Description       |
|-----------|-------------------|
| 300 V RMS | CMG               |
| 150 V RMS | UL AWM Style 2576 |

## Max. Recommended Current:

Current

2.1 Amps per conductor @ 25°C

## Put Ups and Colors:

| Item #       | Putup    | Ship Weight | Color  | Notes | Item Desc     |
|--------------|----------|-------------|--------|-------|---------------|
| 9423 060U500 | 500 FT   | 21.000 LB   | CHROME |       | 9 #22 PVC PVC |
| 9423 060100  | 100 FT   | 4.700 LB    | CHROME |       | 9 #22 PVC PVC |
| 9423 0601000 | 1,000 FT | 43.000 LB   | CHROME | C     | 9 #22 PVC PVC |
| 9423 060500  | 500 FT   | 21.500 LB   | CHROME | C     | 9 #22 PVC PVC |
| 9423 0605000 | 5,000 FT | 210.000 LB  | CHROME |       | 9 #22 PVC PVC |

## Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 09-19-2012

© 2014 Belden, Inc.  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Belden Wire & Cable:

[9423 060U500](#) [9423 0601000](#) [9423 0605000](#)