


## REVISIONS

DOC. NO. SPC-F005 \* Effective: 7/8/02 \* DCP No: 1398


DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
811	C	Renamed - was ECC-*	JWM	8/24/01	JC	9/14/01	JC	9/14/01
1865	D	RoHS ADDED	DCM	10/17/05	JWM	10/18/05	JWM	10/18/05



PART NO.	"D" HOLDING DIAMETER	"E"
ECC-2	1/8 (3.2)	21/64 (8.3)
ECC-3	3/16 (4.8)	25/64 (9.9)
ECC-4	1/4 (6.4)	27/64 (10.7)
ECC-5	5/16 (7.9)	29/64 (11.5)
ECC-6	3/8 (9.5)	31/64 (12.3)
ECC-8	1/2 (12.7)	.62 (15.7)
ECC-10	5/8 (15.9)	5/8 (15.9)
ECC-12	3/4 (19.1)	49/64 (19.4)
ECC-16	1 (25.4)	29/32 (23.0)

## NOTES:

1. MATERIAL: PROPIONATE
2. COLOR: AMBER
3. FLAMMABILITY RATING: UL94HB



DISCLAIMER:  
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED  
HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE  
BELIEVE TO BE ACCURATE AND RELIABLE. SINCE  
CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE  
USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT  
FOR THE INTENDED USE AND ASSUME ALL RISK AND  
LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:  
Unless Otherwise Specified  
Fractional Tolerance =  $\pm 1/64$

DRAWN BY: JAP DATE: 12/16/91  
CHECKED BY: DATE: 12/17/91  
APPROVED BY: DATE: 12/17/91

DRAWING TITLE: "E" Clamps  
SIZE A DWG. NO. TA-394 ELECTRONIC FILE TA-394.dwg REV D  
SCALE: NTS U.O.M.: INCHES [mm] SHEET: 1 OF 1