

# Customer Information Sheet

DRAWING No.: M80-455XX98 SHT 2 OF 2

IF IN DOUBT - ASK

(C)

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm

## SPECIFICATION:

### MATERIAL:

HOUSING = GLASS-FILLED POLYAMIDE 46,  
UL94V-0, BLACK

JACKSCREW, CIRCLIP = STAINLESS STEEL

### ELECTRICAL:

CURRENT RATING AT 25°C = 3.0A MAX

CURRENT RATING AT 85°C = 2.2A MAX

WORKING VOLTAGE = 120V AC/DC

VOLTAGE PROOF = 360V AC/DC

CONTACT RESISTANCE = 25 mΩ MAX

INSULATION RESISTANCE = 100 MΩ MIN

### MECHANICAL:

DURABILITY = 400 OPERATIONS

INSERTION FORCE = 2.8N MAX

WITHDRAWAL FORCE = 0.2N MIN


### ENVIRONMENTAL:

TEMPERATURE RANGE = -55°C TO +125°C


### PACKING:

BAG

FOR COMPLETE SPECIFICATION, SEE COMPONENT  
SPECIFICATION C040XX (LATEST ISSUE)



CONTACT POSITION No.1




### NOTES:

1. POLARISING FEATURE STYLE DEPENDANT ON NUMBER OF CONTACT POSITIONS.
2. HOUSING TO BE USED WITH DATAMATE TRIO-TEK CRIMP CONTACTS:  
M80-25300XX = 24-22 AWG REELED  
M80-25400XX = 28-26 AWG REELED  
M80-28300XX = 24-22 AWG LOOSE  
M80-28400XX = 28-26 AWG LOOSE
3. THE SPECIFICATION APPLIES WHEN HOUSING IS USED WITH THE ABOVE CONTACTS.
4. CONTACT EXTRACTION TOOL = Z80-258.
5. INSTRUCTION SHEETS ARE AVAILABLE.

| DIMENSION                                                 | CALCULATION                         |
|-----------------------------------------------------------|-------------------------------------|
| DIM 'A'                                                   | TOTAL No. OF CONTACT POSITIONS - 2  |
| DIM 'B'                                                   | TOTAL No. OF CONTACT POSITIONS + 5  |
| DIM 'C'                                                   | TOTAL No. OF CONTACT POSITIONS + 10 |
| EXAMPLE: CONNECTOR WITH 20 CONTACT POSITIONS, M80-4552098 |                                     |
| DIM 'A' = 18.00mm, DIM 'B' = 25.00mm, DIM 'C' = 30.00mm   |                                     |

POLARISING FEATURE  
DETAIL  
SEE NOTE 1

STYLE A STYLE B



ORDER CODE:

**M80-455XX98**

TOTAL No. OF  
CONTACT POSITIONS  
04, 06, 08, 10, 12, 14, 20,  
26, 28, 34, 42, 50

PLEASE CONTACT  
datamate@harwin.com  
FOR CURRENT AVAILABILITY

|                      |      |          |        |
|----------------------|------|----------|--------|
| SB                   | 3    | 30.06.11 | 11346  |
| NAME                 | ISS. | DATE     | C/NOTE |
| APPROVED: S.BENNETT  |      |          |        |
| CHECKED: M.G.PLESTED |      |          |        |
| DRAWN: B. M. KENT    |      |          |        |
| CUSTOMER REF.:       |      |          |        |
| ASSEMBLY DRG:        |      |          |        |

## HARWIN

|                                                                        |                                                                                    |                                                                                |
|------------------------------------------------------------------------|------------------------------------------------------------------------------------|--------------------------------------------------------------------------------|
| HARWIN USA<br>TEL: 603 893 5376<br>FAX: 603 893 5396<br>mis@harwin.com | HARWIN Europe (UK)<br>TEL: 023 9231 4545<br>FAX: 023 9231 4590<br>mis@harwin.co.uk | HARWIN Asia<br>TEL: +65 6 779 4909<br>FAX: +65 6 779 3868<br>mis@harwin.com.sg |
|------------------------------------------------------------------------|------------------------------------------------------------------------------------|--------------------------------------------------------------------------------|

THIS DRAWING AND ANY  
INFORMATION OR DESCRIPTIVE  
MATTER SET OUT HEREON ARE  
CONFIDENTIAL AND COPYRIGHT  
PROPERTY OF THE HARWIN  
GROUP AND MUST NOT BE  
DISCLOSED, LOANED, COPIED  
OR USED FOR MANUFACTURING,  
TENDERING OR FOR ANY  
OTHER PURPOSE WITHOUT  
THEIR WRITTEN PERMISSION.

### TOLERANCES

X. = ±1mm  
X.X = ±0.25mm  
X.XX = ±0.10mm  
X.XXX = ±0.01mm

ANGLES = ±5°

UNLESS STATED

### MATERIAL:

SEE ABOVE

FINISH:

S/AREA:

mm<sup>2</sup>

TITLE: DATAMATE TRIO-TEK  
FEMALE CRIMP HOUSING  
WITH SLOTTED JACKSCREW

DRAWING NUMBER:

**M80-455XX98**

SHT  
2 OF 2