




Precision Thin Film Chip Resistor Array ACAS06S0830373P1AT



FEATURE

- Product Information

REFERENCE

This unique special product is derived from the following underlying standard product:

- Precision Thin Film Chip Resistor Array
ACAS 0612 AT

This document is valid only in conjunction with the underlying standard product's data sheet in its most current edition:

- Precision Thin Film Chip Resistor Array
Superior Moisture Resistivity
Document No. 28770

CHARACTERIZATION

This Unique Special Product is characterized by the following facts:

The product definition meets the ranges published in the referenced data sheet:																																		
☒ COMPLETELY	☐ EXCEPT FOR: <table> <tr> <td>Temperature coefficient</td> <td>=</td> <td>± 25ppm/K</td> </tr> <tr> <td>absolute</td> <td>=</td> <td>15ppm/K</td> </tr> <tr> <td>tracking</td> <td>=</td> <td></td> </tr> <tr> <td>Tolerance on rated resistance</td> <td>=</td> <td>± 0,25%</td> </tr> <tr> <td>absolute</td> <td>=</td> <td>0,1%</td> </tr> <tr> <td>matching</td> <td>=</td> <td></td> </tr> <tr> <td colspan="3">Rated resistance values</td> </tr> <tr> <td></td> <td>R1 =</td> <td>47 000 Ω</td> </tr> <tr> <td></td> <td>R2 =</td> <td>47 000 Ω</td> </tr> <tr> <td></td> <td>R3 =</td> <td>47 000 Ω</td> </tr> <tr> <td></td> <td>R4 =</td> <td>47 000 Ω</td> </tr> </table>	Temperature coefficient	=	± 25ppm/K	absolute	=	15ppm/K	tracking	=		Tolerance on rated resistance	=	± 0,25%	absolute	=	0,1%	matching	=		Rated resistance values				R1 =	47 000 Ω		R2 =	47 000 Ω		R3 =	47 000 Ω		R4 =	47 000 Ω
	Temperature coefficient	=	± 25ppm/K																															
	absolute	=	15ppm/K																															
	tracking	=																																
	Tolerance on rated resistance	=	± 0,25%																															
	absolute	=	0,1%																															
	matching	=																																
Rated resistance values																																		
	R1 =	47 000 Ω																																
	R2 =	47 000 Ω																																
	R3 =	47 000 Ω																																
	R4 =	47 000 Ω																																
Technology and manufacturing are identical to those used for the underlying product:																																		
☒ COMPLETELY	☐ EXCEPT FOR: —																																	
The choices of deliverable versions and packaging are identical to those for the underlying product:																																		
☒ COMPLETELY	☐ EXCEPT FOR: —																																	
The details published in the referenced data sheet under <table> <tr> <td>• Technical specification</td> <td>• Dimensions</td> <td>• Description</td> </tr> <tr> <td>• Assembly</td> <td>• Functional performance</td> <td>• Test and Requirements</td> </tr> </table> apply to this product		• Technical specification	• Dimensions	• Description	• Assembly	• Functional performance	• Test and Requirements																											
• Technical specification	• Dimensions	• Description																																
• Assembly	• Functional performance	• Test and Requirements																																
☒ COMPLETELY	☐ EXCEPT FOR:																																	

ORDERING INFORMATION

Product description	ACAS 0612 47K E 47K AT P1
	ACAS 0612 47K E 47K AT P5
Part Number	ACASA4702E4702P5AT
	ACASA4702E4702P1AT