

12000X778 series

High performance toggle switches - threaded bushing Ø 11,9 (15/32)

Distinctive features

UG1410A



Approvals



CECC 96201-005

CECC 96201-008

MIL Standards MIL-DTL-3950 and MIL-DTL-83731

This range of professional toggle switches is suitable for use in military and other high specification environments.

Contacts

Highly reliable contacts suitable for low level applications or power applications

Pinned lever

The base of the switch lever is pinned to the bushing, thus earthing the lever to the bushing. This also provides strain relief to protect the switch if accidentally knocked.

Double shell case

For high mechanical strength and high electrical insulation.

Compact size

The small rear end of the switch allows space saving behind the panel.

Finish

Black finish on body, bushing, lever and hardware.

Sealing

Panel sealed to IP 67, these switches are frontal sealed by two O-rings and have full rear end sealing.

Accessories

A comprehensive range of protection boots (both full and half length), locking levers and security caps are available.

12000X778 series

High performance toggle switches - threaded bushing Ø 11,9 (15/32)


Specifications

ELECTRICAL SPECIFICATIONS

- Max. current/voltage rating with resistive load : 4A 28VDC
- Minimum load : 10mA 50mV, 10µA 5VDC

When used above 300mA 28VDC, the gold plating is removed on contact areas and is considered only as a protection against oxidation during storage.

- Initial contact resistance : 10 mΩ max.
- Insulation resistance : 1.000 MΩ min. at 500VDC
- Dielectric strength :
 - 1.000 Vrms 50 Hz min. between terminals
 - 2.000 Vrms 50 Hz min. between poles
 - 2.000 Vrms 50 Hz min. between terminals and frame
- Contact bounce : 2 ms max.
- Electrical life :
 - At 4A 28VDC : 20.000 cycles (10.000 for functions 5, 4-1R, 4-2R)
 - At low level (50mV 10mA) : 150.000 cycles (switches with 2 maintained positions)
 - 100.000 cycles (switches with 3 maintained positions)
 - 50.000 cycles (momentary functions 7, 8, 4-1R, 4-2R, 5)




MATERIALS

- Case : diallylphthalate (DAP) with plastic external shell (epoxy sealed)
- Actuator : brass, black chrome plated
- Bushing : brass, black chrome plated
- Contacts : solid rivet - gold plated silver/nickel alloy

SEALING

- Front panel sealing by two O-rings
Flattened bush for precise orientation
- Panel seal withstands 1 bar pressure and remains sealed even when the switch is operated.
- Epoxy sealed terminals
- Splash-proof case



GENERAL SPECIFICATIONS

- Torque : 1,50 Nm (1.10 Ft.lb) max. applied to nut
- Panel thickness : 8 mm (.314) max. - 3 mm (.118) min.
- Shock test : 50g - 11ms (IEC 68-2-27)
- Vibrations : 10-500 Hz - 10g (IEC68-2-6)
- Operating temperature : -40°C to +85°C
- Humidity test : 56 days, 93 % R.H., 40°C (IEC 68-2-3)
- Salt spray test : 96 hours (IEC 68-2-11)

APPROVALS



Many models within this range have full CECC approval and are marked CECC. Please consult factory for list of approved models.

12000X778 series

High performance toggle switches - threaded bushing Ø 11,9 (15/32)

Overview

A



ABOUT THIS SERIES

On the following pages, you will find successively :

- model structure of switches
- options in the same order as in above chart

Dimensions : first dimensions are in mm while inches are shown as bracketed numbers.



Sealing boots can be used to further protect the switches against dust and water. They are presented in section H.



Mounting accessories : standard hardware supplied with all models : 1 hex nut 14 mm (.551) across flats, part number U41. This nut is presented after model structure of switches.



Security caps are available to prevent inadvertent lever operation. They are presented in section I.




Packaging unit : 2 pole models : 25 pieces
3 and 4 pole models : 20 pieces




12000X778 series

High performance toggle switches - threaded bushing Ø 11,9 (15/32)


Fully sealed - black



Typical angle of throw (A)	
Function 6	26°
Functions 9, 7, 8, 4	20°
Function 5	12°



MODEL STRUCTURE




Shown with standard lever

Solder lug terminals - double pole



12146 X778
12149 X778
12147 X778
12148 X778
12144 X778
12144-1R X778
12144-2R X778
12145 X778

I II III
ON - ON
ON OFF ON
MOM OFF MOM
ON OFF MOM
ON ON ON
MOM ON ON
MOM ON MOM
ON MOM




Solder lug terminals - three pole



12156 X778
12159 X778
12157 X778
12158 X778

I II III
ON - ON
ON OFF ON
MOM OFF MOM
ON OFF MOM




Solder lug terminals - four pole



12166 X778
12169 X778
12167 X778
12168 X778
12164 X778
12164-1R X778
12164-2R X778

I II III
ON - ON
ON OFF ON
MOM OFF MOM
ON OFF MOM
ON ON ON
ON ON MOM
MOM ON MOM



12000X778 series

High performance toggle switches - threaded bushing Ø 11,9 (15/32)




Fully sealed - black

Straight PC terminals - double pole ▲



12246 X778

I II III
ON - ON




Straight PC terminals - three pole ▲



12256 X778

I II III
ON - ON




Straight PC terminals - four pole ▲




12266 X778

I II III
ON - ON




Positions and connections, see next page.

PANEL CUT-OUT




STANDARD HARDWARE

Hex nut



U41 (matt black)







▲ 3,5 mm (.138) short terminals available on request for function 6. Standard for functions 9, 7, 8, 4 and 5.



12000X778 series

High performance toggle switches - threaded bushing Ø 11,9 (15/32)

Positions and connections


FUNCTION	LEVER POSITION AND CONNECTIONS			TERMINAL IDENTIFICATION	WIRING FOR 3-WAY SWITCHES (FUNCTION 4)
	I	II	III (Flat)		
12146	ON (1-3)-4 (5-7)-8	-	ON (1-3)-2 (5-7)-6		→ External jumper (added by customer)
12147 12148 12149 12148CT	MOM ON ON MOM 1-2 4-5	OFF OFF OFF OFF	MOM MOM ON ON 1-3 4-6	→ Flat	
12145	- 1-2 4-5	ON 1-2 4-5	MOM 1-3 4-6		
12144 12144-1R 12144-2R	ON MOM MOM 1-2 4-5	ON ON ON 1-3 4-5	ON ON MOM 1-3 4-6		
12156	ON (1-3)-4 (5-7)-8 (9-11)-12	-	ON (1-3)-2 (5-7)-6 (9-11)-10		
12166	ON 1A - 3A 1C - 3C 1E - 3E 1G - 3G	-	ON 1A - 2A 1C - 2C 1E - 2E 1G - 2G		
12164	ON 1A - 2A 1C - 2C 1E - 2E 1G - 2G	ON 1A - 2A 1C - 3C 1E - 2E 1G - 3G	ON 1A - 3A 1C - 3C 1E - 3E 1G - 3G		

12000X778 series

High performance toggle switches - threaded bushing Ø 11,9 (15/32)





FLUORESCENT TIP



Standard lever

Locking lever




Blank None


-038 White fluorescent tip.
Becomes luminous when submitted to ultra-violet rays.

A


LEVERS / LOCKING LEVERS



Dash compulsory before lever code.




Standard lever (leave blank)




Short lever

Sealing boots : see section H.
Security caps : see section I.


→ Flat




-1V 1 locked position (function 6)
Typical angle of throw : 26°




-2V 2 locked positions (function 6)
Typical angle of throw : 26°



-3V 3 locked positions (functions 9 and 4)
Typical angle of throw : 20°



Note : -5V and -12V are not true locking levers : no pulling is required before actuation.



AGENCY APPROVAL



CECC CECC 96201-005 and CECC 96201-008

Availability : consult factory for details of approved models.

Marking : to order switches marked CECC, please complete above box with "CECC". Blank : no agency approval required.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Apem:

[12144X778](#) [12145X778](#) [12146X778](#) [12148X778](#) [12159X778](#) [12169X778](#) [12246X778](#) [121441R7V/1X778](#)
[121443VX778](#) [121462VX778](#) [12156X780X545](#)