





Copyright FCI.






spec ref *				dr Rick Bian 2010/07/08		projection 		size A4		scale 0.500		
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED						ecn no ELX-DG-008280-1				
-		eng Nickor Zuo 2011/11/30		chr Jian Huang 2011/12/02				rel level Released				
-		appr Pei-Ming Zheng 2011/12/02		product family								
surface 		linear	0.X ±0.38		title DDR II 240P V/T				dwg no 10005639	rev X		
			0.XX ±0.25		DDR II 240P METAL CLIP ASS'Y							
			0.XXX ±0.13									
-		angular	0° ±2°	www.fci.com	cat. no. *		Product - Customer Drw				sheet 1 of 4	

Print File - REV C - 2009-06-09



Technical drawing of a component area, showing dimensions and labels. The drawing includes a central component area with a hatched pattern. Key dimensions and labels include:

- Overall width: 133.35 ± 0.15
- Overall height: 25.4
- Left side dimensions: 3.00 MIN., 17.80 , 10.00
- Right side dimensions: 4.00 MAX., 4.00 ± 0.10
- Bottom dimensions: 63.00 , 55.00 , 123.0
- Labels: "FULL R", "COMPONENT AREA", "DATUM -A-", "PIN #64", "FUNCTION KEY (VOLTAGE KEY) TYPE 'C'", "PIN #65", "PIN #120 (BACK PIN #240)", "SEE DETAIL E", "SEE DETAIL F", "SUB KEY POS #1"
- Feature callouts: "ACK PIN #121", "PIN #1", "PIN #120 (BACK PIN #240)", "PIN #64", "FUNCTION KEY (VOLTAGE KEY) TYPE 'C'", "PIN #65", "PIN #120 (BACK PIN #240)", "SEE DETAIL E", "SEE DETAIL F", "SUB KEY POS #1"


Prof/E File : REV C : 2009-06-09



Copyright FCI.



RECOMMENDED CIRCUIT BOARD HOLE LAYOUT

spec ref *				dr Rick Bian 2010/07/08		projection 	mm 	size A4	scale 0.500	
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED						ecn no ELX-DG-008280-1	rel level Released	
-		eng Nickor Zuo 2011/11/30								
-		chr Jian Huang 2011/12/02								
		appr Pei-Ming Zheng 2011/12/02		product family						
surface 	linear	0.X	±0.38		title DDR II 240P V/T DDR II 240P METAL CLIP ASS'Y				dwg no 10005639	rev X
		0.XX	±0.25							
		0.XXX	±0.13							
-	angular	0°	±2°	www.fci.com	cat. no. *		Product - Customer Drw		sheet 3 of 4	

Print File - REV C - 2009-06-09



Copyright FCI.

10005639 - □ □ □ □ □

PLATING

STYLE : MECHAMICAL KEYING

- 1 : 1.8 VOLT. W/ CENTER KEY#1
- 2 : 2.5 VOLT. W/ LEFT KEY#1
- 3 : X.X VOLT. W/ RIGHT KEY#1

METAL CLIP

- 1 : WITH METAL CLIP + DIM "D"=3.05
- 2 : WITH METAL CLIP + DIM "D"=3.56
- 3 : WITH METAL CLIP + DIM "D"=3.43

TAIL LENGTH

CODE	DIM "B"
0	2.54
1	2.67
2	3.18
3	4.00

COLOR OF HOUSING AND EJECTOR

- 0 : BLACK HOUSING + IVORY EJECTOR
- 1 : BLUE HOUSING + IVORY EJECTOR
- 2 : BLACK HOUSING + BLACK EJECTOR
- 3 : PURPLE HOUSING + IVORY EJECTOR
- 4 : ORANGE HOUSING + IVORY EJECTOR
- 5 : GREEN HOUSING + IVORY EJECTOR
- 6 : RED HOUSING + IVORY EJECTOR
- 7 : IVORY HOUSING + IVORY EJECTOR
- 8 : YELLOW HOUSING + IVORY EJECTOR
- 9 : IVORY HOUSING + BLACK EJECTOR

CODE	CONTACT	SOLDERTAIL	UNDERPLATE
1	10u" (0.25um) MIN. GOLD	100u" (2.54um) MIN. TIN/LEAD	50u" (1.27um) MIN. NICKEL OVERALL
2	15u" (0.38um) MIN. GOLD		
3	30u" (0.76um) MIN. GOLD		
4	3u" (0.076um) MIN. GOLD		
6LF	10u" (0.25um) MIN. GOLD	100u" (2.54um) MIN. 100% TIN	50u" (1.27um) MIN. NICKEL OVERALL
7LF	15u" (0.38um) MIN. GOLD		
8LF	30u" (0.76um) MIN. GOLD		
9LF	3u" (0.076um) MIN. GOLD		
8HLF	30u" (0.76um) MIN. GOLD	GOLD FLASH	

NOTES:

- 1. MATERIAL:
HOUSING: HIGH PERFORMANCE RESINS, GLASS FILLED UL94V-0 RATED.
EJECTOR: HIGH PERFORMANCE RESINS, GLASS FILLED UL94V-0 RATED.
TERMINAL: PHOSPHOR BRONZE.
METAL CLIP: COPPER ALLOY.
- 2. FCI LOGO TO BE APPROXIMATELY LOCATED AS SHOWN ON PRINT.
- 3. PRODUCT SPECIFICATION: GS-12-251.
- 4. PACKAGING SPECIFICATION: GS-14-899.
- 5. CARD THICKNESS APPLIES ACROSS TABS AND INCLUDES PLATING AND/OR METALIZATION.
- 6. 3.00 mm MINIMUM APPLIES TO BOTH 4.00 mm WIDE NOTCH LENGTH AND COMPONENT KEEPOUT AREA.
- 7. LEADING EDGE OF CONTACT PADS SPECIFIED BY THE KEEP OUT ZONE SHALL BE FREE OF BURRS AND EXTERNAL TIE BARS. FOR OPTIMUM PERFORMANCE, THE TIE BAR IS TO BE ON AN INTERNAL LAYER SO THAT THE REMNANT CANNOT CAUSE CONTACT DAMAGE.
- 8. THE DATE CODE IS SHOWN "MM-DD-YY*" "*" MEANS PRODUCTION LINE CODE.
- 9. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- 10. THE HOUSING WILL WITH STAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.

spec ref *				dr Rick Bian 2010/07/08		projection	mm	size A4		scale 0.500			
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED						ecn no ELX-DG-008280-1					
-													
-													
		eng Nickor Zuo 2011/11/30				product family							
		chr Jian Huang 2011/12/02											
		appr Pei-Ming Zheng 2011/12/02				rel level Released							
surface ✓		linear	0.X	±0.38		title DDR II 240P V/T DDR II 240P METAL CLIP ASS'Y					dwg no 10005639		rev X
			0.XX	±0.25									
			0.XXX	±0.13									
-		angular	0°	±2°	www.fci.com		cat. no. *		Product - Customer Drw			sheet 4 of 4	