





LOC	DIST	REVISIONS						
AA	22	P	LTR	DESCRIPTION	DATE	DWN	APVD	
			A1	REV PER ECR-09-004284	16APR2009	TY	SY	



SUGGESTED PC BOARD LAYOUT
COMPONENT SIDE (TOP)
SCALE 4:1



SUGGESTED PANEL CUTOUT
SCALE 4:1

- ⚠ MATERIAL: HOUSING - NYLON, BLACK, IR REFLOW COMPATIBLE, UL 94V-0.
TERMINALS - 0.33[.013] THICK PHOS BRONZE PLATED WITH 1.27 μ m[.000050] MINIMUM THICK HARD GOLD IN LOCALIZED AREA AND 3.81 μ m[.000150] MINIMUM THICK MATTE TIN IN SOLDER AREA OVER 1.27 μ m[.000050] MINIMUM THICK NICKEL UNDERPLATE.
SHIELDS - 0.25[.010] THICK COPPER ALLOY PLATED WITH 1.27 μ m[.000050] MINIMUM NICKEL AND 2.03 μ m[.000080] MINIMUM HOT TIN DIP ON PCB GROUND TABS.
- ⚠ JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS, PART 68 SUBPART F.
- ⚠ USE #30 DRILL BIT OR 3.25mm DRILL BIT WHEN PRODUCING THESE PCB HOLES.

2.54 [.100]	5406216-2
3.56 [.140]	5406216-1
DIM A	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. ALCORTA - 06JUN2005	Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: mm[inches]		CHK J. WESTMAN - 06JUN2005	NAME S. FLICKINGER			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S. FLICKINGER - 06JUN2005	PRODUCT SPEC 108-1163			
0 PLC ± -		APPLICATION SPEC 114-2048				
1 PLC ± -		SIZE A2				
2 PLC ± 0.25[.01]		CAGE CODE 00779				
3 PLC ± 0.13[.005]		DRAWING NO C=5406216				
4 PLC ± -		RESTRICTED TO -				
ANGLES ± -		SCALE 2:1				
MATERIAL ⚠		SHEET 1 OF 1				
FINISH ⚠		REV A1				
		CUSTOMER DRAWING				