





RECOMMENDED HOLE LAYOUT

3.984	3.900	39	80	4-87215-0
3.884	3.800	38	78	3-  -9
3.784	3.700	37	76	3-  -8
3.684	3.600	36	74	3-  -7
3.584	3.500	35	72	3-  -6
3.484	3.400	34	70	3-  -5
3.384	3.300	33	68	3-  -4
3.284	3.200	32	66	3-  -3
3.184	3.100	31	64	3-  -2
3.084	3.000	30	62	3-  -1
2.984	2.900	29	60	3-  -0
2.884	2.800	28	58	2-  -9
2.784	2.700	27	56	2-  -8
2.684	2.600	26	54	2-  -7
2.584	2.500	25	52	2-  -6
2.484	2.400	24	50	2-  -5
2.384	2.300	23	48	2-  -4
2.284	2.200	22	46	2-  -3
2.184	2.100	21	44	2-  -2
2.084	2.000	20	42	2-  -1
1.984	1.900	19	40	2-  -0
1.884	1.800	18	38	1-  -9
1.784	1.700	17	36	1-  -8
1.684	1.600	16	34	1-  -7
1.584	1.500	15	32	1-  -6
1.484	1.400	14	30	1-  -5
1.384	1.300	13	28	1-  -4
1.084	1.000	10	22	1-  -3
.284	.200	2	6	1-  -2
.184	.100	1	4	1-  -1
.084	—	—	2	1-  -0
1.284	1.200	12	26	 -9
1.184	1.100	11	24	 -8
.984	.900	9	20	 -7
.884	.800	8	18	 -6
.784	.700	7	16	 -5
.684	.600	6	14	 -4
.584	.500	5	12	 -3
.484	.400	4	10	 -2
.384	.300	3	8	 -1
C	B	A	NO OF POS	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. MAYER	3-15-85	 TE Connectivity	
		CHK T. ZOLA	5-21-85		
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME ASSEMBLY, MOD II, HEADER, DOUBLE ROW, .100 X .100 CL. VERTICAL, .025 SQUARE POSTS	
		APVD R. FLICKER	5-21-85		
		PRODUCT SPEC			
		APPLICATION SPEC			
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ALL ANGLES ± ± -		WEIGHT		SIZE A2	
MATERIAL HOUSING-FLAME RETARDANT THERMOPLASTIC, COLOR-BLACK POSTS-PHOS BRONZE		FINISH POSTS-.00030 GOLD ON THE CONTACT AREA, GOLD FLASH ON SOLDER AREA, ALL OVER .00050 NICKEL		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C-87215	
				RESTRICTED TO -	
				SCALE -	
				SHEET 1 OF 1	
				REV 14	