




Sub-Miniature Non-Polar Radial Electrolytics

MLNP Series



FEATURES

- 85°C, 1000 hours assured, non-polarized series with 7mm height
- Suitable for use in circuits which has a reversed or unknown polarity
- RoHS Compliant



CHARACTERISTICS

Items	Performance									
Operating Temperature Range	-40°C ~ +85°C									
Capacitance Tolerance	±20% (at 120Hz, 20°C)									
Leakage Current (at 20°C)	I = 0.05CV or 10 (μA) whichever is greater (after 2 minutes) Where: C = rated capacitance in μF. V = rated DC working voltage in V.									
Dissipation Factor (Tan δ at 120Hz, 20°C)	Rated voltage	4	6.3	10	16	25	35	50	50	
	Tan δ (max)	0.35	0.24	0.20	0.16	0.16	0.14	0.12	0.12	
Low Temperature Characteristics	Impedance ratio shall not exceed the values given in the table below.									
	Rated voltage		4	6.3	10	16	25	35	50	63
	Impedance	Z(-25°C)/Z(+20°C)	4	4	3	2	2	2	2	2
	Ratio	Z(-40°C)/Z(+20°C)	10	10	8	6	4	3	3	3
Load Life Test (after application of the rated voltage at 85°C, the polarity inverted every 250hrs.)	Test Time		1000 Hrs							
	Capacitance Change		≤ ± 20%							
	Dissipation Factor		Less than 200% of specified value							
	Leakage Current		Within specified value							
	•The above specifications shall be satisfied when the capacitors are restored to 20°C after the rated voltage applied for 1000 hrs at 85°C.									
Shelf Life Test	Test Time		500Hrs							
	Capacitance Change		≤ ± 20%							
	Dissipation Factor		Less than 200% of specified value							
	Leakage Current		Within specified value							
	•The above specifications shall be satisfied when the capacitors are restored to 20°C after exposing them for 500 hrs at 85°C without voltage applied.									
Standards	Satisfies Characteristic W of JIS C 5141									

PART NUMBERING SYSTEM

1	4	0	-	M	L	N	P	5	0	V	2	2	-	R	C
Prefix				Series				Voltage Actual Value			Capacitance (μF) Actual Value			Suffix (RoHS compliant)	


Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.



Sub-Miniature Non-Polar Radial Electrolytics

MLNP Series

DIMENSIONS AND PERMISSIBLE RIPPLE CURRENT



Lead Spacing and Diameter (mm)

φD	4	5	6.3	8
P	1.5	2.0	2.5	3.5
φd	0.45	0.50		
α	1.0			
β	0.5			

Dimensions: φD x L (mm); Ripple Current: mA/rms @ 120Hz, 85°C																	
V.DC Contents (μF)		4V (0G)		6.3V (0J)		10V (1A)		16V (1C)		25V (1E)		35V (1V)		50V (1H)		63V (1J)	
		φD x L	mA	φD x L	mA	φD x L	mA	φD x L	mA	φD x L	mA	φD x L	mA	φD x L	mA	φD x L	mA
0.1	OR1													4 x 7	2.1	4 x 7	2.6
0.22	R22													4 x 7	4.5	4 x 7	5
0.33	R33													4 x 7	5.6	4 x 7	6.1
0.47	R47													4 x 7	6.6	4 x 7	7.3
1	010													4 x 7	9.7	4 x 7	10
2.2	2R2											4 x 7	13	4 x 7	14	5 x 7	16
3.3	3R3									4 x 7	15	5 x 7	16	5 x 7	18	6.3 x 7	20
4.7	4R7							4 x 7	18	5 x 7	18	5 x 7	20	6.3 x 7	22	8 x 7	24
10	100					4 x 7	23	5 x 7	27	6.3 x 7	28	8 x 7	30				
22	220			5 x 7	40	5 x 7	40	6.3 x 7	45	8 x 7	52						
33	330	5 x 7	40	5 x 7	40	6.3 x 7	45	8 x 7	52								
47	470	6.3 x 7	45	6.3 x 7	49	8 x 7	55										
100	101	8 x 7	66														

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Xicon:](#)

[140-MLNP35V4.7-RC](#) [140-MLNP50V4.7-RC](#) [140-MLNP10V22-RC](#) [140-MLNP16V22-RC](#) [140-MLNP35V22-RC](#) [140-MLNP50V1.0-RC](#) [140-MLNP50V.33-RC](#) [140-MLNP16V33-RC](#) [140-MLNP10V33-RC](#) [140-MLNP50V10-RC](#) [140-MLNP16V10-RC](#) [140-MLNP35V10-RC](#) [140-MLNP50V.1-RC](#) [140-MLNP50V3.3-RC](#) [140-MLNP50V.47-RC](#) [140-MLNP50V.22-RC](#) [140-MLNP10V47-RC](#) [140-MLNP50V2.2-RC](#)